



# POWERHOUSE

PRODUCT SELECTION



NAME:

QTY:

CONTACT:

METERING (Check One Option)	
Unmetered	
Digital Electronic Metering - Both Sides	
Digital Electronic Metering - Side 1 Only	
Digital Electronic Metering - Side 2 Only	

BUSSING (Check One Option)	
Single Phase Copper Stud Bus Bar	
Three Phase Copper Stud Bus Bar	
Single Phase Aluminum Mechanical Bus Bar	
Three Phase Aluminum Mechanical Bus Bar	

LIGHTING (Check One Option)	
LED Light	
No Lighting	

LENS COLOR (Check One Option)	
Amber	
Clear	
Blue	

SIDE 1			
RECEPTACLE 1 (Check One Option)	STANDARD BREAKER		RECEPTACLE 2 (Check One Option)
50A 125/250V			50A 125/250V
30A 125V			30A 125V
20A GFI Duplex			20A GFI Duplex

SIDE 2			
RECEPTACLE 1 (Check One Option)	STANDARD BREAKER		RECEPTACLE 2 (Check One Option)
50A 125/250V			50A 125/250V
30A 125V			30A 125V
20A GFI Duplex			20A GFI Duplex
None			None

ADDITIONAL 20A GFI DUPLEX	
(1) 20A GFI DUPLEX (UNMETERED)	
(2) 20A GFI DUPLEX (UNMETERED)	

Minimum of 1 Required per NEC 551

COMMUNICATIONS (Quantity of Each)	
Phone	
Internet	
CATV	

WATER OPTIONS (Check One Option)	
NONE	
1 Water Valve	
2 Water Valves	
Dual Water Meters	

COMMENTS & SPECIAL NOTES