

# Single Meter Sockets - Lever Bypass

125 - 320 Amp



EL20L71GR1F (closed)



EL20L71GR1F (open)

## Application

- Single meter position
- Receive ANSI C12.10 watt-hour meters
- Surface mount

## Construction

- Ringless cover
- NEMA Type 3R
- ANSI 61 gray E-coat finish



## Standards

- UL 414 Listed
- ANSI C12.7

## Accessories

- 5th Jaw Kit - 50366
- 200A Triplex Ground - ETB200
- AW Hub, H Hub
- 7th Jaw Kit - 50368

Part/UPC Number	Catalog Number	Amp Rating	Jaws	Service Type	Bypass	Access	Connections	
							Line	Load
79903855153	EL20L53GR1F	200	5	1Ø/3W	Lever	OH/UG	#6 - 350MCM	#6 - 350MCM
79903855154	EL20L73GR1F	200	7	3Ø/4W	Lever	OH/UG	#6 - 350MCM	#6 - 350MCM
79903855159	EL32T53GR1F	320	5	1Ø/3W	Lever	OH/UG	(2) 1/0 - 250MCM	(2) 1/0 - 250MCM
79903855160	EL32T56GR1F	320	5	1Ø/3W	Lever	OH/UG	3/8" Studs	3/8" Studs
79903855161	EL32T75GR1F	320	7	3Ø/4W	Lever	OH/UG	3/8" Studs	3/8" Studs
79903855162	EL32T76GR1F	320	7	3Ø/4W	Lever	OH/UG	3/8" Studs	3/8" Studs

Part/UPC Number	Catalog Number	Overall Dimensions			Top Provision	Knockout Layout
		Height	Width	Depth		
79903855153	EL20L53GR1F	19 <sup>1</sup> / <sub>8</sub> "	13 <sup>3</sup> / <sub>4</sub> "	5"	AW Hub, Cap	Fig. 1
79903855154	EL20L73GR1F	21 <sup>1</sup> / <sub>4</sub> "	13 <sup>3</sup> / <sub>4</sub> "	5"	AW Hub, Cap	Fig. 1
79903855159	EL32T53GR1F	36 <sup>1</sup> / <sub>8</sub> "	16"	6 <sup>1</sup> / <sub>2</sub> "	H Hub, Cap	Fig. 2
79903855160	EL32T56GR1F	36 <sup>5</sup> / <sub>8</sub> "	18 <sup>1</sup> / <sub>4</sub> "	6 <sup>1</sup> / <sub>2</sub> "	H Hub, Cap	Fig. 3
79903855161	EL32T75GR1F	38 <sup>1</sup> / <sub>8</sub> "	18 <sup>1</sup> / <sub>4</sub> "	6 <sup>1</sup> / <sub>2</sub> "	H Hub, Cap	Fig. 4
79903855162	EL32T76GR1F	39 <sup>1</sup> / <sub>8</sub> "	20 <sup>1</sup> / <sub>4</sub> "	6 <sup>1</sup> / <sub>2</sub> "	H Hub, Cap	Fig. 3





# Single Meter Sockets - Lever Bypass

125 - 320 Amp

## Knockouts - Conduit Sizes

- 1V = 1/4" diameter hole
- 1W = 1/4"
- 1Y = 5/16"
- 2B = 3/4" - 1/2"
- 4H = 3" - 2 1/2" - 2" - 1 1/2"
- 4J = 3 1/2" - 3" - 2 1/2" - 2"
- 4K = 4" - 3 1/2" - 3" - 2 1/2"
- 5G = 2 1/2" - 2" - 1 1/2" - 1 1/4" - 1"
- Top Provision = See Chart

## Knockout Layouts



Data subject to change without notice. Consult local utility for area acceptance. All dimensions are in inches.