

# Commercial Meter Pedestals - Pad Mounted



**CMP4111MC-1**



## Application

- Utility meter, main disconnect and distribution panel
- Receive ANSI C12.10 watt-hour meters

## Construction

- Ring type
- NEMA Type 3R
- ANSI 61 gray E-coat finish
- Separate sealable utility termination and meter compartments
- Padlockable disconnect and distribution section
- Underground feed

## Standards

- UL Listed
- ANSI C12.7
- EUSERC #308

## Accessories

- 5th jaw kit - 50365 (single phase)
- Filler plate kit - 25139
- Class T fusible pullouts
- Controls, see page 109

Commercial  
Meter Pedestals

Catalog Number	Amp Rating	Jaws	Service Type	Bypass	Voltage	Distribution		Type	Mounting Pad	Dimensions		
						Main Breaker	Branches			Width	Depth	Height
CMP4111MC-1	100	4	1Ø,3W	TB	240	100A,2P	12	Plug-In	MB1515	15"	17 1/2"	54"
CMP4111MCH-1	100	4	1Ø,3W	TB	480	100A,2P	14	Bolt-On	MB2015	20"	17 1/2"	54"
CMP4121MC-1	200	4	1Ø,3W	TB	240	200A,2P	12	Plug-In	MB2015	20"	17 1/2"	54"
CMP4121MCH-1	200	4	1Ø,3W	TB	480	200A,2P	18	Bolt-On	MB1515	15"	17 1/2"	54"
CMP4411MC-1	100	7	3Ø,4W	TB	240	100A,3P	12	Plug-In	MB1515	15"	17 1/2"	54"
CMP4411MCH-1	100	7	3Ø,4W	TB	480	100A,3P	12	Bolt-On	MB2015	20"	17 1/2"	54"
CMP4421MC-1	200	7	3Ø,4W	TB	240	200A,3P	12	Plug-In	MB1515	15"	17 1/2"	54"
CMP4421MCH-1	200	7	3Ø,4W	TB	480	200A,3P	18	Bolt-On	MB2015	20"	17 1/2"	54"

