

Commercial Meter Pedestals - Pad Mounted, Unmetered



CUP4111

Application

- Utility meter, main disconnect and distribution panel

Construction

- Ring type
- NEMA Type 3R
- ANSI 61 gray E-coat finish
- Separate sealable utility termination and meter compartments
- Padlockable disconnect and distribution section
- Underground feed

Standards

- UL Listed
- ANSI C12.7

Accessories

- 5th jaw kit - 50365 (single phase)
- Filler plate kit - 25139
- Class T fusible pullouts
- Controls, see page 109

Catalog Number	Amp Rating	Service Type	Bypass	Distribution				Mounting Pad	Dimensions		
				Voltage	Main Breaker	Branches	Type		Width	Depth	Height
CUP4111	100	1Ø,3W	TB	240	100A,2P	12	Plug-In	MB1515	15"	17 1/2"	32"
CUP4111H	100	1Ø,3W	TB	480	100A,2P	14	Bolt-On	MB2015	20"	17 1/2"	32"
CUP4121	200	1Ø,3W	TB	240	200A,2P	12	Plug-In	MB1515	20"	17 1/2"	32"
CUP4121H	200	1Ø,3W	TB	480	200A,2P	18	Bolt-On	MB2015	15"	17 1/2"	32"
CUP4411	100	3Ø,4W	TB	240	100A,3P	12	Plug-In	MB1515	15"	17 1/2"	32"
CUP4411H	100	3Ø,4W	TB	480	100A,3P	12	Bolt-On	MB2015	20"	17 1/2"	32"
CUP4421	200	3Ø,4W	TB	240	200A,3P	12	Plug-In	MB1515	15"	17 1/2"	32"
CUP4421H	200	3Ø,4W	TB	480	200A,3P	18	Bolt-On	MB2015	20"	17 1/2"	32"

