

Meter Socket / Enclosure Combination Cabinets

CT Rated



U122013 (closed)



U122013 (open)

Application

- Removable test switch perch included
- Includes provisions to install model 6019/6067 CT mounts
- Receive ANSI C12.10 watt-hour meters
- Overhead and/or underground feed (see chart)
- Surface mount

Construction

- Ring type
- NEMA Type 3R
- ANSI 61 gray E-coat finish
- Aluminum snap ring included



Standards

- UL 414 Listed
- ANSI C12.7
- EUSERC 313
- EUSERC 314

Part/UPC Number	Catalog Number	Amp Rating	Jaws	Service Type	Access	Connections		
						Line	Load	Neutral
78205150030	121814	20	4	1Ø	OH/UG	#14 - #10	#14 - #10	#14 - #10
78205150040	121815	20	5	1Ø	OH/UG	#14 - #10	#14 - #10	#14 - #10
78205150020	121816	20	6	1Ø	OH/UG	#14 - #10	#14 - #10	#14 - #10
78205150050	121818	20	8	1Ø	OH/UG	#14 - #10	#14 - #10	#14 - #10
78205150080	122013	20	13	3Ø	OH/UG	#14 - #10	#14 - #10	#14 - #10
78205122735	122015	20	15	3Ø	OH/UG	#14 - #10	#14 - #10	#14 - #10
78205150090	122018	20	8	1Ø or 3Ø	OH/UG	#14 - #10	#14 - #10	#14 - #10
78205149000	U121814 *	20	4	1Ø	UG	#14 - #10	#14 - #10	#14 - #10
78205149010	U121815 *	20	5	1Ø	UG	#14 - #10	#14 - #10	#14 - #10
78205149020	U121816 *	20	6	1Ø	UG	#14 - #10	#14 - #10	#14 - #10
78205149030	U121818 *	20	8	1Ø or 3Ø	UG	#14 - #10	#14 - #10	#14 - #10
78205149040	U122013 *	20	13	3Ø	UG	#14 - #10	#14 - #10	#14 - #10
78205149045	U122015 *	20	15	3Ø	UG	#14 - #10	#14 - #10	#14 - #10
78205149050	U122018 *	20	8	1Ø or 3Ø	UG	#14 - #10	#14 - #10	#14 - #10

Part/UPC Number	Catalog Number	Overall Dimensions			L Dimension	Top Provision	Knockout Layout
		Height	Width	Depth			
78205150030	121814	42"	24"	11"	15 ¹¹ / ₁₆ "	H Hub	Fig. 1
78205150040	121815	42"	24"	11"	15 ¹¹ / ₁₆ "	H Hub	Fig. 1
78205150020	121816	42"	24"	11"	15 ¹¹ / ₁₆ "	H Hub	Fig. 1
78205150050	121818	42"	24"	11"	15 ¹¹ / ₁₆ "	H Hub	Fig. 1
78205150080	122013	42"	36"	11"	15 ¹¹ / ₁₆ "	H Hub	Fig. 2
78205122735	122015	42"	36"	11"	15 ¹¹ / ₁₆ "	H Hub	Fig. 2
78205150090	122018	42"	36"	11"	15 ¹¹ / ₁₆ "	H Hub	Fig. 2
78205149000	U121814 *	52"	24"	11"	25 ¹¹ / ₁₆ "	None	Fig. 1
78205149010	U121815 *	52"	24"	11"	25 ¹¹ / ₁₆ "	None	Fig. 1
78205149020	U121816 *	52"	24"	11"	25 ¹¹ / ₁₆ "	None	Fig. 1
78205149030	U121818 *	52"	24"	11"	25 ¹¹ / ₁₆ "	None	Fig. 1
78205149040	U122013 *	52"	36"	11"	25 ¹¹ / ₁₆ "	None	Fig. 2
78205149045	U122015 *	52"	36"	11"	25 ¹¹ / ₁₆ "	None	Fig. 2
78205149050	U122018 *	52"	36"	11"	25 ¹¹ / ₁₆ "	None	Fig. 2




* Items beginning with "U" comply with EUSERC 314, all other items comply with EUSERC 313.

Data subject to change without notice. Consult local utility for area acceptance. All dimensions are in inches.




Meter Socket / Enclosure Combination Cabinets

Style #	Suffixes
(U) 121814	SS - Stainless Steel
(U) 121815	
(U) 121816	
(U) 121818	
(U) 122013	
(U) 122015	
(U) 122018	

CT Rated



Test Switch Perch Instructions



This enclosure is assembled with the test switch installed at a factory offset distance from the cover (see Figure 1). If a greater offset is desired, follow these instructions:

1. Loosen and remove the screws holding the perch to the bracket, remove the perch. Loosen and remove the nuts on the bracket studs. (See Figure X)
2. Remove and rotate the brackets 180 degrees and relocate back onto bracket studs. (See Figure Y) Then fasten the nuts back on the bracket studs and torque them to 45 in/lbs.
3. Place the perch on the brackets and fasten with the screws, and torque screws to 35 in/lbs. (See Figure Z)

Data subject to change without notice. Consult local utility for area acceptance. All dimensions are in inches.