

CT Mounting Bases



6019 HE



6019 HELS



6019 HEL



Application

- For use with CT rated enclosures
- For use with ANSI C12.11 bar type current transformers

Construction

- Bar mounts are 1/2" studs on 1 3/4" centers (line & load)

Standards

- UL 414 Listed
- ANSI C12.7
- EUSERC 328A (6019 stud/stud)
- EUSERC 328B (6019 lug/lug)
- EUSERC 329A (6067 stud/stud)
- EUSERC 329B (6067 lug/lug)

Part/UPC Number	Catalog Number	Amp Rating	# of C.T. Provisions	Service Type	Access	AIC	Phase / Neutral Conductors Line	Load
78205137750	6019 A	400	2	1Ø or 3Ø/3W	OH/UG	10K	Studs	Studs
78205137755	6019 E	800	2	1Ø or 3Ø/3W	OH/UG	10K	Studs	Studs
78205140822	6019 HA	400	2	1Ø or 3Ø/3W	OH/UG	50K	Studs	Studs
78205108761	6019 HAL	400	2	1Ø or 3Ø/3W	OH/UG	50K	#4 - 600 MCM	#4 - 600 MCM
78205111459	6019 HALS	400	2	1Ø or 3Ø/3W	OH/UG	50K	Studs	#4 - 600 MCM
78205140826	6019 HE	800	2	1Ø or 3Ø/3W	OH/UG	50K	Studs	Studs
78205108608	6019 HEL	800	2	1Ø or 3Ø/3W	OH/UG	50K	#4 - 600 MCM	#4 - 600 MCM
78205111461	6019 HELS	800	2	1Ø or 3Ø/3W	OH/UG	50K	Studs	#4 - 600 MCM
78205137760	6067 A	400	3	3Ø/4W	OH/UG	10K	Studs	Studs
78205137765	6067 E	800	3	3Ø/4W	OH/UG	10K	Studs	Studs
78205140776	6067 HA	400	3	3Ø/4W	OH/UG	50K	Studs	Studs
78205108698	6067 HAL	400	3	3Ø/4W	OH/UG	50K	#4 - 600 MCM	#4 - 600 MCM
78205111452	6067 HALS	400	3	3Ø/4W	OH/UG	50K	Studs	#4 - 600 MCM
78205140780	6067 HEE	800	3	3Ø/4W	OH/UG	50K	Studs	Studs
78205107177	6067 HEEL	800	3	3Ø/4W	OH/UG	50K	#4 - 600 MCM	#4 - 600 MCM
78205111464	6067 HEELS	800	3	3Ø/4W	OH/UG	50K	Studs	#4 - 600 MCM

All lugs accept three (3) wires per phase/neutral