

SERIES SHORT CIRCUIT RATINGS				
MAIN MODULE BREAKER FAMILY or CLASS FUSE	SYSTEM AIC RATING AT 240 VAC MAX.	METER MODULE TENANT BREAKER or LOADCENTER MAIN BREAKER FAMILY	M.M. TENANT BREAKER or LOADCENTER MAIN BREAKER SHORT CIRCUIT RATING	LOADCENTER BRANCH BREAKER FAMILY (1, 2 or 3 POLE) + *
NONE	10,000	NONE	N/A	
WITHOUT MAIN DISCONNECT CABLE TAP BOX FAMILY 1MTB, 3MTB MAIN SWITCH MODULE FAMILY 1MFS, 3MFS TYPE 1BPS, 3BPS MAIN BREAKER MODULE FAMILY 1MCB, 3MCB	10,000	BR, CC, BW, CCV	10,000	** , BRCAF, BRAFGF, GFTCB
	22,000	BRH	22,000	
	22,000	QBHW	22,000	** , BRCAF, BRAFGF
	25,000	CSR, CCVH++	25,000	
	42,000	BRHH, CVS	42,000	** , BRCAF, BRAFGF, GFTCB
	65,000	BRX	65,000	
	65,000	CV+++	65,000	BR, BD, BRD, BQ, BQC, GFTCB
	65,000	ED, GHB	65,000	** , BRCAF, BRAFGF, GFTCB
	65,000	FD****	65,000	** , BRAFGF, GFTCB
	65,000	KD, HKD	100,000	BR
100,000	KDC	100,000		
100,000	CVH	100,000	BR, BD, BRD, BQ, BQC, GFTCB	
65,000	T / J fuse(200A Max)	100,000	** , BRAFGF, BRH	
MAIN BREAKER MODULE FAMILY 1MCB, 3MCB RGH / PDG6xM 2000A NGS / PDG5xM 1200A MDL / PDG4xG 800A LGS / LD / PDG3xG 600A KD / PDG3xG 400A	65,000	BRHX	22,000	** , GFTCB
MAIN BREAKER MODULE FAMILY 1MCB, 3MCB RGH / PDG6xM 2000A NGH1 / PDG5xM 1200A HMDL / PDG4xM 800A LGH / HLD / PDG3xM 600A HKD / PDG3xM 400A	100,000	BRHX***	22,000	BR***, ETN01, GFTCB
MAIN SWITCH MODULE FAMILY 1MFS, 3MFS WITH CLASS T FUSE 600A MAX	100,000	BRH	22,000	** , BRCAF, GFTCB
MAIN SWITCH MODULE FAMILY 1MFS, 3MFS WITH CLASS T FUSE 1200A MAX	100,000	BRHH	42,000	
*BREAKERS IN THIS COLUMN MAY NOT FIT IN THIS LOADCENTER, SEE BREAKER INFO TO LEFT. ** ALSO INCLUDES THESE BRANCH BREAKER FAMILIES: BR, BD, BRD, BQ, BQC, ETN01. ***BR (110 AMPS MAX.) +GFTCB/GFCB (50 AMPS MAX UNLESS OTHERWISE NOTED) ****FD 150A ONLY WITH ETN01 ++GFTCB (30 AMPS MAX.) +++GFTCB (1 POLE 40A MAX.)				



Powering Business Worldwide