

CH loadcenter series rating

SERIES SHORT CIRCUIT RATINGS				
MAIN MODULE BREAKER FAMILY or CLASS FUSE	SYSTEM AIC RATING AT 240 VAC MAX.	METER MODULE TENANT BREAKER or LOADCENTER MAIN BREAKER FAMILY	M.M. TENANT BREAKER or LOADCENTR MAIN BREAKER SHORT CIRCUIT RATING	LOADCENTER BRANCH BREAKER FAMILY (1, 2 or 3 POLE) *
NONE	10,000	NONE	N/A	SEE NOTE **
	100,000	T fuse(400A Max)	100,000	CH***,CHFCAF,CHFGF
WITHOUT MAIN DISCONNECT CABLE TAP BOX FAMILY 1MTB or 3MTB MAIN SWITCH MODULE FAMILY 1MFS or 3MFS 1BPS or 3BPS MAIN BREAKER MODULE FAMILY 1MCB or 3MCB	10,000	BR,CC,BW,CCV,CH,CHF	10,000	SEE NOTE **, ETN02
	22,000	BRH	22,000	
	22,000	QBHW	22,000	CH,CHF,CHFAFGF,CHFGFT,CHFCAF,ETN02
	25,000	CSR***,BWH***	25,000	CH,CHF,CHT,CHFCAF,CHFGF
	25,000	CCVH	25,000	CH,CHF,CHFGFT,CHFCAF,ETN02
	42,000	BRHH,CVS	42,000	SEE NOTE **, ETN02
	65,000	BRX,CV,ED,GHB	65,000	SEE NOTE **
	25,000	KD	25,000	
	100,000	CVH	100,000	
				SEE NOTE **
MAIN BRKR MOD FAMILY 1MCB or 3MCB RGH / PDG6xM 2000A NGS / PDG5xM 1200A MDL / PDG4xG 800A LGS / LD / PDG3xG 600A KD / PDG3xG 400A	65,000	BRHX	22,000	SEE NOTE **, ETN02
MAIN BRKR MOD FAMILY 1MCB, 3MCB RGH / PDG6xM 2000A NGH / PDG5xM 1200A HMDL / PDG4xM 800A LGH / HLD / PDG3xM 600A HKD / PDG3xM 400A	100,000	BRHX	22,000	
MAIN SWITCH MOD FAMILY 1MFS or 3MFS WITH CLASS T FUSE 600A MAX	100,000	BRH	22,000	SEE NOTE **
MAIN SWITCH MOD FAMILY 1MFS or 3MFS WITH CLASS T FUSE 1200A MAX	100,000	BRHH	42,000	
*BREAKERS IN THIS COLUMN MAY NOT FIT IN THIS LOADCENTER, SEE BREAKER INFO TO LEFT. ** ALSO INCLUDES THESE BRANCH BREAKER FAMILIES: CH, CHF, CHT, CHFAFGF, CHFGFT, CHFCAF. ***CSR & BWH (200 AMPS MAX.) ****CH (70 AMPS MAX.)				



Powering Business Worldwide