

Pricing shown on this list expires June 30th 2024.

Customer Metering and Monitoring Devices

Item	Minimum Lead Time
Addressable Relay II (ARII)	C
Audible Horn/Buzzer Alarm (alarm cause to be added in note, i.e. ground fault trip, etc...)	C
Basler BE1-60 (voltage balance relay)	C
Basler ES-25 (synch check relay)	C
Control Power transformer - 1kVA	C
Control Power transformer - 2kVA	C
Control Power transformer - 3kVA	C
Eaton Pushbutton Control Box and Cable. Style# 1C15983G01	C
Eaton Receptacle and cap [to use with pushbutton control box]. Style# 1C15983G04	C
Key Interlock (additional/loose)	C
Key Interlock - SKRU type	C
Lockout relay (style# 7804D)	C
MINTII RS-232 MINT	C
MMINT	C
Potential Transformer (each)	C
PXM 4000/6000/8000 12" screen upgrade (standard is 6")	D
Taylor Phase Guard (voltage monitoring relay)	C
VERISAFE ABSENCE OF VOLTAGE TESTER (catalog VS-AVT-C08-L10)	C
Voltage Vision (catalog# R-3W)	C
<i>To add one of the following components, first add a Customer Metering - Special Metering - CT's only (3) wired to shorting block*</i>	
<i>*Consult product line if attempting to mount in a chassis section</i>	
Item	Minimum Lead Time
Customer supplied, customer installed meter/relay (factory provisions only)	C
Customer supplied, factory installed meter/relay	C
Basler BE1-11f	C
EDR-3000 (M)	C
EDR-5000	C
EGR-4000	C
ETR-4000	C
ION 7600	C
ION 8600	C
PM820	C

PM8000	C
PM5500	C
PQM-II (GE)	C
SEL-735	C
SEL-700G	C
SEL-751A (base model - no cards)	C
SEL-751A (contains 1 to 3 optional cards or conformal coating)	D
Veris E50H5	C

Device Accessories & Modifications

SUB GROUP: Bolted Pressure Switches

Item	Minimum Lead Time
5000A SWITCH (NON-UL- contact factory for price and dimensions)	E
6000A SWITCH (NON-UL- contact factory for price and dimensions)	E
Special Padlock in either OPEN or CLOSED	C
Basler ES-25 (synch check relay)	C
Control Power transformer - 1kVA	C
Control Power transformer - 2kVA	C

SUB GROUP: PD-SB & Magnum Circuit Breakers

Item	Minimum Lead Time
4 pole option (contact factory for price and dimensions)	E

Bus Modifications

Item	Minimum Lead Time
Insulated horizontal cross bus - sleeved (Must Price Density Bus) (The bus joints are not covered for maintenance reasons)	D
Epoxy coated bus is not an available offering. Our insulated bus offering is to use a flame retardant, sleeve type insulation. This would only be installed on bus bar runs that are longer than 8" without any joints, so there will still be a lot of exposed bus within the general construction.	D

Structure Modifications		
<i>SUB GROUP: IR Windows</i>		
Item		Minimum Lead Time
IR Windows		
Iriss CAP-ENV-12		D
Iriss CAP-ENV-18		D
Iriss CAP-ENV-24 (not available in sections 30" wide or smaller)		D
IR windows are typically only used to monitor cable terminations.		
IR windows are not an option on chassis structures.		
<i>SUB GROUP: Heat/Humidity</i>		
Item		Minimum Lead Time
Space heater - per additional required		C
Humidistat	per structure	B
<i>SUB GROUP: Tamper Resistant Hardware</i>		
Item		Minimum Lead Time
Tamper resistant hardware	per structure	C
Chicago, Phoenix, Los Angeles		
<i>SUB GROUP: Type 3R Enclosure & Modifications</i>		
Item		Minimum Lead Time
Type 3R Enclosure modifications		
Gasketing	per structure	B
Filters behind louvers (<i>not N12</i>)	per structure	B
Screens to keep out insects	per structure	B
Interior LED Lighting	per structure	C
Light switch & duplex receptacle	per structure	C
Limit switch for interior light	per structure	C
Drip Shields (not satisfying N2 application)	per structure	C
Door-in-Door (distribution only) PRL4 trim on a chassis sectio	per structure	C

4000A Generator Quick Connect

Item	Minimum Lead Time
Pick 36" wide bussed transition structure Pick 4000A feeder structure with 4000A device selected. Ensure breaker/switch is picked with a key interlock Select the Common mod note for 4000A generator quick connect	pick within Bid Man pick within Bid Man pick within Bid Man E