

DEADFRONT ELBOW ARRESTER CROSS REFERENCE

Interface	Duty Cycle (kV)	MCOV (kV)	CPS VariGAP M.O.V.E.	CPS Gapless M.O.V.E.	Elastimold	Joslyn
15kV Class	3	2.55	—	3238018C03M	167ESA-3	8132B0003J001
	6	5.1	—	3238018C06M	167ESA-6	8132B0006J001
	9	7.65	3238118C09M	3238018C09M	—	—
	10	8.4	3238118C10M	3238018C10M	167ESA-10	8132B0010J001
	12	10.2	3238118C12M	3238018C12M	167ESA-12	8132B0012J001
	15	12.7	3238118C15M	3238018C15M	167ESA-15	—
	18	15.3	3238118C18M	3238018C18M	167ESA-18	—
25kV Class	9	7.65	3238119C09M	3238019C09M	—	—
	10	8.4	3238119C10M	3238019C10M	273ESA-10	8132B1010J001
	12	10.2	3238119C12M	3238019C12M	273ESA-12	—
	15	12.7	3238119C15M	3238019C15M	273ESA-15	—
	18	15.3	3238119C18M	3238019C18M	273ESA-18	8132B0018J001
	21	17.0	3238119C21M	3238019C21M	273ESA-21	—
35kV Class	18 ⁽³⁾	15.3	3238120C18M	3238020C18M	—	—
	21 ⁽³⁾	17.0	3238120C21M	3238020C21M	—	—
	24 ⁽²⁾	19.5	—	—	375ESA-24	—
	24 ⁽³⁾	19.5	3238120C24M	3238020C24M	—	8132B2024J001
	27 ⁽¹⁾	22.0	—	—	—	8132B0027J001
	27 ⁽²⁾	22.0	—	—	375ESA-27	8132B1027J001
	27 ⁽³⁾	22.0	3238120C27M	3238020C27M	—	8132B2027J001
	30 ⁽²⁾	24.4	—	—	375ESA-30	—

- (1) Large Interface; Single Phase Rated Probe
- (2) Small Interface
- (3) Large Interface; Three Phase Rated Probe

PARKING STAND ARRESTER CROSS REFERENCE

Interface	Duty Cycle (kV)	MCOV (kV)	CPS VariGAP	CPS (Gapless)	Elastimold
15kV Class	3	2.55	—	3237686C03M	167PSA-3
	6	5.1	—	3237686C06M	167PSA-6
	9	7.65	3238104C09M	3237686C09M	—
	10	8.4	3238104C10M	3237686C10M	167PSA-10
	12	10.2	3238104C12M	3237686C12M	167PSA-12
	15	12.7	3238104C15M	3237686C15M	167PSA-15
	18	15.3	3238104C18M	3237686C18M	167PSA-18
25kV Class	9	7.65	3238105C09M	3237758C09M	—
	10	8.4	3238105C10M	3237758C10M	273PSA-10
	12	10.2	3238105C12M	3237758C12M	273PSA-12
	15	12.7	3238105C15M	3237758C15M	273PSA-15
	18	15.3	3238105C18M	3237758C18M	273PSA-18
	21	17.0	3238105C21M	3237758C21M	273PSA-21