

No.: CP-0507 Rev.01
 E-Ref.: None
 Supersedes: 5/15/2005
 File Ref.: Cat. Sec. 240-94
 Date: 06/09/06

Cross Reference: S&C Electric SMU[®]-20/Cooper Power Systems CMU-20 Power Fuses

Voltage Ratings, Speed	S&C SMU-20 Catalog Number	Cooper CMU-20 Catalog Number	Description
17 kV, K	702003	CMU702003	FUSE, POWER, CMU-20,17KV,3 AMP,K
	702006	CMU702006	6 AMP,K
	702008	CMU702008	8 AMP,K
	702010	CMU702010	10 AMP,K
	702012	CMU702012	12 AMP,K
	702015	CMU702015	15 AMP,K
	702020	CMU702020	20 AMP,K
	702025	CMU702025	25 AMP,K
	702030	CMU702030	30 AMP,K
	702040	CMU702040	40 AMP,K
	702050	CMU702050	50 AMP,K
	702065	CMU702065	65 AMP,K
	702080	CMU702080	80 AMP,K
	702100	CMU702100	100 AMP,K
	702140	CMU702140	140 AMP,K
702200	CMU702200	200 AMP,K	
17 kV, E	612005	CMU612005	FUSE, POWER, CMU-20,17KV,5 AMP,E
	612007	CMU612007	7 AMP,E
	612010	CMU612010	10 AMP,E
	612013	CMU612013	13 AMP,E
	612015	CMU612015	15 AMP,E
	612020	CMU612020	20 AMP,E
	612025	CMU612025	25 AMP,E
	612030	CMU612030	30 AMP,E
	612040	CMU612040	40 AMP,E
	612050	CMU612050	50 AMP,E
	612065	CMU612065	65 AMP,E
	612080	CMU612080	80 AMP,E
	612100	CMU612100	100 AMP,E
	612125	CMU612125	125 AMP,E
	612150	CMU612150	150 AMP,E
612175	CMU612175	175 AMP,E	
612200	CMU612200	200 AMP,E	

No.: CP-0507 Rev.01
 E-Ref.: None
 Supersedes: 5/15/2005
 File Ref.: Cat. Sec. 240-94
 Date: 06/09/06

**Cross Reference: S&C Electric SMU[®]-20/Cooper Power Systems
 CMU-20 Power Fuses**

Voltage Ratings, Speed	S&C SMU-20 Catalog Number	Cooper CMU-20 Catalog Number	Description
17 kV, SE	712015	CMU712015	FUSE, POWER, CMU-20,17KV,15 AMP,SE
	712020	CMU712020	20 AMP,SE
	712025	CMU712025	25 AMP,SE
	712030	CMU712030	30 AMP,SE
	712040	CMU712040	40 AMP,SE
	712050	CMU712050	50 AMP,SE
	712065	CMU712065	65 AMP,SE
	712080	CMU712080	80 AMP,SE
	712100	CMU712100	100 AMP,SE
	712125	CMU712125	125 AMP,SE
	712150	CMU712150	150 AMP,SE
	712175	CMU712175	175 AMP,SE
712200	CMU712200	200 AMP,SE	
27 kV, K	703003	CMU703003	FUSE, POWER, CMU-20,27KV,3 AMP,K
	703006	CMU703006	6 AMP,K
	703008	CMU703008	8 AMP,K
	703010	CMU703010	10 AMP,K
	703012	CMU703012	12 AMP,K
	703015	CMU703015	15 AMP,K
	703020	CMU703020	20 AMP,K
	703025	CMU703025	25 AMP,K
	703030	CMU703030	30 AMP,K
	703040	CMU703040	40 AMP,K
	703050	CMU703050	50 AMP,K
	703065	CMU703065	65 AMP,K
	703080	CMU703080	80 AMP,K
	703100	CMU703100	100 AMP,K
	703140	CMU703140	140 AMP,K
703200	CMU703200	200 AMP,K	

No.: CP-0507 Rev.01
 E-Ref.: None
 Supersedes: 5/15/2005
 File Ref.: Cat. Sec. 240-94
 Date: 06/09/06

**Cross Reference: S&C Electric SMU[®]-20/Cooper Power Systems
 CMU-20 Power Fuses**

Voltage Ratings, Speed	S&C SMU-20 Catalog Number	Cooper CMU-20 Catalog Number	Description
27 kV, E	613005	CMU613005	FUSE, POWER, CMU-20,27KV,5 AMP,E
	613007	CMU613007	7 AMP,E
	613010	CMU613010	10 AMP,E
	613013	CMU613013	13 AMP,E
	613015	CMU613015	15 AMP,E
	613020	CMU613020	20 AMP,E
	613025	CMU613025	25 AMP,E
	613030	CMU613030	30 AMP,E
	613040	CMU613040	40 AMP,E
	613050	CMU613050	50 AMP,E
	613065	CMU613065	65 AMP,E
	613080	CMU613080	80 AMP,E
	613100	CMU613100	100 AMP,E
	613125	CMU613125	125 AMP,E
	613150	CMU613150	150 AMP,E
	613175	CMU613175	175 AMP,E
613200	CMU613200	200 AMP,E	
27 kV, SE	713015	CMU713015	FUSE, POWER, CMU-20,27KV,15 AMP,SE
	713020	CMU713020	20 AMP,SE
	713025	CMU713025	25 AMP,SE
	713030	CMU713030	30 AMP,SE
	713040	CMU713040	40 AMP,SE
	713050	CMU713050	50 AMP,SE
	713065	CMU713065	65 AMP,SE
	713080	CMU713080	80 AMP,SE
	713100	CMU713100	100 AMP,SE
	713125	CMU713125	125 AMP,SE
	713150	CMU713150	150 AMP,SE
	713175	CMU713175	175 AMP,SE
	713200	CMU713200	200 AMP,SE

No.: CP-0507 Rev.01
 E-Ref.: None
 Supersedes: 5/15/2005
 File Ref.: Cat. Sec. 240-94
 Date: 06/09/06

**Cross Reference: S&C Electric SMU[®]-20/Cooper Power Systems
 CMU-20 Power Fuses**

Voltage Ratings, Speed	S&C SMU-20 Catalog Number	Cooper CMU-20 Catalog Number	Description
38 kV, K	704003	CMU704003	FUSE, POWER, CMU-20,38KV,3 AMP,K
	704006	CMU704006	6 AMP,K
	704008	CMU704008	8 AMP,K
	704010	CMU704010	10 AMP,K
	704012	CMU704012	12 AMP,K
	704015	CMU704015	15 AMP,K
	704020	CMU704020	20 AMP,K
	704025	CMU704025	25 AMP,K
	704030	CMU704030	30 AMP,K
	704040	CMU704040	40 AMP,K
	704050	CMU704050	50 AMP,K
	704065	CMU704065	65 AMP,K
	704080	CMU704080	80 AMP,K
	704100	CMU704100	100 AMP,K
	704140	CMU704140	140 AMP,K
704200	CMU704200	200 AMP,K	
38 kV, E	614005	CMU614005	FUSE, POWER, CMU-20,38KV,5 AMP,E
	614007	CMU614007	7 AMP,E
	614010	CMU614010	10 AMP,E
	614013	CMU614013	13 AMP,E
	614015	CMU614015	15 AMP,E
	614020	CMU614020	20 AMP,E
	614025	CMU614025	25 AMP,E
	614030	CMU614030	30 AMP,E
	614040	CMU614040	40 AMP,E
	614050	CMU614050	50 AMP,E
	614065	CMU614065	65 AMP,E
	614080	CMU614080	80 AMP,E
	614100	CMU614100	100 AMP,E
	614125	CMU614125	125 AMP,E
	614150	CMU614150	150 AMP,E
614175	CMU614175	175 AMP,E	
614200	CMU614200	200 AMP,E	

No.: CP-0507 Rev.01
 E-Ref.: None
 Supersedes: 5/15/2005
 File Ref.: Cat. Sec. 240-94
 Date: 06/09/06

**Cross Reference: S&C Electric SMU[®]-20/Cooper Power Systems
 CMU-20 Power Fuses**

Voltage Ratings, Speed	S&C SMU-20 Catalog Number	Cooper CMU-20 Catalog Number	Description
38 kV, SE	714015	CMU714015	FUSE, POWER, CMU-20,38KV,15 AMP,SE
	714020	CMU714020	20 AMP,SE
	714025	CMU714025	25 AMP,SE
	714030	CMU714030	30 AMP,SE
	714040	CMU714040	40 AMP,SE
	714050	CMU714050	50 AMP,SE
	714065	CMU714065	65 AMP,SE
	714080	CMU714080	80 AMP,SE
	714100	CMU714100	100 AMP,SE
	714125	CMU714125	125 AMP,SE
	714150	CMU714150	150 AMP,SE
	714175	CMU714175	175 AMP,SE
714200	CMU714200	200 AMP,SE	
	3097	CMU3097	FUSE, POWER, CMU-20, END FITTINGS INDOOR
	3095	CMU3095	FUSE, POWER, CMU-20, END FITTINGS OUTDOOR
	FDA1103	CMUFDA1103	FUSE, POWER, CMU-20, MUFFLER

* S&C Electric does not sell loadbreak live-parts separately from mountings.
 SMU[®] Is a registered trademark of S&C Electric Inc.