

Elbow Arrester Cross Reference Tables

Table 1. Parking Stand Arrester Cross Reference Table

Interface	Duty Cycle (kV)	MCOV (kV)	Eaton M.O.V.E. [™]	Elastimold [®]
15 kV Class	3	2.55	3237686C03M	167PSA-3
	6	5.1	3237686C06M	167PSA-6
	9	7.65	3237686C09M	—
	10	8.4	3237686C10M	167PSA-10
	12	10.2	3237686C12M	167PSA-12
	15	12.7	3237686C15M	167PSA-15
	18	15.3	3237686C18M	167PSA-18
25 kV Class	9	7.65	3237758C09M	—
	10	8.4	3237758C10M	273PSA-10
	12	10.2	3237758C12M	273PSA-12
	15	12.7	3237758C15M	273PSA-15
	18	15.3	3237758C18M	273PSA-18
	21	17.0	3237758C21M	273PSA-21



Powering Business Worldwide

Table 2. Deadfront Elbow Arrester Cross Reference Table

Interface	Duty Cycle (kV)	MCOV (kV)	Eaton M.O.V.E.	Elastimold	Joslyn®	Hubbell®
15 kV Class	3	2.55	3238018C03M	167ESA-3	8132B0003J001	215ELA03
	6	5.1	3238018C06M	167ESA-6	8132B0006J001	215ELA06
	9	7.65	3238018C09M	—	—	215ELA09
	10	8.4	3238018C10M	167ESA-10	8132B0010J001	215ELA10
	12	10.2	3238018C12M	167ESA-12	8132B0012J001	215ELA12
	15	12.7	3238018C15M	167ESA-15	—	215ELA15
	18	15.3	3238018C18M	167ESA-18	—	215ELA18
25 kV Class	9	7.65	3238019C09M	—	—	225ELA09
	10	8.4	3238019C10M	273ESA-10	8132B1010J001	225ELA10
	12	10.2	3238019C12M	273ESA-12	—	225ELA12
	15	12.7	3238019C15M	273ESA-15	—	225ELA15
	18	15.3	3238019C18M	273ESA-18	8132B0018J001	225ELA18
	21	17.0	3238019C21M	273ESA-21	—	225ELA21
35 kV Class	18 ⁽³⁾	15.3	3238020C18M	—	—	—
	21 ⁽³⁾	17.0	3238020C21M	—	—	—
	24 ⁽²⁾	19.5	—	375ESA-24	—	235ELA24
	24 ⁽³⁾	19.5	3238020C24M	—	8132B2024J001	—
	27 ⁽¹⁾	22.0	—	—	8132B0027J001	—
	27 ⁽²⁾	22.0	—	375ESA-27	8132B1027J001	235ELA27
	27 ⁽³⁾	22.0	3238020C27M	—	8132B2027J001	—
	30 ⁽²⁾	24.4	—	375ESA-30	—	235ELA30
	30 ⁽³⁾	24.4	3238020C30M	—	—	—
	33 ⁽³⁾	27.0	3238020C33M	—	—	—
	36 ⁽³⁾	29.0	3238020C36M	—	—	—

(1) Large Interface; Single-Phase Rated Probe

(2) Small Interface

(3) Large Interface; Three-Phase Rated Probe

Eaton
 1000 Eaton Boulevard
 Cleveland, OH 44122
 United States
 Eaton.com

Eaton's Power Systems Division
 2300 Badger Drive
 Waukesha, WI 53188
 United States
 Eaton.com/cooperpowerseries

© 2016 Eaton
 All Rights Reserved
 Printed in USA
 Publication No. TD235019EN

Eaton is a registered trademark.

All other trademarks are property
 of their respective owners.

For Eaton's Cooper Power series product
 information call 1-877-277-4636 or visit:
www.eaton.com/cooperpowerseries.