



**NR & NRV Single-Phase Oil Capacitor Switch Ordering Guide**

System Information	
System Voltage (kV-LL)	
Maximum System Voltage (kV-LL)	
System Frequency (Hz)	
System BIL (kV)	
System Fault Current (kA)	
System Grounding	<input type="checkbox"/> Grounded <input type="checkbox"/> Ungrounded

General Information	
Altitude (Feet Above Sea Level)	
Maximum Temperature (°C)	
Minimum Temperature (°C)	
Pollution Level	

Switch Information	
Switch Type	<input type="checkbox"/> 15 kV, 95 kV-BIL, 200 amp, 12" creepage <input type="checkbox"/> 15 kV, 95 kV-BIL, 200 amp, 17" creepage <input type="checkbox"/> 15 kV, 125 kV-BIL, 200 amp, 16" creepage <input type="checkbox"/> 22 kV, 125 kV-BIL, 60 amp, 17" creepage
Control Voltage (50 Hz and 60 Hz)	<input type="checkbox"/> 120 Vac <input type="checkbox"/> 240 Vac
Auxiliary Switch (SPDT)	<input type="checkbox"/>
Holding Switch	<input type="checkbox"/>

Options & Accessories	
Birdgaurds	<input type="checkbox"/>
Zinc Plated Tank	<input type="checkbox"/>
Stainless Steel Tank	<input type="checkbox"/>
Surge Arrester, 120 Vac	<input type="checkbox"/>
Switch Cable (w/one plug)	<input type="checkbox"/> Length in Feet: _____
Mating Plug	<input type="checkbox"/>
Cross Arm Mounting Bracket	<input type="checkbox"/>

Special Requirements