

Type NR oil switch spare parts list

General

This document provides Greenwood, SC part numbers for Eaton's Cooper Power™ series Type NR oil switch service parts previously supplied by South Milwaukee, WI. Cross references are provided for service parts, assemblies, and repair kits which cover necessary items for repair and maintenance of Type NR and NRV oil switches.



Powering Business Worldwide

Effective February 2016

Catalog Number	Description	Minimum Order Qty	Lead Time Code
TYPE NR, NRV SWITCH			
Greenwood Part No.	Replaces		
721515106062A	K721515106062A	SCREW-RD HD, #6-32 UNC-2A SSL	50 D
730115131137A	K730115131137A	CAPSCREW-HEX HD, 5/16X18X1 3/8 SSL	50 C
730115150100A	K730115150100A	CAPSCREW-HEX HD, 1/2-13X1 SSL	25 D
730125125125A	K730125125125A	CAPSCREW-HEX HD, 1/4-20X11/4 BRASS	50 C
751515102018A	K751515102018A & KP51	SCREW-RD HD, TYPE Z #2X3/16 SSL	50 C
751515104031A	K751515104031A	SELF TAPPING SCREW-RD HD, TYPE F 4-40X5/16 SSL	50 D
751515106037A	K751515106037A	SELF TAPPING SCREW-RD HD, TYPE F #6X3/8 SSL	50 C
802815010037A	K801515010037A	SCREW-RD HD, TYPE Z #10X3/8 SSL	50 D
831501125037A	K831501125037A	MACHINE SCREW-RD HD W/LOCKWASHER 1/4-20X3/8, PREASSEMBLED	25 D
881025118031A	K881025118031A	HEX NUT-5/16-18, BRASS	50 C
881025120025A	K881025120025A	MACHINE SCREW NUT-HEX HD, 1/4-20 BRASS	50 C
900525020043A	K900525020043A	FLAT WASHER-#10S BRASS, NO. 10S	50 C
900525026056A	K900525026056A	FLAT WASHER-9/16X.260X.040 BRASS	50 C
900525033075A	K900525033075A	PLAIN WASHER-#206 BRASS	50 C
900815006000A	K900815006000A	LOCKWASHER-#6X.047X.031 SSL	50 C
900815031000A	K900815031000A	LOCKWASHER-5/16X.125X.078, FOR USE UNDER KP416 SSL	50 D
90083002500019	K900830025000A	LOCKWASHER-1/4X.109X.062 BRONZE	50 C
900830031000A	K900830031000A	SPLIT LOCKWASHER-MED 5/16 BRONZE	50 C
901032010000A	K901032010000A	INTERNAL TOOTH STAR WASHER-#10, SSL	50 D
KA20010030	K970801125093C	ROLL PIN-1/8X15/16 STL	50 D
970901188000M	K970901188000M	RETAINING C RING-WA510	50 C
999904250369A	K999904250369A	MACHINE SCREW-FIL HD, 10-24X7/8 SST	25 D
GRA0033001	KA33NR1	OPERATING HANDLE ASSEMBLY	1 C
GRA0159	KA37NR	CONTACT BOX ASSEMBLY-INCL. KA76NR MOVING CONTACT AND TOGGLE ASSEMBLIES, BUT LESS STATIONARY CONTACTS	1 D
GRA0040	KA40NR1	BELL CRANK ASSEMBLY	1 D
CCR010P1	KA48NRS	PLUG-5 CONDUCTOR	1 A
GN3A0000640002	KA64GN3-2	STATIONARY CONTACT ASSEMBLY-NR ABOVE 198799 AND NRV ABOVE 1468 (NOTE: 2 REQUIRED PER UNIT)	2 C
GRA0121002	KA121NR1S	RECEPTACLE-5 CONDUCTOR WITH 5 LEADS, ABOVE 65745	1 C
GRA0121005	KA121NR5S	RECEPTACLE-5 CONDUCTOR WITH 3 LEADS, ABOVE 65745	1 C
HA00227	KA227H900	PARALLEL GROUND CLAMP	1 B
GRA0346003	KA238NR	SUPERSEDED BY KA346NR3 STANDARD BUSHING ASSEMBLY	1 B
GRA0346005	KA344NR1	SUPERSEDED BY KA360NR1 BUSHING ASSEMBLY	1 B
GRA0346003	KA346NR3	BUSHING ASSEMBLY-STD, ABOVE 57218; SUPERSEDES KA238NR	1 B
GRA0346005	KA346NR5	BUSHING ASSEMBLY-17 IN. CREEPAGE, ABOVE 57218; SUPERSEDES KA243NR	1 C
GRA0360001	KA360NR1	BUSHING ASSEMBLY-125 KV BIL, 17 IN. CREEPAGE	1 C
GRA0384	KA384NR	MOVING CONTACT BAR ASSEMBLY-NR ABOVE 304585 AND NRV ABOVE 10142	1 C
GRA0385	KA385NR	SIDE PLATE ASSEMBLY. W/CONTACT ASSEMBLY. -NR ABOVE 304585 AND NRV ABOVE 10142	1 C
GR00326	KA386NR	SUPERSEDED BY KA385NR SIDE PLATE ASSEMBLY	1 C
GRA0700	KA700NR	REPLACEMENT BARCOL MOTOR KIT-INCL. ACTUATOR SPRING, SUPERSEDES KA703NR; NR BELOW 309807 AND NRV BELOW 10436	1 C

Lead Time Code is for Reference Only, contact your ISR for verification of lead times.

A . . . 2 Weeks
 B . . . 4 Weeks
 C . . . 8 Weeks
 D . . . Consult Factory

Catalog Number	Description	Minimum Order Qty	Lead Time Code
TYPE NR, NRV SWITCH			
Greenwood Part No.	Replaces		
GRA0709010	KA709NR10S	5 PIN PLUG KA48NRS, 5 CONDUCTOR WIRED, STANDARD CABLE 10 FT. AVAILABLE TO 35 FT. SPECIFY ADDITIONAL LENGTH OVER 10 FT AS SUFFIX AND ADD .60 FOR EACH ADDED FOOT; EXAMPLE KA709NR35S	1 D
GRA0710010	KA710NR10S	6 PIN CONDUCTOR PLUG, KA98NRS AND STANDARD CABLE 10 FT ADDITIONAL LENGTH OVER 10 FT AS SUFFIX AND ADD .60 FOR EACH ADDED FOOT; EXAMPLE KA710NR35S	1 D
MEA0121010	KA711NR10S	5 PIN PLUG KA48NRS 5 CONDUCTOR WIRED, STANDARD CABLE 10 FT. AVAILABLE TO 35 FT. SPECIFY ADDITIONAL LENGTH OVER 10 FT AS SUFFIX AND ADD .60 FOR EACH ADDED	1 D
GRA0727001	KA727NR1	CONTACT BOX ASSEMBLY-BELOW 198800	1 C
GRA0727002	KA727NR2	CONTACT BOX ASSEMBLY-ABOVE 198799 TO 309899	1 D
KA23980001	KA741NR1S	SUPERSEDED BY KP2398A2 SWITCH ONLY OR KA743NR2 ACTUATOR REPAIR KIT	1 D
KA23980002	KA741NR2S	SUPERSEDED BY KP2398A1 SWITCH ONLY OR KA743NR1 ACTUATOR REPAIR KIT	1 D
GRA0381	KA744NR1	ACTUATOR REPAIR KIT-WITH KA381NR ACTUATOR ASSEMBLY; NR ABOVE 309900 AND NRV ABOVE 10500	1 C
GRA0744002	KA744NR2	ACTUATOR REPAIR KIT-WITH HOLDING SWITCH, KA381NR ACTUATOR ASSEMBLY; MR ABOVE 309900 AND NRV ABOVE 10500"	1 D
GRA0364	KA745NR	S.P.D.T. AUXILIARY SWITCH KIT-NR ABOVE 309900 AND NRV 10500	1 C
GR00038001	KP38NR1	VENTILATING SCREEN PLUG	1 D
GS00040	KP40GH	MOVING CONTACT TOGGLE SPRING	1 C
GR00275	KP50NR	SUPERSEDED BY KP2000A3, OIL SEAL	1 C
KA21030012	KP68NR	SUPERSEDED BY KP2103A12 HEAD GASKET	1 C
GR00233	KP83NR900	SUPERSEDED BY KP233NR BUSHING CLAMP	1 C
KA31230011	KP98NR	SUPERSEDED BY KP3123A11, PIN	1 C
GR00107	KP107NR	SHOCK ABSORBER PAD	1 C
GR00110	KP110NR	SPLIT ALUMINUM CLAMPING RING OR GASKET	50 C
KA20900040	KP111NR	SUPERSEDED BY KP2090A40 LOWER BUSHING GASKET	1 C
GR00114	KP114NR	TANK BOTTOM LINER (POLYPROPYLENE)	1 C
GR00115	KP115NR	TANK WALL LINER (FIBER)	1 C
GS00118001	KP118GH1	BUSHING OIL SEAL	1 D
GR00120	KP120NR	PIN, RETAINER AND SPRING ANCHOR	1 D
GR00121	KP121NR	ACTUATOR COVER GASKET	1 C
GR00302	KP166NR	SUPERSEDED BY KP221NR AND KP302NR CLOSING SPRING	1 C
6A00471702	KP172NR2	CONTROL RATING PLATE-DECAL	1 D
GR00323	KP182NR	ACTUATOR COVER-ABOVE 18197 TO 309899 OBSOLETE SUPERCEDED BY KP323NR	1 C
GR00214	KP214NR	CONTACT RETAINER	1 D
GR00233	KP233NR	BUSHING CLAMP-SSL, 3 REQUIRED PER BUSHING	3 B
GR00256	KP256NR	CONTACT ROLLER	1 D
GR00257	KP257NR	BUSHING LEAD	1 C
GR00266	KP266NR	TERMINAL STRIP-ABOVE 65745	1 D
GR00275	KP275NR	OIL SEAL-125 KV BIL BUSHING	1 C
GR00289	KP289NR	TANK WALL LINER-125 KV BIL (POLYPROPYLENE)	1 C
GR00330	KP293NR2	HEAD CASTING-194324 AND ABOVE	1 D
SI01057	KP295NR	CAUTION PLATE	1 C
GR00296	KP296NR	OPERATING HANDLE SPRING	1 C

Lead Time Code is for Reference Only, contact your ISR for verification of lead times.
 A 2 Weeks
 B 4 Weeks
 C 8 Weeks
 D Consult Factory

Effective February 2016

Catalog Number	Description	Minimum Order Qty	Lead Time Code
TYPE NR, NRV SWITCH			
Greenwood Part No.	Replaces		
GR00302	KP302NR	CLOSING SPRING-SUPERSEDES KP166NR AND KP22NR	1 C
GR00320	KP320NR	MOTOR-120 VAC, NR ABOVE 309900 AND NRV ABOVE 10500	1 C
GR00323	KP323NR	ACTUATOR COVER-ABOVE 18197 TO 309899	1 C
H000472	KP421H900	SUPERSEDED BY KP472H LIFTING STRAP	1 C
H000472	KP472H	LIFTING STRAP-SSL	1 C
KA20000003	KP2000A3	OIL SEAL-SUPERSEDES KP50NR	50 A
KA20000006	KP2000A6	GASKET-O-RING	50 C
KA20200003	KP2020A3	ELASTIC STOP NUT-1/4	1 C
KA2090A40	KP2090A40	BUSHING GASKET-LOWER	25 A
KA2090A43	KP2090A43	GASKET	1 C
KA20900050	KP2090A50	BUSHING TERMINAL GASKET - UPPER BELOW S/N 213269	1 B
KA2090A99	KP2090A99	BUSHING TERMINAL GASKET - UPPER ABOVE S/N 213270	1 C
KA2103A13	KP2103A12	HEAD GASKET - SUPERSEDES KP68NR	1 B
KA23980001	KP2398A1	SELECTOR SWITCH ABOVE S/N 309900	1 C
KA23980002	KP2398A2	HOLDING SWITCH ONLY	1 C
KA30360019	KP3036A1	SHAFT INSERT- SUPERSEDES KP116GS	1 C
KA30540002	KP3052A3	PIN-FOR ATTACHING KP78NR SWITCH TO LEVER AND SHAFT	1 D
KA30540002	KP3054A2	LATCH LEVER PIN OR SHAFT - SUPERSEDES KP15GS	1 D
KA31230011	KP3123A11	GROOVE PIN, SUPERSEDES KP98NR	1 D

Lead Time Code is for Reference Only, contact your ISR for verification of lead times.

- A . . . 2 Weeks
- B . . . 4 Weeks
- C . . . 8 Weeks
- D . . . Consult Factory

Eaton
 1000 Eaton Boulevard
 Cleveland, OH 44122
 United States
 Eaton.com

Eaton's Cooper Power Systems Division
 2300 Badger Drive
 Waukesha, WI 53188
 United States
 Eaton.com/cooperpowerseries

© 2016 Eaton
 All Rights Reserved
 Printed in USA
 Publication No. TD230002EN

Eaton is a registered trademark.
 All other trademarks are property
 of their respective owners.

For Eaton's Cooper Power series product
 information call 1-877-277-4636 or visit:
www.eaton.com/cooperpowerseries.