Weatherproof telephone ResistTel

Comforable telephone for rough environmental conditions

Overview

ResistTel stands for: telephony under rough environmental conditions with the highest degree of safety in industrial areas.

Our telephone is resistant to seawater as well as alkali, acids and lubricants. The housing made of special compression-moulded material is impact-resistant.

The V4A stainless steel keypad withstands high stresses and protects the inner parts of the telephone. The steel-armoured handset cord is designed for high tensile strain.

Its alphanumeric display allows for a clear reading. Moreover, the telephone offers all the amenities that are already supplied as standard in the office communication sector.

A number of accessories and components especially certified for potentially explosive areas even enhance the telephone's functionality.

Features

- Locking function with PIN
- Hands-free operation
- Temperature range -25 °C to +60 °C
- Handset volume adjustable from 0 dB to +12 dB, 7-step
- Telephone book
- V4A keypad
- Display
- Protection class IP 66 according to EN 60529
- Different housing colours



Eator FHF Funke + Huster Fernsig GmbH Gewerbeallee 15-19 D-45478 Mülheim an der Ruhr

Telephone +49-208-82 68-0 Fax +49-208-82 68-286 http://www.eaton.com/telephones

© 2022 Eaton All Rights Reserved Printed in UK Publication No.DSFH0007/B January 2022

Eaton is a registered trademark. All other trademarks are property

of their respective owners




Follow us on social media to get the latest product and support information.






CROUSE-HINDS

Technical data			
Supply voltage	24 VDC to 66 VDC		
Supply current	15 mA to 100 mA		
Ringer voltage	24 VAC to 90 VAC (at 2154 Hz ringing frequency) 30 VAC to 90 VAC (at 16.654 Hz ringing frequency)		
Ringer impedance	Greater than 6.0 K Ω at 25 Hz and 2490 VAC. Greater than 4.0 K Ω at 50 Hz and 2490 VAC		
Inquiry key	Flash function may be set from 40 ms to 399 ms		
Dialling procedure	PD-DTMF operation to be set in the menu. PD operation where the pulse/pause ratio can be set to 1.5:1 or 2:1 in the menu		
Bell-Shunt	Connection for external secondary ringer		
Connection terminals	Up to 4 mm² rigid, Up to 2.5 mm² flexible		
Housing			
Material Height x width x depth Weight	Glass fibre reinforced polyester Approx. 266 mm x 227 mm x 135 mm Approx. 5.5 kg		
Display	Two-line alphanumeric diplay with pictograms Visual field approx. 78 mm x 26 mm		
Keypad	Metal keypad with ice protection 21 keys with ABC lettering for name entries		
Handset			
Stabilization bracket	Integrated, adjustable stabilization bracket		
Handset cord	Stainless steel armoured cord		
Earpiece	Dynamic capsule with stray field coil for inductive coupling of hearing aids		
Mouthpiece	Electret microphone		
Noise suppression	Greater than 3 dB due to integrated horn mouth		
Stabilization bracket	Integrated, adjustable stabilization bracket		
Handset cord	Stainless steel armoured cord		
Earpiece	Dynamic capsule with stray field coil for inductive coupling of hearing aids		
Mouthpiece	Electret microphone		
Noise suppression	Greater than 3 dB due to integrated horn mouth		
Environmental conditions			
Protection class	IP 66 according to EN60529		
Impact protection	IK 09 according to EN50102		
Operating temperature	-25 °C to +60 °C		
Storage temperature	-25 °C to +70 °C		
Further characteristics			
Optical call indication	Display screen (((🌲)))		
Ringing volume	Approx. 95 dB(A) in 1 m distance		
Ring tones	10 sounds available		
Listening by loudspeaker	Maximum volume approx. 70 dB in 1 m distance		
Handsfree operation	Maximum volume approx. 70 dB in 1 m distance		
Amplified listening in receiver	Receiver volume may be set from 0 dB(A) to +12 dB(A), in 7 steps		
Menu guide	Multilingual		
Telephone book	Max. 50 items (names and phone numbers)		







Ordering requirements


Туре	Designation	Mode	Article number
ResistTel	Weatherproof telephone	Black	FHF 112 643 01
ResistTel	Weatherproof telephone	Red	FHF 112 643 01 02
ResistTel	Weatherproof telephone ZB	Black	FHF 112 643 02
ResistTel	Weatherproof telephone ZB	Red	FHF 112 643 02 02
Accessories			
	Additional earpiece		FHF 112 861 03
	Headset		FHF 112 643 04
	Secondary sounder		FHF 211 101 05
	Telephone hood model 404	Galvanized steel, yellow	FHF 118 901 01
	Telephone hood model 404	V4A stainless steel	FHF 118 901 11
	Telephone hood model 404	Synthetic material, orange	FHF 118 901 12
	Telephone hood model 404	Synthetic material, yellow	FHF 118 901 13
	Telephone hood model 404	Galvanized steel, red	FHF 118 901 14
	Telephone hood model 404	Synthetic material, red	FHF 118 901 15
	Telephone hood model 404	GRP, yellow	FHF 118 901 22
	Telephone hood model 404	GRP, orange	FHF 118 901 23
	Floor mounting console for Model 404	Yellow	FHF 118 901 03
	TWIN LED	24 VDC	FHF 118 833*
	TWIN LED	100253VAC	FHF 118 827*

transparent	01
red	02
amber	03
green	04
blue	05

*The full article number for the TWIN is made up by appending the colour code to the article numbers given beside.

Accessories

headset



secondary sounder











