



- 1 - EPCT TOUCHSCREEN
  - 2 - EXTERNAL USB PORT
  - 3 - SOURCE 1 MAIN ISOLATING SWITCH POWER SWITCH
  - 4 - SOURCE 1 CIRCUIT BREAKER POWER SWITCH
  - 5 - SOURCE 2 MAIN ISOLATING SWITCH POWER SWITCH
  - 6 - SOURCE 2 CIRCUIT BREAKER POWER SWITCH
  - 7 - START PUSHBUTTON
  - 8 - STOP PUSHBUTTON
  - 9 - MSH (EMERGENCY START HANDLE)
  - 10 - RECOMMENDED CABLE ACCESS (BOTTOM ONLY)
- NOTES:  
 1 - DIMENSIONS: in [mm]  
 2 - ALL ENCLOSURES FINISHED IN RED  
 3 - STANDARD ENCLOSURE: TYPE (NEMA) 2

Motor HP	Line voltage	Withstand rating			Approximate weight Lbs. (Kg)
		Standard	Intermediate	High	
200 - 250	200 - 208V	100,000	N/A	N/A	990 (448)
250 - 300	220 - 240V				
350 - 500	380 - 415V				
450 - 600	440 - 480V				
550 - 700	550 - 600V	25,000			