

703 contact transmitter



The multipurpose transmitter that keeps you in control

Behind the clean, contemporary looks of the 703 lies a highly sophisticated remote transmitter offering a wide variety of applications.

Capable of transmitting signals from up to four locations, it's ideal for communicating with a central control point. And whether you need it to monitor lights, doors, pumps, machines, plant or farm machinery or other equipment, you'll find our 868 MHz narrow-band ensures secure, reliable operation.

Moreover, it can work with vibration sensors to detect attacks on doors, windows, walls and safes. Likewise, by using it with a keyswitch it can act as a simple alarm system.

Powered by either 12vDC or batteries, the 703 can just as easily be used for outbuildings with no electricity as indoor locations.

However, you use it though, you can expect the 703 to perform to the highest standards to keep you in control.

At a glance...

- Reliable, secure Scantronic 868 MHz narrow-band radio operation
- Programmable supervision signals for extra protection
- Programmable options to cater for a wide variety of uses
- Can function as a simple alarm system + transmitter
- Integral analyser for connection of external inertia sensors
- Accepts up to four signals from a wide variety of monitoring triggers
- 12vDC and/or 2 x AA alkaline battery powered

Product specification

Channels	1, 2 or 4 (mode selectable)
Inputs	2 x DP or 4 x SP; keyswitch option; entry/exit timer option; inertia sensor analyser option
Option programming	Via internal push button switches and display
Programming display	Two by seven-segment LED. Visible with case open
Compliance	Product complies with: EN 50131-3. Security Grade 2. Environmental grade II
Radio section	Operating frequency 868.6625MHz at 20kHz bandwidth. CE tested to I-ETS 300 220
Transmitter range	Up to 1000m free space
Supervision interval	Programmable 4 or 29 minutes
Power	12vDC and/or Quiescent current 15mA
Battery (optional)	2 x AA 1.5V Alkaline
Battery life	2 Years (30 days in Modes 7 and 8)
Dimensions	152 x 104 x 30 mm (H x W x D)
Weight	0.206 kg (not including batteries)

Compatible products

Scantronic 9960rEUR-08 & 16 RFX	receiver interfaces
Scantronic Homelink 55	24 zone radio alarm panel
Scantronic Homelink 75	32 zone radio alarm system
Scantronic 762rEUR-00	2 channel receiver
Scantronic 768rEUR-00	8 - 32 channel receiver
Scantronic EXP-R10	10 zone radio expander
Scantronic EXP-R30	30 zone radio expander
i-on16	16 zone control panel
i-on30EX	30 zone control panel
i-on40	40 zone control panel
i-on50EX	50 zone control panel
i-on160EX	160 zone control panel
Menvier30	30 zone control panel
Menvier40	40 zone control panel
Menvier100	100 zone control panel
Menvier300	300 zone control panel
Menvier MRNODE	receiver interface
Multibus	1000 zone control panel
792rEUR-00	indoor 1/4 wave (Supplied with 703r)
794rEUR-00	indoor/outdoor co-linear 8 x 1/2 wave
797rEUR-00	indoor/outdoor 1/2 wave

Eaton
Electrical Sector EMEA
Route de la Longeraie 7
1110 Morges, Switzerland

Eaton
Security House,
Vantage Point Business Village,
Mitcheldean, Gloucestershire
GL17 0SX

Tel: +44 (0)1594 545 400
Fax: +44 (0)1594 545 401
Email: securitysales@eaton.com
Web: www.touchpoint-online.com