

i-on Style - Hybrid intruder alarm panel



An integrated panel solution with large colour TFT display and low profile keypad. Built-in ethernet/IP communications provides for flexible and secure communication options and supports Cloud/App connectivity.

Built with cyber security in its DNA the i-on Style is Eaton SecureConnect™ Cloud and App enabled

Multiple communication options

Built-in Ethernet port and optional PSTN or GSM allow you to tailor installations to the properties needs.

Eaton SecureConnect™ Cloud and App

Control and monitor your panel through the cloud 24/7 anytime anywhere across multiple locations. Provide your customers with a secure App for convenient control of their system ensuring peace of mind.

Simple visual verification

Connect Eaton security cameras to the i-on Style panel to provide an additional layer of security. Capturing images locally on an SD card and view through App or email.

At a glance:

- 40 radio zones with additional 4 wired zones
- 30 radio outputs
- Plug on GSM modul to give tri-path communications
- SIA/IP ARC communications
- Social care features
- Built in speech dialer
- Ethernet / web server / virtual
- Visual verification
- Perimeter zone functionality
- SMS control
- Class leading Scantronic radio
- Email notifications
- EN50131 Grade 2: Independently approved
- Available in kit format:
STYLE-EU-KIT1
STYLE-EU-KIT2

* Excludes UK



Powering Business Worldwide

Product specification

Feature	Description
Compliance	EN50131-1:2006 + A1:2009 Grade 2 and environmental class II, EN50131-3:2009, EN50131-6:2008, BS8243:2010, PD6662:2017
Zones	40 radio and 4 wired on board, all fully programmable
Partitions	4 independent partitions each with a part set or full set and three part sets
Users	40 user codes, 4 digit PIN number, proximity, remote control, radio panic button, medical and social pendants
Event log	1000 events; 750 mandatory events and 250 non-mandatory
Outputs	2 x programmable relay outputs 2 x 500mA open collector programmable outputs 30 radio outputs
Internal sounder	One independently controlled integrated sounder 4 internal radio sounders
External sirens	4 external radio sirens
Remote communications	SIA IP via built in Ethernet port FF/CID/SIA via built in PSTN digital communicator Email and images via built in Ethernet port Footprint for connection of i-gsm03
Visual verification	Up to 4 IP cameras
Power supply	Conforms to EN50131-6:2008 Type A power supply, rated power output 1.5A. 600mA is available for auxiliary power
Configuration options	Configurable via the cloud
Battery	Up to 2 x 7.4V, 2500mAh, Li-Polymer
Dimensions	287mm (h) x 203mm (w) x 52mm (d)

Compatible products

Product Code	Description
i-GSM03	Plug on GSM communicator
SDR-REXT-G2	External radio sounder
SDR-WEXT-G2	External wired sounder grade 2
SDR-RINT	Internal radio sounder
XCELR	Radio PIR
XCELRPT	Radio pet tolerant PIR
734rEUR-00(06)	Radio door contact white (brown)
738rEUR-00(04)	Radio shock sensor white (brown)
739rEUR-00	Radio break glass detector
DET-RSMOKE	Radio smoke detector
DET-RDCS	Radio shock detector and magnet
DET-RARB	Radio assistance required button
DET-REXT-PIR30	Perimeter zone PIR
DET-RDT-G2	Radio dual tech detector

Product Code	Description
DET-RDTPT-G2	Radio pet tolerant dual tech detector
CAM-EXT-00	External IP camera
CAM-INT-00	Internal IP camera
i-RK01	Radio keypad
701rEUR-50/60	Long and short range pendant transmitter
702rEUR-00	Watch/pendant transmitter
710rEUR-00	Radio panic button
726rEUR-50	Radio panic button (long range)
706rEUR-00	Radio lone worker button
762rEUR-00	Radio receiver
FOB-2W-4-B	Two way radio FOB
i-FB01	Remote control
PROXTAGPK5	Proximity tags

Eaton
Electrical Sector EMEA
Route de la Longeraie 7
1110 Morges, Switzerland

Eaton
Eaton Electrical Products Limited
Security House,
Vantage Point Business Village,
Mitcheldean, Gloucestershire
GL17 0SZ

Contact us:
Eaton Electrical Products Limited

Tel: +44 (0)1594 545 400
Fax: +44 (0)1594 545 401
Email: securitysales@eaton.com
Web: www.touchpoint-online.com