

i-on40H - Hybrid intruder alarm panel



The i-on40H is a 40-zone hybrid (wireless and/or wired) control panel, which is expandable to 80 zones. It is ideal for installers who prefer a radio or hybrid solution and is highly versatile, being both backward and forward compatible.

Built with cyber security in its DNA the i-on40H is Eaton SecureConnect™ Cloud and App enabled

Multiple communication options

Built-in Ethernet port and optional PSTN or GSM allow you to tailor installations to the properties needs.

Eaton SecureConnect™ Cloud and App

Control and monitor your panel through the cloud 24/7 anytime anywhere across multiple locations. Provide your customers with a secure App for convenient control of their system ensuring peace of mind.

Simple visual verification

Connect Eaton security cameras to the i-on40H panel to provide an additional layer of security. Capturing images locally on an SD card and view through App or email.

At a glance:

- 30 radio and 10 wired zones expandable to 80
- Hybrid expansion using EXP-R10/R30/W10/PSU
- Ethernet / web server / virtual
- Visual verification
- Perimeter zone functionality
- SMS control
- Plug on ARC/Speech/SMS for PSTN/GSM
- Class leading Scantronic radio
- Email notifications
- EN50131 Grade 2: Independently approved



Powering Business Worldwide

Product specification

Compliance	EN50131-1:2006 + A1:2009 Grade 2 and environmental class II, EN50131-3:2009, EN50131-6:2008, BS8243:2010, PD6662:2017
Zones	30 Radio and 10 wired on board, expandable to 80, all fully programmable
Partitions	4 independent partitions each with a part set or full set and three part sets
Users	50 user codes, 4 digit PIN number, proximity, remote control or radio panic button
Event log	1000 events; 750 mandatory events and 250 non-mandatory
Outputs	One programmable relay outputs One 500mA open collector programmable outputs 12 low-current outputs for plug-by communicators 10 radio outputs
Bus devices	Accepts up to 20 bus devices (keypads, expanders and power supplies)
Internal sounder	One independently controlled 16 Ω speaker 4 internal radio sounders
External sirens	Dedicated siren and strobe open collector outputs 4 external radio sirens
Remote communications	SIA IP via built in Ethernet port Email and images via built in Ethernet port Footprint for connection of a range of alarm communications modules as described below
Visual verification	Up to 4 IP cameras
Power supply	Conforms to EN50131-6:2008 Type A power supply, rated power output 1.0A. 650mA is available for auxiliary power
Configurations options	Configurable via the cloud
Battery	Accepts a 12v standby battery up to 7Ah rechargeable lead acid, gel type
Dimensions	End station: 384 x 245 x 94mm
Weight	End station: 2.2kg
Temperature range	Environmental class II. Tested -10°C to 55°C @ 93% RH

Compatible products

i-on40H	40 zone hybrid panel end station
i-KP01, KEY-K01, KEY-KP01, KEY-KPZ01	Wired keypad
KEY-RKPZ-KIT	Two way radio keypad and base station
KEY-EP (External Reader)	External Proximity reader
i-RK01	Wireless keypad
i-FB01	Remote control
EXP-W10	Wired CC 10 zone expander
EXP-PSU	Smart power supply
EXP-R10	Radio 10 zone expander
EXP-R30	Radio 30 zone expander
i-DIG02	Digital communicator
i-SD02	Plug-in SD/comms module
ADSL01	ADSL filter
i-GSM02	GSM dialler
SDR-REXT-G2	External wireless sounder
SDR-WEXT-G2	External wired sounder grade 2
SDR-WEXT-G3	External wired sounder grade 3
SDR-RINT	Internal wireless sounder

*Both alarms will display as a HUA on the panel

XCELR	Radio PIR
XCELRPT	Radio pet tolerant PIR
XCELW	Wired PIR
XCELWPT	Wired pet tolerant PIR
734rEUR-00 (06)	Radio door contact white (brow)
DET-RSMOKE	Radio smoke detector
738rEUR-00 (04)	Radio shock sensor white (brown)
739rEUR-00	Radio break glass detector
710rEUR-00	Radio panic button
09040UK-00	Extension speaker
726rEUR-50	Radio panic button (long range)
DET-RDCS	Radio shock detector and magnetic
DET-RARB	Radio assistance required button
DET-RDTPT-G2	Radio pet tolerant dual tech detector
DET-RDT-G2	Radio dual tech detector
703rEUR-00	Four channel radio transmitter
706rEUR-00	Radio HUA and lone worker device *
FOB-2W-4B	Two way radio fob
762rEUR-00	Radio receiver
768rEUR-50	Radio receiver
WDC02	Wired door contact
PROXTAGPK5	Proximity tags

Eaton
Electrical Sector EMEA
Route de la Longeraie 7
1110 Morges, Switzerland

Eaton
Security House,
Vantage Point Business Village,
Mitcheldean, Gloucestershire
GL17 0SZ

Tel: +44 (0)1594 545 400
Fax: +44 (0)1594 545 401
Email: securitysales@eaton.com
Web: www.touchpoint-online.com