

734 Radio door contact



Grade2, radio door contact with configurable second radio channel.

For use with HUA (PA), door contact, key switch or other voltage free device. Compact unit with replaceable CR2 lithium battery.

At a glance...

- Choice of finishes for installation on wood or pvc
- Independently certified to EN50131
- Flexible installation choices
- Compatible with EXP-R10 and EXP-R30

Product specification

	734rEUR-00	734rEUR-01
Detection coverage	10mm	10mm
Second zone	Yes	Yes
Wired input type	CC	FSL
Wireless frequency	868.6625 MHz	868.6625 MHz
Batteries	3V CR2	3V CR2
Security Grade	2	2
Environmental class	11 (tested to -10°C + 55°C)	11 (tested to -10°C + 55°C)
Dimensions	(W x H x D) 33mm x 88mm x 27mm	(W x H x D) 33mm x 88mm x 27mm

Compatible products

762	2 channel narrow band receiver
768 & 769	8-32 channel narrow band receivers
EXP-R10	10 zone radio expander
EXP-R30	30 zone radio expander
i-on16/ EUR	16 zone control panel
i-on30EX/ EXEUR	30 zone control panel
i-on40/ EUR	40 zone control panel
i-on50EX/ EXEUR	50 zone control panel
i-on160EX/ EXEUR	160 zone control panel
Multibus	1000 zone control panel
Menvier30KPZ	30 zone control panel
Menvier40KPZ	40 zone control panel
Menvier100KPZ	100 zone control panel
Menvier300KPZ	300 zone control panel
Eaton Legacy 868MHz panels	panel end station