

# Eaton Single-sliding and Dual-sliding End of Row Doors

End of row doors create more efficient aisle containment by blocking an obvious air escape route and opportunity for air re-circulation and air mixing. This allows you to set a higher overall temperature within the data center thus saving energy and extending hardware life.

## Features and benefits:

- Automatic close and hold open feature comes standard
- Fully transparent, impact resistant UL94, V-0 windows
- Height options: 90" H and 96" H
- Single-sliding doors are left and right hand sliding capable (field reversible)
- Ease of installation reduces downtime and disruption in the data center
- Ceiling mount provisions for threaded rod install
- Sliding doors do not interfere with open aisles

## Specifications:

- Door material: sheet steel
- Window insert material: fully transparent, UL 94 V-0 flame rated polycarbonate
- Color options: Black, NuGrey and Eaton White



Dual-sliding End of Row Doors with Eaton's Paramount Enclosures and Horizontal Ceiling Containment.



Eaton's Single-sliding End of Row Door.



*Powering Business Worldwide*

## EATON SLIDING END OF ROW DOORS

Item Number	Type	Color Options	Weight (lbs.)	Height (in.)	Width (in.)	Depth (in.)	Door Opening Height (in.)	Max Door Opening Width (in.)	Window Opening H x W (in.)
EORDSS9036	Single-sliding EORD	Black, NuGrey, or Eaton White	205	90	36	6.1	84.7	35.2	20 x 29.8
EORDSS9636	Single-sliding EORD	Black, NuGrey, or Eaton White	215	96	36	6.1	84.7	35.2	20 x 29.8
EORDDD9048	Dual-sliding EORD	Black, NuGrey, or Eaton White	250	90	48	6.1	84.7	46.4	14 x 29.8
EORDDD9648	Dual-sliding EORD	Black, NuGrey, or Eaton White	265	96	48	6.1	84.7	46.4	14 x 29.8

## OPTIONAL MOUNTING BRACKETS

Item Number	Type	Color Options	Qty.	Notes
SCCI	Ceiling Mounting Brackets	Black, NuGrey, or Eaton White	Single	Order (2) for each EoRD that will be ceiling-mounted and (1) for each End of Row Panel **threaded rod not provided

## OPTIONAL END OF ROW PANELS

Item Number	Type	Color Options	Weight (lbs.)	Height (in.)	Width (in.)
EOR2P9006	EORD Panel	Black, NuGrey, or Eaton White	15	90	6
EOR2P9009	EORD Panel	Black, NuGrey, or Eaton White	19	90	9
EOR2P9012	EORD Panel	Black, NuGrey, or Eaton White	24	90	12
EOR2P9024	EORD Panel	Black, NuGrey, or Eaton White	41	90	24
EOR2P9606	EORD Panel	Black, NuGrey, or Eaton White	16	96	6
EOR2P9609	EORD Panel	Black, NuGrey, or Eaton White	21	96	9
EOR2P9612	EORD Panel	Black, NuGrey, or Eaton White	25	96	12
EOR2P9624	EORD Panel	Black, NuGrey, or Eaton White	43	96	24

To contact an Eaton® salesperson or local distributor, please visit

[www.eaton.com/wrightline](http://www.eaton.com/wrightline)

or call 800-225-7348

**Eaton**  
1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
Eaton.com

© 2017 Eaton  
All Rights Reserved  
Printed in USA  
Publication No. SA301022EN  
February 2017

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

