

RS Enclosure technical specifications

Catalog number	Application	H (U) x W (mm) x D (mm)*	Configuration	Color
Server				
RSVHHWC	Server	H = 42, 45, 48 or 52 W = 6 for 600 mm; 8 for 800 mm D = 0 for 1000 mm; 1 for 1100 mm; 2 for 1200 mm C = B for black; W for white	Frame, rails (flush), locking sides, casters, top, full front door with swing handle, split rear doors with swing handle; PDU mounting brackets	Black or white
RSVNSHHWC	Server – no sides	H = 42, 45, 48 or 52 W = 6 for 600 mm; 8 for 800 mm D = 0 for 1000 mm; 1 for 1100 mm; 2 for 1200 mm C = B for black; W for white	Frame, rails (flush), casters, top, full front door with swing handle, split rear doors with swing handle; PDU mounting brackets	Black or white
Networking				
RSNHHWC	Networking	H = 42, 45, 48 or 52 W = 6 for 600 mm; 8 for 800 mm D = 0 for 1000 mm; 1 for 1100 mm; 2 for 1200 mm C = B for black; W for white	Frame, rails (recessed to accommodate cable management), vertical cable managers with fingers – front and rear; locking sides, casters, top, full front door with swing handle, split rear door with swing handle; PDU mounting brackets	Black or white
Colocation				
RSCHHWDC	Colocation	H = 42, 45, 48 or 52 W = 6 for 600 mm; 8 for 800 mm D = 0 for 1000 mm; 1 for 1100 mm; 2 for 1200 mm C = B for black; W for white	Frame, rails (flush mount on front), locking sides, casters, top, full front door with combo lock, split rear door with combo lock; PDU mounting brackets	Black or white
Key accessories				
Air dams				
RSAIRD600HH	For 600 mm enclosures	HH = 42, 45, 48 or 52	Air dam flex gasketing kit	N/A
RSAIRD800HH	For 800 mm enclosures	HH = 42, 45, 48 or 52; C = B for black; W for white	Air dam flex gasketing with vertical blanking panels and grommets	Black or white
PDU brackets				
RSPDUMTGB	Standard PDU bracket	For all enclosures	Additional PDU brackets for mounting on second side or for half height rack PDUs	Black
RSPDU9MTGC	Standard PDU mounting	For 800 mm wide enclosures only	Rack PDU brackets to install behind rear rails on 800 mm wide enclosures; accommodates two rack PDUs facing rear	Black or white
Vertical cable managers				
RSCMFHHU	For all enclosures	Vertical cable management fingers HH = 42, 45, 48, 52	Kit of fingers for vertical cable management; fingers attach to square hole rails; may be used on 600 mm or 800 mm enclosures	
RCVCMHBB	For 800 mm enclosures	High density cable manager HH = 42, 45, 48, 52	High density cable manager with two rows of fingers and a cable management door; mounting brackets; for use with 800 mm enclosures/square hole rails	Black
Anchor brackets				
RSANCC	For all enclosures	Anchor brackets	Anchor brackets for floor anchorage; meets IBC seismic requirements; refer to seismic analysis for loading and anchorage specification	Black or white

*This column does not list actual part numbers but it does show how to configure a part number.

RS Enclosure configurations support Eaton's industry-leading power management products and accessories, such as:

- The ePDU® third-generation (G3) platform that provides best-in-class power management capabilities for data centers and colocation facilities
- ENERGY STAR® qualified 9PX UPSs, which maximize the availability of IT systems
- Intelligent Power Manager™ software that enables remote monitoring, management and control of operators' power infrastructure from a single interface

For more information, visit Eaton.com/RS



Follow us on social media to get the latest product and support information.



Eaton, ePDU and Intelligent Power Manager are registered trademarks.

All other trademarks are property of their respective owners.