



FEATURES

- Available for tubing O.D. ranges of 3/8" to 2 1/2"
- One piece design greatly reduces installation time
- No tools required to install; easily snaps into channel or 3/8" all threaded rod (ATR)
- Non-metallic design eliminates metal-to-metal contact; preventing galvanic corrosion
- Meets UL2043 requirements for plenum rating and UL94 HB flame rating
- Working temperature range of -40°F to +275°F
- BPIC and BPSC Kwik-Clips can be used with insulation, maintaining an unbroken barrier seal and eliminating sweating
- BPRC Kwik-Clips can be snapped onto 3/8" all threaded rod at any location, making it flexible to use on the job-site



Channel Mount Clips
BPIC Series
BPSC Series



Rod Mount Clips
BPRC Series



Powering Business Worldwide

UPC/Part #	Catalog #	Copper/PEX/CTS CPVC Pipe Size	O.D. Tubing	Sch. 40 Pipe	Box Quantity	Inner Bag Quantity	Wt./Bag
78205153205	BPIC062	½"	⅝"	–	500	25	0.725
78205153206	BPIC075	⅝"	¾"	–	500	25	0.725
78205153207	BPIC087	¾"	⅞"	½"	500	25	0.750
78205153208	BPIC100	–	1"	¾"	500	25	0.800
78205153209	BPIC112	1"	1 ⅛"	–	500	25	0.825
78205154008	BPIC125	–	1 ¼"	1"	500	25	0.850
78205153210	BPIC137	1 ¼"	1 ⅜"	–	250	25	0.875
78205154009	BPIC150	–	1 ½"	–	300	25	0.950
78205153211	BPIC162	1 ½"	1 ⅝"	–	300	25	1.000
78205153212	BPIC200	–	2"	–	300	25	1.050
78205153213	BPIC212	2"	2 ⅛"	–	200	25	1.100



BPIC Series

UPC/Part #	Catalog #	Copper/PEX/CTS CPVC Pipe Size	O.D. Tubing	Sch. 40 Pipe	Box Quantity	Inner Bag Quantity	Wt./Bag
78205153214	BPSC037	¼"	⅜"	–	500	25	0.575
78205153215	BPSC050	⅜"	½"	–	500	25	0.650
78205153216	BPSC062	½"	⅝"	–	500	25	0.700
78205153217	BPSC075	⅝"	¾"	–	500	25	0.825
78205153218	BPSC087	¾"	⅞"	½"	500	25	0.975
78205153219	BPSC112	1"	1 ⅛"	–	500	25	1.125
78205153220	BPSC137	1 ¼"	1 ⅜"	–	250	25	1.250
78205153221	BPSC162	1 ½"	1 ⅝"	–	250	25	1.375



BPSC Series

UPC/Part #	Catalog #	Copper/PEX/CTS CPVC Pipe Size	O.D. Tubing	Sch. 40 Pipe	Box Quantity	Inner Bag Quantity	Wt./Bag
78205153216	BPRC062	½"	⅝"	–	500	25	0.300
78205153223	BPRC075	⅝"	¾"	–	500	25	0.325
78205153224	BPRC087	¾"	⅞"	½"	500	25	0.350
78205153225	BPRC100	–	1"	¾"	500	25	0.375
78205153226	BPRC112	1"	1 ⅛"	–	500	25	0.400
78205154010	BPRC125	–	1 ¼"	1"	500	25	0.425
78205153227	BPRC137	1 ¼"	1 ⅜"	–	500	25	0.450
78205154011	BPRC150	–	1 ½"	–	500	25	0.525
78205153228	BPRC162	1 ½"	1 ⅝"	–	500	25	0.575
78205153229	BPRC200	–	2"	–	500	25	0.625
78205153230	BPRC212	2"	2 ⅛"	–	500	25	0.675



BPRC Series



1. Insert in channel.



2. Twist into place.



3. Lay tubing/pipe into clip.



4. Snap clip closed.