

Vickers® SystemStak™ Valves




Pressure Operated Check Valves

DGPC-01-**-51
DGPC-06-**-51

Model Code

DG PC - 01 - * * - 51



1 Model Series

DG - Directional control manifold or subplate mounted

3 Size

01 - 1/8 inch

5 Check Valve Cracking Pressure

(Omit for 30 PSIG standard)


2 Model Series

PC - Pressure operated check module

4 Check Valve in Cylinder Port


A - Cylinder port A
B - Cylinder port B

6 Design



Model Code

DG PC - 06 - * * - 51



1 Model Series DG - Directional control manifold or subplate mounted	3 Port Size 06 - 3/4 inch	5 Check Valve Cracking Pressure (Omit for standard 30 PSIG)
2 Model Series PC - Pressure operated check module	4 Check Valve Location A - Cylinder port 'A' B - Cylinder port 'B'	6 Design

