

Extra duty while-in-use weather protective covers

Product description


- 1-Gang extra duty, self-closing
- 2-Gang extra duty, self-closing

Features

- Meets 2014 NEC® 406.9 (B)(1) extra duty requirements for any application
- Rugged UV-resistant polycarbonate cover and back protects devices without cracking or breaking and is non-corrosive and non-conductive
- Self-closing cover
- Box inserts accommodate decorator devices, duplex receptacles and a variety of single receptacle sizes and toggle switches
- 1-Gang box includes 3 inserts for 16 different configurations
- 2-Gang box includes 4 inserts for over 60 different configurations
- Cord cover opening fits #12 AWG or lighter cord
- Includes pre-mounted gasket



Single gang inserts



WIU-2



2-Gang inserts

Extra duty while-in-use weather protective covers



Description	Gang	Color	Catalog no.	
Horizontal mount	1	GY	□ WIU-1HX	•
Horizontal mount	1	W	□ WIU-1WHX	•
Vertical mount	1	GY	□ WIU-1VX	•
Vertical mount	1	W	□ WIU-1VWX	•
Horizontal/vertical mount	2	GY	□ WIU-2X	•
Horizontal/vertical mount	2	W	□ WIU-2WX	•

While-in-use weather protective covers

Product description

- 1-Gang self-closing
- 1-Gang extra depth, self-closing
- 2-Gang, self-closing

Features

- Rugged UV-resistant polycarbonate cover and back protects devices without cracking or breaking and is non-corrosive and non-conductive
- Moveable hinges reposition easily for vertical or horizontal mounting (1-Gang only)
- Self-closing cover
- 1-Gang box includes 3 inserts for 16 different configurations
- 2-Gang box includes 4 inserts for over 60 different configurations
- Includes pre-mounted gasket
- Meets Canadian electrical code rule 26-702

Standard duty while-in-use weather protective covers

Description	Gang	Color	Depth	Catalog no.	
Horizontal/vertical mount	1	GY	3.25" deep (82.6mm)	□ WIU-1	•
Horizontal/vertical mount	1	W	3.25" deep (82.6mm)	□ WIU-1W	•
Horizontal/vertical mount	1	GY	4.75" deep (120.7mm)	□ WIU-1D	•
Horizontal/vertical mount	2	GY	3.25" deep (82.6mm)	□ WIU-2	•
Horizontal/vertical mount	2	W	3.25" deep (82.6mm)	□ WIU-2W	•

Color information:

GY (Gray), W (White)



Compliances, specifications and availability are subject to change without notice.

RoHS compliant - Page Q-32