

Eaton's Arrow Hart
Universal dimmers

Arrow Hart

Eaton's universal dimmers

High wattage and dual rated, cost effective solution for commercial lighting control installations

EATON

Powering Business Worldwide



Universal slide dimmers (Forward Phase-cut)



SUT7

Product description

Single pole & 3-Way
Dimmable **LED/CFL/FLR**; 450W, 120V/AC; 600W, 277V/AC
INC/HAL/MLV/ELV; 720W, 120V/AC; 1000W, 277V/AC

Features

- Universal dimming of most common lighting loads (phase-cut)
- Dual rated for 120/277V/AC
- Adjustable low-end trimming for increased lamp compatibility
- No de-rating for LED/CFL loads in multi-gang applications
- Integrated full slide control for easy, precise operation
- Ideal for commercial and residential applications
- No neutral required for installation
- Fits standard decorator wallplates

Universal slide dimmers US

Catalog no.	Description	Compatible lamp types	Rating		Color suffix
			Watt	V/AC	
□ SUT7__	Universal slide dimmer (forward phase-cut)	LED/CFL/FLR	450	120	BK, GY, LA, V, W
			600	277	
		INC/HAL/MLV/ELV	720	120	BK, GY, LA, V, W
1000	277				

Color ordering information

For ordering devices, include Catalog no. followed by the color suffix: BK (Black), GY (Gray), LA (Light Almond), V (Ivory), W (White)

BK	GY	LA	V	W
(Black)	(Gray)	(Light Almond)	(Ivory)	(White)

Compliances, specifications and availability are subject to change without notice.

Eaton's Arrow Hart Universal dimmers



SUF7

Universal Phase Selectable slide dimmers

Product description

Single pole & 3-Way
Dimmable **LED/CFL/FLR**; 450W, 120V/AC; 450W, 277V/AC
INC/HAL/ELV; 650W, 120V/AC; 1000W, 277V/AC

Features

- Select between forward and reverse phase cut dimming for the most optimal dimming compatibility
- Dual rated for 120/277V/AC
- Adjustable low-end trimming for increased lamp compatibility
- No de-rating for LED/CFL loads in multi-gang applications
- Integrated full slide control for easy, precise operation
- Ideal for commercial and residential applications
- Neutral required for installation
- Fits standard decorator wallplates
- Do Not use with MLV loads

Universal slide dimmers

Catalog no.	Description	Compatible lamp types	Rating		Color suffix
			Watt	V/AC	
□ SUF7__	Universal phase selectable slide dimmer	LED/CFL/FLR	450	120	BK, GY, LA, V, W
			450	277	
		INC/HAL/ELV	650	120	BK, GY, LA, V, W
			1000	277	

Color ordering information

For ordering devices, include Catalog no. followed by the color suffix: BK (Black), GY (Gray), LA (Light Almond), V (Ivory), W (White)



Compliances, specifications and availability are subject to change without notice.

Electrical Sector
203 Cooper Circle
Peachtree City, GA 30269
United States
Eaton.com
Eaton.com/arrowhart

Electrical Sector
Canada Operations
5925 McLaughlin Road
Mississauga, Ontario, L5R 1B8
Canada
EatonCanada.ca
Eaton.com/arrowhart

Electrical Sector
Mexico Operations
Carr. Tlalnepantla -
Cuautitlán Km 178 s/n
Col. Villa Jardín esq.
Cerrada 8 de Mayo
Cuautitlán, Mexico CP 54800
México
Eaton.mx
Eaton.com/arrowhart

Eaton
1000 Eaton Boulevard
Cleveland, OH 44122
United States
Eaton.com

© 2017 Eaton
All Rights Reserved
Printed in USA
Publication No. SA620013EN
April 2017

Eaton is a registered trademark.
All other trademarks are property
of their respective owners.