

Eaton's
Aspire design collection

Aspire



EATON

Powering Business Worldwide

The Aspire design collection enhances décor

Aspire's award-winning architectural wiring devices add a touch of elegance to the most sophisticated interior design. The clean, modern appearance of the Aspire product line represents the most innovative approach to designer wiring devices. An Aspire wiring device makes a statement as an integral element of décor.





Upgrade to the exceptional with Aspire


Table of contents	Page
Aspire	
Aspire features and benefits	2-3
Dimmers	4-5
Fan speed controls	6
Switches	7
Timers	8
Screwless wallplates	9
Aspire Z-Wave wireless collection	
Aspire Z-Wave features and benefits	10
Wireless system product overview	11

Aspire design collection

The unique and sophisticated appearance is designed to be an integral element of interior design and a luxury upgrade that's affordable to everyone. Aspire's coordinating colors and textures and the stylish high-shine and pearlescent finishes, mark each device as an exceptional finishing touch designed for the finest homes and offices.

Aspire Z-Wave wireless collection

Provides intelligent wireless control of the lights in and around your home - at the touch of a button. Set the mood for family movies, entertaining friends, or a romantic dinner to match your lifestyle. Control lighting as well as appliances to help reduce energy costs.



Dimmers

Aspire dimmers provide adjustable lighting control to set the mood of a room. It creates atmosphere and paints the walls with sophistication.

Switches

Aspire switches combine a modern, sophisticated appearance with performance-enhancing technical features.

Receptacles/GFCIs

Behind the stylish faceplate are the less visible features that make Aspire receptacles high-performing yet easy to install. Aspire GFCIs automatically self-tests periodically to ensure GFCI protection.

Wallplates

Aspire wallplates come in three distinctive colors to coordinate with the entire Aspire line of devices as well as Aspire Z-Wave. Single-gang through six-gang mid-size wallplates offer a myriad of choices for the most complex home or office installations.



Wallplates are designed for easy and fast installation, simply attach the backplate to the device and snap the wallplate cover into place.

Smart dimmers

Product description

Single-pole & multi-location
 300W, 600W, 1000W, 120V/AC
 Incandescent/halogen, magnetic low-voltage, electronic low-voltage, LED/CFL, fluorescent

Design features

- Available in three distinctive, two-tone color combinations: White Satin, Desert Sand, and Silver Granite, plus single-tone Alpine White
- LED light level display for presetting illumination levels and master/accessory units for multi-location control
- Seven step green LED display alongside push pad indicates selected light level—and reduces brightness when OFF (location feature)
- Durable top and backbody
- 600W dimmers have wrap around strap to eliminate the need for de-rating for 1 or 2 gangs
- Electro-mechanical push pad for ON/OFF operation with separate DIM/BRIGHT bar
- Preset feature allows user to return to previous light setting when turning lights ON
- Illumination level may be adjusted with switch in on or off position
- 10 second delayed-OFF feature by pressing and holding push pad for 2 seconds when dimmer is ON
- Pressing and holding push pad for 2 seconds when dimmer is off brings light to full brightness
- Amber LED at bottom of LED display indicates ON/OFF load status
- Master controls as many as 5 accessory units for multiple location installations
- Adjustable low-end and high end trimming to prevent lamp flickering
- Title 24 compliant (Except 9542)



9540-N



9534



9537



9542

Smart dimmer system master & accessories



Rating		Description	Color suffix	Catalog no.	TITLE 24
W	V/AC				
300	120	Smart dimmer, single-pole/3-way, incandescent/halogen, dimmable LED/CFL, magnetic low-voltage, electronic low-voltage	AW, DS, SG, WS	□ 9540-N_	•
600	120	Smart dimmer, incandescent/halogen, magnetic low-voltage, electronic low-voltage	AW, DS, SG, WS	□ 9534_	•
1000	120	Smart dimmer, incandescent/halogen, magnetic low-voltage, single-pole	AW, DS, SG, WS	□ 9536_	•
		Electronic low-voltage, single-pole	AW, DS, SG, WS	□ 9537_	•
—	—	Accessory dimmer, multi-location	AW, DS, SG, WS	□ 9542_	

cULus Listed to UL1472, file no. E47967; NOM certified

Color ordering information:

For ordering devices, include Catalog no. followed by the Color suffix: AW (Alpine White), DS (Desert Sand), SG (Silver Granite), WS (White Satin)

AW	AW	DS	DS	SG	SG	WS	WS
(Alpine White)		(Desert Sand)		(Silver Granite)		(White Satin)	

TITLE 24 Indicates Title 24 compliant

Compliances, specifications and availability are subject to change without notice.

Slide dimmers

Product description

Single-pole & 3-way
300W, 600W or 1000W, 120V/AC
Incandescent/halogen, magnetic low-voltage, electronic low-voltage, LED/CFL, fluorescent

Design features

- Available in three distinctive, two-tone color combinations: White Satin, Desert Sand, and Silver Granite, plus single-tone Alpine White
- All units are available in combined single-pole/3-way versions
- Replaces a standard switch and offers dimming capabilities
- Neutral is not required for installation of device
- Dimmers can be adjusted with or without the lights on; preset feature returns the light level to its prior setting without readjustment
- Electrostatic discharge protection
- Incandescent/halogen and magnetic low-voltage offered in single unit versions
- Power failure memory
- Square law dimming—perceived dimming level is proportional to the slider position
- Durable top and backbody for long reliable performance
- Switch has quiet, smooth actuation
- Title 24 compliant



9530



9532



9568



9573

Slide dimmers

Rating		Description	Neutral	Color suffix	Catalog no.	TITLE 24
W	V/AC					
600	120	Incandescent/halogen, magnetic low-voltage dimmer, single-pole /3-way with preset	N	AW, DS, SG, WS	<input type="checkbox"/> 9530__	•
		Electronic low-voltage dimmer, single-pole/3-way with preset	N	AW, DS, SG, WS	<input type="checkbox"/> 9531__	•
1000	120	Incandescent/halogen, magnetic low-voltage dimmer, single-pole /3-way with preset	N	AW, DS, SG, WS	<input type="checkbox"/> 9532__	•
		Electronic low-voltage dimmer, single-pole/3-way with preset	N	AW, DS, SG, WS	<input type="checkbox"/> 9533__	•

cULus Listed to UL1472, file no. E47967; NOM certified

Fluorescent dimmers

Rating			Description	Neutral	Color suffix	Catalog no.	TITLE 24
A	W/VA	V/AC					
8	1000	120	Fluorescent dimmer, single-pole/3-way with preset Mark 10®, AmbiStar® & Tu-Wire® compatible	Y	AW, DS, SG, WS	<input type="checkbox"/> 9568__	•
		277	Fluorescent dimmer, single-pole/3-way with preset Mark 10®, compatible	Y	AW, DS, SG, WS	<input type="checkbox"/> 95687__	•

cULus Listed to UL1472, file no. E47967; NOM certified

LED & compact fluorescent dimmers

Rating		Description	Neutral	Color suffix	Catalog no.	TITLE 24
W	V/AC					
300	120	LED/CFL, single-pole/3-way	Y	AW, DS, SG, WS	<input type="checkbox"/> 9573__	•
600	120	Incandescent/halogen	Y			

For a list of compatible dimmable LED & CFL lamps and fixtures, see product page at www.cooperwiringdevices.com.
cULus Listed to UL1472, file no. E47967; NOM certified

Color ordering information:

For ordering devices, include Catalog no. followed by the Color suffix: AW (Alpine White), DS (Desert Sand), SG (Silver Granite), WS (White Satin)

AW	AW	DS	DS	SG	SG	WS	WS
(Alpine White)		(Desert Sand)		(Silver Granite)		(White Satin)	

 Indicates Title 24 compliant

Compliances, specifications and availability are subject to change without notice.

Fan speed controls

Product description

Single-pole & 3-way
1.5A or 5A 120V/AC
3-speed or fully variable



9543

Design features

- Quiet fan speed controls have special circuitry to reduce fan motor noise at low speeds
- Available in three distinctive, two-tone color combinations: White Satin, Desert Sand, and Silver Granite, plus single-tone Alpine White
- All units are available in combined single-pole/3-way versions
- Replaces a standard switch and adds fan control capabilities
- Neutral is not required for installation of device
- Electrostatic discharge protection
- Radio frequency interface filtering is standard on all models
- Power failure memory
- Virtually unbreakable top and backbody
- Switch has quiet, smooth actuation
- Easy-access ground screws
- Tri-combo screws accept Slotted, Phillips, and Robertson-head tools for installation flexibility

Fan speed controls

Rating	A	V/AC	Description	Color suffix	Catalog no.
1.5		120	Quiet 3-speed fan control, single-pole/3-way, side wire	AW, DS, SG, WS	□ 9544__
5		120	Fully variable fan speed control, single-pole/3-way, side wire	AW, DS, SG, WS	□ 9543__

cULus Listed to UL1917, file no. E202842; NOM certified

Color ordering information:

For ordering devices, include Catalog no. followed by the Color suffix: AW (Alpine White), DS (Desert Sand), SG (Silver Granite), WS (White Satin)

AW	AW	DS	DS	SG	SG	WS	WS
(Alpine White)		(Desert Sand)		(Silver Granite)		(White Satin)	

Compliances, specifications and availability are subject to change without notice.

Aspire design collection

Switches

Product description

Single-pole, 3-way, 4-way
 15A, 120/277V/AC
 20A, 120/277V/AC

Design features

- Available in three distinctive, two-tone color combinations: White Satin, Desert Sand, and Silver Granite, plus single-tone Alpine White
- 120/277V/AC rating ideal for fluorescent lighting fixtures typical in commercial applications
- Virtually unbreakable, ultrasonically welded top and back body
- Long, broad mounting strap virtually eliminates floating installations
- Easy-access ground screws
- Tri-combo screws accept Slotted, Phillips, and Robertson-head tools for installation flexibility
- Push-in terminals accept #14 AWG solid wire
- Backwire clamps (4-way models only) on the side terminals provide for easy installation of #12 and #14 AWG wire



9503



9504

Switches   

Rating		Description	Color suffix	Catalog no.
A	V/AC			
15	120/277	Single-pole, side wire & push wire	AW, DS, SG, WS	□ 9501__
		3-way, side wire & push wire	AW, DS, SG, WS	□ 9503__
		4-way, back wire & push wire	AW, DS, SG, WS	□ 9504__*
20	120/277	Single-pole, side wire & push wire	AW, DS, SG, WS	□ 9515__
		3-way, side wire & push wire	AW, DS, SG, WS	□ 9516__

cULus Listed to UL20, file no. E18704

* UL verified to Federal Spec. WC-896E; NOM certified

Color ordering information:

For ordering devices, include Catalog no. followed by the Color suffix: AW (Alpine White), DS (Desert Sand), SG (Silver Granite), WS (White Satin)

AW	AW	DS	DS	SG	SG	WS	WS
(Alpine White)		(Desert Sand)		(Silver Granite)		(White Satin)	

Compliances, specifications and availability are subject to change without notice.

Timers

Product description

Single-pole
15A, 120V/AC; 1800W
Incandescent/halogen, magnetic low-voltage, electronic low-voltage, fluorescent, compact fluorescent, LED

Design features

- Perfect for both new construction and retrofit with no neutral required for installation
- Available in both hours and minutes versions
- Five (5) preset time intervals
- Easily programmable to alternate time intervals to suit your needs
- Color change faceplate kits available
- Works with all popular load types: incandescent/halogen, magnetic low-voltage, electronic low-voltage, fluorescent, compact fluorescent, and LED
- Horsepower rated for 1/4 HP motor loads
- LED indication of time interval selected and countdown



9591

Timers



Rating		W	Description	Color suffix	Catalog no.
A	V/AC				
15	120	1800	5-button minute timer with OFF button, single-pole	AW, DS, SG, WS, C1, C2, C3	□ 9590__
			5-button hour timer with OFF button, single-pole	AW, DS, SG, WS, C1, C2, C3	□ 9591__


cULus Listed to UL60730-1A & 60730-2-7, file no. E325082; certified to CSA E60730-1:02 & E60730-2-9:01; NOM certified

Color change kits for Aspire timers

Description	Color suffix	Catalog no.
Color change kit 1 (5, 10, 15, 30, 60) for minute timer	AW, DS, SG, WS	□ 951MK__-P
Color change kit 2 (5, 10, 20, 30, 60) for minute timer	AW, DS, SG, WS	□ 952MK__-P
Color change kit 3 (5, 15, 30, 45, 60) for minute timer	AW, DS, SG, WS	□ 953MK__-P
Color change kit 4 (1, 5, 10, 15, 30) for minute timer	AW, DS, SG, WS	□ 954MK__-P
Color change kit 5 (1, 10, 15, 20, 30) for minute timer	AW, DS, SG, WS	□ 955MK__-P
Color change kit 1 (1, 2, 4, 8, 12) for hour timer	AW, DS, SG, WS	□ 951HK__-P
Color change kit 2 (1, 3, 6, 9, 12) for hour timer	AW, DS, SG, WS	□ 952HK__-P
Color change kit 3 (2, 4, 8, 12, 24) for hour timer	AW, DS, SG, WS	□ 953HK__-P
Color change kit 4 (30, 1, 2, 4, 8) for hour timer	AW, DS, SG, WS	□ 954HK__-P
Color change kit 5 (15, 30, 1, 2, 4) for hour timer	AW, DS, SG, WS	□ 955HK__-P

Color ordering information:

For ordering devices, include Catalog no. followed by the Color suffix: AW (Alpine White), DS (Desert Sand), SG (Silver Granite), WS (White Satin), C1 (Color Change Kit: DS, SG, WS), C2 (Color Change Kit: AW, DS, SG), C3 (Color Change Kit: AW, DS, WS)



Compliances, specifications and availability are subject to change without notice.

Aspire design collection

Aspire coordinating screwless wallplates

Product description

Mid-size thermoplastic

Design features

- Available in three distinctive colors to coordinate with the rest of the Aspire product line: Desert Sand, Silver Granite and White Satin (select White Satin wallplates for Alpine White devices)
- Screwless wallplates clip smoothly into place with gentle pressure
- Clearly marked top edges make mounting wallplates easy to orient and attach
- Virtually unbreakable polycarbonate construction
- Standard decorator-style opening
- Mid-size to cover wall imperfections and large wallboard openings
- Wallplates appear to float freely on the surface of the wall, framing every device beautifully
- Screw-catch feature holds backplate mounting screws captive for ease of installation



9521



9522

Mid-size screwless wallplates

Description	Color suffix	Catalog no.
1-Gang Aspire wallplate	DS, SG, WS	□ 9521__
2-Gang Aspire wallplate	DS, SG, WS	□ 9522__
3-Gang Aspire wallplate	DS, SG, WS	□ 9523__
4-Gang Aspire wallplate	DS, SG, WS	□ 9524__
5-Gang Aspire wallplate	DS, SG, WS	□ 9525__
6-Gang Aspire wallplate	DS, SG, WS	□ 9526__

cULus Listed to UL5154D, file no. E33216

Color ordering information:

For ordering devices, include Catalog no. followed by the Color suffix: DS (Desert Sand), SG (Silver Granite), WS (White Satin)

DS	DS	SG	SG	WS	WS
(Desert Sand)		(Silver Granite)		(White Satin)	

Compliances, specifications and availability are subject to change without notice.

Aspire Z-Wave

Experience more with the
Aspire Z-Wave wireless collection

Aspire Z-Wave combines the elegance of the sophisticated Aspire design with the innovation of intelligent wireless technology to deliver a new level of comfort, control and style throughout your home.



Anyplace switch
provides flexibility to put a switch anyplace you want without running wire



Handheld controller
enables you to control and monitor your home lighting



Scene control keypads
provide ON/OFF control and dimming for groups of lights

Industry leading breadth of line

- Handheld controllers
- Home controller and USB stick
- 5-button scene keypads
- Dimmers, switches and accessories
- Receptacles and plug-in lamp modules
- Battery operated switch/dimmer

Personalized choices

Personalized controller screens allow for favorite scenes to be defined by the user on each handheld controller with a single press of a button.

Accessorize with designer Aspire devices to complete the look throughout the home. Complement the look of your Aspire Z-Wave system with Aspire smart and slide dimmers, fan speed controls, and screwless wallplates.

Aspire Z-Wave

Aspire with Z-Wave® technology is a new generation of easy-to-install and easy-to-use wireless RF-based home control technology. Aspire Z-Wave offers a full array of one-touch controllers and a wide range of wiring devices that can be integrated together, creating a wireless home control network.

Best of all, installing an Aspire Z-Wave wireless system requires no special wiring or rewiring — making it ideal for retrofitting existing homes and for new home construction.

Unparalleled system features & benefits

- Easy installation
- Ideal retrofit solution; no new wiring is needed
- Energy savings and comfort
- Added security and convenience inside and outside the home
- Simple and intuitive programming
- Control shades
- Expandable and scalable system
- Control over 200 devices locally or remotely via the web
- Interoperability powered by Z-Wave technology
- Matching Aspire designer devices and screwless wallplates

Z-Wave® technology

Z-Wave is a highly versatile and dependable RF-based home control technology that effectively transforms any component into an intelligently networked device that can be controlled and monitored wirelessly. Aspire Z-Wave products are compatible with any Z-Wave certified device. This interoperability with other manufacturers' devices provides maximum flexibility and expandability.



Each Aspire Z-Wave device functions as a repeater, using 908 MHz signals to ensure that every command is carried out. Z-Wave's "mesh network" offers extremely high performance and greater reliability than many control systems.

Z-Wave wireless collection

Aspire Z-Wave

Handheld & home controllers



RFHDCSG

Rating Hz	V/AC	Description	Aspire color suffix	Catalog no.
—	—	Handheld controller, battery operated (2 AA batteries)		<input type="checkbox"/> RFHDCSG
60	120	Wall mount 5-button keypad	AW, DS, SG, WS	<input type="checkbox"/> RFWC5__*

Complies with FCC Part 15, Class B; *cULus Listed to UL1472, file no. E47967, certified to CSA C22.2 no. 187.1, NOM certified

Smart dimmer system master & accessories



RF9542-ZDS

Rating W/AC V/AC Hz	Description	Aspire color suffix	Catalog no.	TITLE 24
300 120 60	Z-Wave smart dimmer, dimmable LED/CFL	AW, DS, SG, WS	<input type="checkbox"/> RF9540-N__	•
600 120 60	Z-Wave smart dimmer, dimmable incandescent, electronic & magnetic low voltage, fluorescent			
600 120 60	Z-Wave smart dimmer, incandescent (no neutral required)	AW, DS, SG, WS	<input type="checkbox"/> RF9534__	•
1000 120 60	Z-Wave smart dimmer, incandescent/magnetic low voltage	AW, DS, SG, WS	<input type="checkbox"/> RF9536-N__	•
	Z-Wave smart dimmer, incandescent (no neutral required)	AW, DS, SG, WS	<input type="checkbox"/> RF9536__	•
	Z-Wave smart dimmer, electronic low voltage	AW, DS, SG, WS	<input type="checkbox"/> RF9537-N__	•
	Z-Wave accessory w/LEDs, compatible with Z-Wave master dimmers (neutral required)	AW, DS, SG, WS	<input type="checkbox"/> RF9542-Z__	
120 60	Non-RF accessory w/LEDs, compatible only with RF9534 & RF9536 (no neutral required)	AW, DS, SG, WS	<input type="checkbox"/> RF9542__	

*RF9575 anyplace switch can also be used as accessory dimmer with Z-Wave master dimmer for hassle free installation
Complies with Z-Wave®, FCC (except RF9542), cULus, NOM certified

Switches



RF9501AW

Rating A V/AC Hz	Description	Aspire color suffix	Catalog no.
15 120 60	15A single-pole, LED, CFL, INC, MLV, ELV, FLR	AW, DS, SG, WS	<input type="checkbox"/> RF9501__
8 120 60	8A single-pole, incandescent only, no neutral required	AW, DS, SG, WS	<input type="checkbox"/> RF9518__
— 120 60	Accessory switch, compatible with RF9501 and RF9518	AW, DS, SG, WS	<input type="checkbox"/> RF9517__

*RF9575 anyplace switch can also be used as accessory switch with Z-Wave master switches for hassle free installation
Complies with FCC Part 15, Class B; cULus Listed to UL1472, file no. E47967, certified to CSA C22.2 no. 187.1; NOM certified

Tamper resistant receptacles



RFTR9505-TDS

Rating A V/AC	Description	Color suffix	Catalog no.
15 125	Tamper resistant NEMA 5-15R split control duplex receptacle, wire leads	AW, BK, DS, SG, WS	<input type="checkbox"/> RFTR9505-T__

Complies with FCC Part 15, Class B; cULus Listed to UL38DS, file no. E325082; NOM certified

Battery operated anyplace switch and combination kits



Anyplace switch

Description	Color suffix	Catalog no.
Battery operated anyplace switch	AW, DS, SG, WS	<input type="checkbox"/> RF9575__
Anyplace switch (RF9575AW) w/ Z-Wave switch (RF9501AW)	AW	<input type="checkbox"/> RFAS01AW
Anyplace switch (RF9575AW) w/ Z-Wave dimmer (RF9540-NAW)	AW	<input type="checkbox"/> RFAS40AW
Anyplace switch (RF9575AW) w/ Z-Wave receptacle (RFTR9505-TAW)	AW	<input type="checkbox"/> RFAS05AW
Anyplace switch (RF9575AW) w/ Z-Wave appliance module (RFAPM)	AW	<input type="checkbox"/> RFASAPMAW
Anyplace switch (RF9575AW) w/ Z-Wave lamp dimming module (RFLDM)	AW	<input type="checkbox"/> RFASLDMAW

Complies with FCC, cULus, NOM/ANCE certified

Color ordering information:

For ordering devices, include catalog no. followed by the color suffix: AW (Alpine White), DS (Desert Sand), SG (Silver Granite), WS (White Satin), BK (Black)

AW	AW	DS	DS	SG	SG	WS	WS	BK
(Alpine White)		(Desert Sand)		(Silver Granite)		(White Satin)		(Black)

TITLE 24 Indicates Title 24 compliant

Compliances, specifications and availability are subject to change without notice.

Visit our website:
www.eaton.com/wiringdevices

Electrical Sector
203 Cooper Circle
Peachtree City, GA 30269
United States
Eaton.com
Eaton.com/wiringdevices

Electrical Sector
Canada Operations
5925 McLaughlin Road
Mississauga, Ontario, L5R 1B8
Canada
EatonCanada.ca
Eaton.com/wiringdevices

Electrical Sector
Mexico Operations
Carr. Tlalnepantla -
Cauhtitlán Km 17.8 s/n
Col. Villa Jardín esq.
Cerrada 8 de Mayo
Cauhtitlán, México CP 54800
México
Eaton.mx
Eaton.com/wiringdevices

Eaton
1000 Eaton Boulevard
Cleveland, OH 44122
United States
Eaton.com

© 2016 Eaton
All Rights Reserved
Printed in USA
Publication No. BR610001EN
March 2016

Eaton is a registered trademark.

All other trademarks are property
of their respective owners.



Powering Business Worldwide