

# Our universe is always expanding Universal SUL06P

### Highly versatile

Compatible with dimmable LED, dimmable CFL, INC, HAL, dimmable FLR, ELV and MLV light sources.

### Adjustable low-end and high-end trim

Set the minimum light level for each switch using a simple control.

## Flicker-free dimming

Microprocessor-based design enhances performance and delivers seamless dimming.

**Easy installation** No neutral wire required. Back wire clamps speed installation, too.

# Dimming done right.



See the latest additions to the Eaton Universal Dimmer family at **Eaton.com** 

Eaton Universal Slide Dimmers are ergonomically designed and provide flicker-free dimming for seamless ambiance.



Specifications	SUL06P	SUF7
Load rating	<b>300W - 120VAC</b> Dimmable LED, dimmable CFL	<b>450W - 120VAC/277VAC</b> Dimmable LED, dimmable CFL
	650W - 120VAC HAL, INC, dimmable FLR, ELV/MLV	650W - 120VAC, 1000W - 277VAC HAL, INC, dimmable FLR, ELV
No de-rating required	$\checkmark$	Not required for LED/CFL loads in multi-gang applications
Neutral required	_	$\checkmark$
Wiring configurations	Single pole & 3-way	Single pole & 3-way
Dimming type	Forward phase cut	Forward & reverse phase cut
Adjustable low-end trim	$\checkmark$	$\checkmark$
Wiring type	Back & side wire	Wire leads
Title 24 compliant	$\checkmark$	$\checkmark$



Eaton 1000 Eaton Boulevard Cleveland, OH 44122 United States Eaton.com Electrical Sector 203 Cooper Circle Peachtree City, GA 30269 United States Eaton.com Eaton.com/wiringdevices © 2021 Eaton All Rights Reserved Printed in USA Publication No. BR610053EN March 2021 Eaton is a registered trademark.

All other trademarks are property of their respective owners.