

# Portable GFCIs

Project Name:	Prepared By:
Project Number:	Date:
Catalog Number:	Type:

## Description

15A 120 VAC

### Design features

- High-strength polycarbonate housing for durability
- Compact body design
- NEMA 3R rated for indoor/outdoor use
- Field wireable versions available for attachment to existing cords or equipment supply
- Automatic and manual GFCI reset options available



GFP11M1P3



GFPI11M133



GFI11MN3

**Table 1. 15A Plug Series - Single & Tri-Tap**

Catalog No.	NEMA	NEMA Rating	Cord Length	Cord Gauge	Rating	
					A	VAC
<input type="checkbox"/> GFP11M1P3	5-15	3R	2' (0.61m)	12/3 AWG	15	120
<input type="checkbox"/> GFP11M1P9	5-15	3R	2' (0.61m)	12/3 AWG	15	120
<input type="checkbox"/> GFP11M4P3	5-15	3R	25' (7.62m)	12/3 AWG	20	120
<input type="checkbox"/> GFP11M4P9	5-15	3R	25' (7.62m)	12/3 AWG	20	120

Automatic resetting GFCIs also available. When ordering automatic Portable GFCIs replace "M" in catalog number with "A". Example: GFP11**A**1P3 = Automatic; GFP11**M**1P3 = Manual.

**Table 2. 15A Plug Series - Field Wireable**

Catalog No.	NEMA	NEMA Rating	Cord Length	Cord Gauge	Rating	
					A	VAC
<input type="checkbox"/> GFP11MNP	5-15	3R	2' (0.61m)	12/3 AWG	15	120

Automatic resetting GFCIs also available. When ordering automatic Portable GFCIs replace "M" in catalog number with "A". Example: GFP11**A**NP = Automatic; GFP11**M**NP = Manual.

**Table 3. 15A Plug Series - Field Wireable**

Catalog No.	NEMA	NEMA Rating	Cord Length	Cord Gauge	Rating	
					A	VAC
<input type="checkbox"/> GFI11M133	5-15	3R	2' (0.61m)	12/3 AWG	15	120
<input type="checkbox"/> GFI11M139	5-15	3R	2' (0.61m)	12/3 AWG	15	120
<input type="checkbox"/> GFI11M233	5-15	3R	6' (1.83m)	12/3 AWG	15	120
<input type="checkbox"/> GFI11M239	5-15	3R	6' (1.83m)	12/3 AWG	15	120
<input type="checkbox"/> GFI11M433	5-15	3R	25' (7.62m)	12/3 AWG	15	120
<input type="checkbox"/> GFI11M439	5-15	3R	25' (7.62m)	12/3 AWG	15	120
<input type="checkbox"/> GFI11M633	5-15	3R	50' (15.24m)	12/3 AWG	15	120
<input type="checkbox"/> GFI11M639	5-15	3R	50' (15.24m)	12/3 AWG	15	120

Automatic resetting GFCIs also available. When ordering automatic Portable GFCIs replace "M" in catalog number with "A". Example: GFI11**A**133 = Automatic; GFI11**M**133 = Manual.

**Table 4. 15A Inline Series - Field Wireable**

Catalog No.	NEMA	NEMA Rating	Cord Length	Cord Gauge	Rating	
					A	VAC
<input type="checkbox"/> GFI11MN3	5-15	3R	1' (0.3m)	12/3 AWG	15	120

Automatic resetting GFCIs also available. When ordering automatic Portable GFCIs replace "M" in catalog number with "A". Example: GFI11**A**N3 = Automatic; GFI11**M**N3 = Manual.



Powering Business Worldwide

Project Name:	Prepared By:
Project Number:	Date:
Catalog Number:	Type:

## Applications

Wet locations, power generators, agricultural equipment, portable electric heaters, submersible pumps, pipeline heaters, automotive garages, industrial part washers, cement cutting equipment, outdoor signage, vending equipment and anywhere else a portable GFCI-protected circuit is needed.

**Table 5. Specifications**

Description	15A Plug Series	15A Plug Series (Field Wireable)	15A Inline Series	15A Inline Series (Field Wireable)
<b>Part Nos.</b>	GFP11M1P3, GFP11M1P9 GFP11M4P3, GFP11M4P9	GFP11MNP	GFI11M133, GFI11M139 GFI11M233, GFI11M239 GFI11M433, GFI11M439 GFI11M633, GFI11M639	GFI11MN3
<b>Rated Supply Amperage / Voltage</b>	15A, 120V/AC	15A, 120V/AC	15A, 120V/AC	15A, 120V/AC
<b>Rated Current</b>	Up to 15A or rating of wiring device and/or cable	Up to 15A or rating of wiring device and/or cable	Up to 15A or rating of wiring device and/or cable	Up to 15A or rating of wiring device and/or cable
<b>NEMA Rating</b>	3R	3R	3R	3R
<b>Plug Style</b>	Straight Blade	Straight Blade	Straight Blade	Straight Blade
<b>NEMA Configuration</b>	5-15	5-15	5-15	5-15
<b>Cord</b>	Heavy-duty 12/3 SJTW Cable	Heavy-duty 12/3 SJTW Cable	Heavy-duty 12/3 SJTW Cable	Heavy-duty 12/3 SJTW Cable
<b>Reset Type</b>	Manual or Automatic	Manual or Automatic	Manual or Automatic	Manual or Automatic
<b>Operating Frequency</b>	60 Hz	60 Hz	60 Hz	60 Hz
<b>Type</b>	Class A	Class A	Class A	Class A
<b>Ground Trip Current</b>	4-6 mA	4-6 mA	4-6 mA	4-6 mA
<b>Overload Current</b>	90A @ 125 V/AC	90A @ 125 V/AC	90A @ 125 V/AC	90A @ 125 V/AC
<b>Insulation Voltage</b>	1,500 VRMS – 1 Minute	1,500 VRMS – 1 Minute	1,500 VRMS – 1 Minute	1,500 VRMS – 1 Minute
<b>Endurance Operations</b>	3,000 Operations	3,000 Operations	3,000 Operations	3,000 Operations
<b>Testing &amp; Code Compliance</b>	UL 943 & CSA C22.2 No. 144 OSHA 29 CFR 1926.404 (b)(1)(ii) & OSHA 29 CFR 1926.405 (a)(2)(ii)(G) NEC 590.6 NEC 511.12 NEC 600.10 NEC 680.5B NEC 680.40 NEC 555.3	UL 943 & CSA C22.2 No. 144 OSHA 29 CFR 1926.404 (b)(1)(ii) & OSHA 29 CFR 1926.405 (a)(2)(ii)(G) NEC 590.6 NEC 511.12 NEC 600.10 NEC 680.5B NEC 680.40 NEC 555.3	UL 943 & CSA C22.2 No. 144 OSHA 29 CFR 1926.404 (b)(1)(ii) & OSHA 29 CFR 1926.405 (a)(2)(ii)(G) NEC 590.6 NEC 511.12 NEC 600.10 NEC 680.5B NEC 680.40 NEC 555.3	UL 943 & CSA C22.2 No. 144 OSHA 29 CFR 1926.404 (b)(1)(ii) & OSHA 29 CFR 1926.405 (a)(2)(ii)(G) NEC 590.6 NEC 511.12 NEC 600.10 NEC 680.5B NEC 680.40 NEC 555.3

Compliances, specifications and availability are subject to change without notice.

Project Name:	Prepared By:
Project Number:	Date:
Catalog Number:	Type:

## Certifications & Compliances

Catalog No.	UL	CSA
GFP11M1P3	•	•
GFP11M1P9	•	•
GFP11M4P3	•	•
GFP11M4P9	•	•
GFP11MNP	•	•
GFI11M133	•	•
GFI11M139	•	•
GFI11M233	•	•
GFI11M239	•	•
GFI11M433	•	•
GFI11M439	•	•
GFI11M633	•	•
GFI11M639	•	•
GFI11MN3	•	•

**KEY:**  UL  CSA

**Compliances, specifications and availability are subject to change without notice.**

Electrical Sector  
203 Cooper Circle  
Peachtree City, GA 30269  
United States  
Eaton.com  
Eaton.com/arrowhart

Electrical Sector  
Canada Operations  
5925 McLaughlin Road  
Mississauga, Ontario, L5R 1B8  
Canada  
EatonCanada.ca  
Eaton.com/arrowhart

Electrical Sector  
Mexico Operations  
Carr. Tlalnepantla -  
Cuautitlan Km 17.8 s/n  
Col. Villa Jardin esq.  
Cerrada 8 de Mayo  
Cuautitlan, Mexico CP 54800  
Mexico  
Eaton.mx  
Eaton.com/arrowhart