

Protect your valuables with Eaton's tamper resistant surge receptacles



Audible alarm signals when surge protection has expired

LED indicators to verify surge protection and wiring diagnostics

Front access switch for muting audible alarm until device is replaced

Provides surge protection for hot to neutral, hot to ground and neutral to ground

Additional features & benefits

- Available in hospital and commercial grades in 15A & 20A 125V configurations with LED, audible alarm and isolated ground versions
- Provides surge protection for hot to neutral, hot to ground and neutral to ground
- Available in isolated ground versions for noise protection against EMI and RFI
- Audible alarm signals when surge protection has expired
- Available in eight different colors

LED and Audible



Residential and commercial grade



Hospital grade



Isolated ground variants

LED Indication



Residential and commercial grade

EATON

Powering Business Worldwide

Eaton's Wiring Devices Tamper resistant surge receptacles



With **over 80% of surges** originating from inside a building, **Eaton's surge protection point-of-use receptacles** provide branch circuit surge protection for sensitive electronic equipment that panel mounted surge protection systems alone cannot provide.



TR8262

Receptacles w/audible alarm & LED indicators, back & side wire

Rating						
A	V/AC	NEMA	Description	Color suffix	Catalog no.	
15	125	5-15R	Hospital grade, duplex receptacle, TR	B, BK, BL, GY, LA, RD, V, W	TR8262__S	
			IG hospital grade, duplex receptacle, TR	B, BK, BL, GY, LA, RN, RD, V, W	TRIG8262__S	
			Commercial grade, duplex receptacle, TR	B, BK, BL, GY, LA, RD, V, W	TR5262__S-SP-L	
			IG commercial grade, duplex receptacle, TR	B, BK, BL, GY, LA, RN, RD, V, W	TRIG5262__S	
20	125	5-20R	Hospital grade, duplex receptacle, TR	B, BK, BL, GY, LA, RD, V, W	TR8362__S	
			IG hospital grade, duplex receptacle, TR	B, BK, BL, GY, LA, RN, RD, V, W	TRIG8362__S	
			Commercial grade, duplex receptacle, TR	B, BK, BL, GY, LA, RD, V, W	TR5362__S	
			IG commercial grade, duplex receptacle, TR	B, BK, BL, GY, LA, RN, RD, V, W	TRIG5362__S	

560 Joules, max. surge current - 18kA per mode, UL 1449 3rd edition cULus, file no. E15058



TRIG8362

Receptacles w/LED indicators, back & side wire

Rating						
A	V/AC	NEMA	Description	Color suffix	Catalog no.	
15	125	5-15R	Commercial grade, duplex receptacle, TR	B, BK, BL, GY, LA, RD, V, W	TR5260__S-SP-L	
20	125	5-20R	Commercial grade, duplex receptacle, TR	B, BK, BL, GY, LA, RD, V, W	TR5360__S	

840 Joules, max. surge current - 18kA per mode, cULus listed to UL 1449 3rd edition, file no E15058



TR5260

Accessories for surge protection receptacles

Description	Color	Catalog no.
1-Gang mid-size decorator polycarbonate wallplate	B, BK, BL, GY, LA, RD, V, W	PJ26__
1-Gang mid-size decorator polycarbonate wallplate, pre-marked "Isolated Ground"	RN	PJ26IG__

Color ordering information:

For ordering devices, include Catalog no. followed by the Color suffix: B (Brown), BK (Black), BL (Blue), GY (Gray), LA (Lt. Almond), RN (Orange), RD (Red), V (Ivory), W (White)

B	BK	BL	GY	LA	RN	RD	V	W
(Brown)	(Black)	(Blue)	(Gray)	(Lt. Almond)	(Orange)	(Red)	(Ivory)	(White)

Compliances, specifications and availability are subject to change without notice.

Electrical Sector
203 Cooper Circle
Peachtree City, GA 30269
United States
Eaton.com
Eaton.com/wiringdevices

Electrical Sector
Canada Operations
5925 McLaughlin Road
Mississauga, Ontario, L5R 1B8
Canada
EatonCanada.ca
Eaton.com/wiringdevices

Electrical Sector
Mexico Operations
Carr. Tlalnepantla -
Cuautitlán Km 178 s/n
Col. Villa Jardín esq.
Cerrada 8 de Mayo
Cuautitlán, Mexico CP 54800
México
Eaton.mx
Eaton.com/wiringdevices