

As well as Fire, Bells still remain a popular choice for many applications such as schools where they can sometimes be used as a signal for class change. All CF bells incorporate highly efficient rotary centrifugal movements combining high sound output with low current consumption.


Features


- High sound output
- Classic design
- Simple installation
- For fire or non fire use

Benefits

- Delivers up to 95dB(A)
- Easily recognisable sound for instant recognition
- Easy to install with a multifixing baseplace
- Flexible usage

Dimensions





Technical Specification

Voltage	20-28Vdc	
Current	25mA (typical) @ 24V	
Sound Output	95dB(A) 24V	
Monitoring	Reverse polarity	
Temperature	- 10°C to + 55°C	
Protection	IP21C	
Construction	Gong - Steel, Base - Polycarbonate	
Weight	0.85Kg	
Colours	Gong - Red Base - Black	

Catalogue Numbers

Reference	Cat No	Description
CFB6D12RED	521301FULL-1301	6 Inch Motorised Bell 12Vdc, Red (Centrifugal *)
CFB6D24RED	521601FULL-1601	6 Inch Motorised Bell 24Vdc, Red (Centrifugal *)



