


Y04133

Frontcase




65R-01

Part No:	English:	Deutsch:	Français:	Italiano:	Espanol:	Notes	QTY:	
00	U8875933	FRONT CASE ASSY	Vordergehäuse-Montage	Carter AV	Scatola anteriore	Tapa delantera	VERTICAL	1
01	8875926	FRONT CASE	Vorerer Gehäuse	Carter AV	Scatola anteriore	Tapa delantera		1
07	DX11245	WASHER	Scheibe	Rondelle	Rondella	Arrandela	M10 X 2MM	4
09	DMX-8-1003	SCREW	Schraube	Vis	Vite	Tornillo	M10 X 35 HEX HD	4
10	X8870542	DOWEL	Dübel, stift	Goujon	Spina	Cabilla	8.0 DIA X 16	2
11	8882415	BUSH	Buchse	Bague	Boccola	Casquillo		1
12	MX-9-1005	NUT	Mutter	Ecrou	Dado	Tuerca	M10	15
14	MX-8-1079	SCREW	Schraube	Vis	Vite	Tornillo	M10 x 40	3
15	MX-8-1080	BOLT	Schraub	Boulon	Vite	Perno	M10 X 58MM	15
16	8873654	PLUNGER	Bolzen	Plongeur	Nottlino	Vastago		1
17	8874897	COMPRESSION SPRING	Feder	Ressort	Molla	Ballesta		1
18	8870590	GASKET	Dichtung	Joint	Guarnizione	Junta		1
19	D8870259	COVER-DETENT	Deckel	Couvercle de verrouillage	Coperchio fermo	Tapa reten		1
20	DMX-3-0801	SPRING WASHER	Federscheibe	Rondelle grower	Rondella di sicurezza	Arandela elásti	M8	2
21	DMX-8-0801	SCREW	Schraube	Vis	Vite	Tornillo	M8 X 14 HEX HD	2
22	DX8874942	OIL FILLER PLUG	Oleinfüllschraibe	Bouchon rempl.d'huile	Tappo riemp.olio	Orificio de llenado aceit		1
23	X8880519	WASHER	Scheibe	Rondelle	Rondella	Arrandela	DOWTY SEAL	1

Y04133


Frontcase



Part No:	English:	Deutsch:	Français:	Italiano:	Espanol:	Notes	QTY:	
26	X8880519	WASHER	Scheibe	Rondelle	Rondella	Arrandela	DOWTY SEAL	1
27	DX8874941	MAGNETIC PLUG	Ablasstopfen	Bouchon vidange	Tappo	Tapón de vaciad	M24	1
29	2005144	COVER	Deckel	Couvercle	Coperchio	Tapa		1
31	DMX-8-1001	SCREW	Schraube	Vis	Vite	Tornillo	M10 X 20	6
32	D8870278	CUP PLUG	Veschlußschraube	Bouchon	Tappo nucleo	Tapón acopado		1
33	8880066	COVER	Deckel	Couvercle	Coperchio	Tapa		1
34	DMX-3-1201	SPRING WASHER	Federscheibe	Rondelle grower	Rondella di sicurezza	Arandela elásti	M12	4
35	DMX-8-1209	SCREW	Schraube	Vis	Vite	Tornillo	M12 X 25MM	4
38	8872603	OIL TROUGH	Olleitblech	Cuve a huile	Raccoglitore olio	Cubeta aceite		1
39	X8872604	SCREW	Schraube	Vis	Vite	Tornillo	6mm DIA x 12.7	2

Y04133


Rearcase



Part No:	English:	Deutsch:	Français:	Italiano:	Espanol:	Notes	QTY:	
00	U8876807	REAR CASING ASSY.	Hinteres Gehäuse	Carter Amere	Scatola Posteriore	Tapa Trasera	VERTICAL	1
01	8876779	REAR CASE	Hinteres Gehäuse	Carter AR	Scatola posteriore	Tapa trasera		1
02	8880066	COVER	Deckel	Couvercle	Coperchio	Tapa		1
03	DMX-3-1201	SPRING WASHER	Federscheibe	Rondelle grower	Rondella di sicurezza	Arandela elásti	M12	4
04	MX-8-1210	SCREW	Schraube	Vis	Vite	Tornillo	M12 x 30	4
05	D8870278	CUP PLUG	Veschlußschraube	Bouchon	Tappo nucleo	Tapón acopado		1
06	X8880496	CUP PLUG	Veschlußschraube	Bouchon	Tappo nucleo	Tapón acopado	DOWTY SEAL	1
09	2005144	COVER	Deckel	Couvercle	Coperchio	Tapa		1
11	DMX-8-1001	SCREW	Schraube	Vis	Vite	Tornillo	M10 X 20	6
12	X8870543	DOWEL	Dübel, stift	Goujon	Spina	Cabilla	16.0 DIA X 30.5	2
13	8882415	BUSH	Buchse	Bague	Boccola	Casquillo		1
15	8874494	PLATE	Platte	Plaque	Disco	Placa		1
16	8874473	SCREW	Schraube	Vis	Vite	Tornillo	3.5mm DIA x 8	2

Y04133

Input Shaft




6 SR-03

Part No:	English:	Deutsch:	Français:	Italiano:	Espanol:	Notes	QTY:
00 U8877944	INPUT SHAFT ASSY	Antriebswelle	Arbre d'entrée	Albero entrata	Eje primario		1
01 8877820	INPUT SHAFT	Antriebswelle	Arbre primaire	Albero entrata	Eje impulsor		1
02 8877317	SYNCHRO FLANGE	SynchronFlansch	Bride de Synchro	Flangia sincronizzatore	Brida de sincronizacion		1
03 X8872593	BEARING	Lagerbausatz	Roulement	Corredo cuscinetti	Conj. Cojinete		1
04 8877700	SPACER	Distanzstück	Entretoise	Distanziale	Separador	3.50MM	1
04 8877699	SPACER	Distanzstück	Entretoise	Distanziale	Separador	3.45MM	1
04 8877698	SPACER	Distanzstück	Entretoise	Distanziale	Separador	3.40MM	1
04 8877697	SPACER	Distanzstück	Entretoise	Distanziale	Separador	3.35MM	1
04 8877696	SPACER	Distanzstück	Entretoise	Distanziale	Separador	3.30MM	1
04 8877695	SPACER	Distanzstück	Entretoise	Distanziale	Separador	3.25MM	1
04 8877694	SPACER	Distanzstück	Entretoise	Distanziale	Separador	3.20MM	1
04 8877693	SPACER	Distanzstück	Entretoise	Distanziale	Separador	3.15MM	1
04 8877692	SPACER	Distanzstück	Entretoise	Distanziale	Separador	3.10MM	1
04 U8877691	SPACER ASSY	Distanzstück satz	Entretoise	Distanziale	Separador		1
05 X8877706	CIRCLIP	Seegerring	Circlip	Anello elastico	Anillo elastico		1

Y04133

Frontcover assy




6 SR-04

Part No:	English:	Deutsch:	Français:	Italiano:	Espanol:	Notes	QTY:
00 U8875121	FRONT COVER ASSY	Vordergehäuse-Montage	Couvercle AV	Coperchio anteriore	Tapa delantera		1
01 8875120	FRONT COVER	Vorderdeckel	Couvercle antérieur	Coperchio anteriore	Tapa delantera		1
02 X8870760	OIL SEAL	Öldichtung	Joint d'huile	Anello tenuta cambio	Reten diferencial		1
04 DMX-8-1002	SCREW	Schraube	Vis	Vite	Tornillo	M10 X 25	5

Y04133


Mainshaft



Part No:	English:	Deutsch:	Français:	Italiano:	Espanol:	Notes	QTY:
00	U8877900	MAINSHAFT ASSY	Hauptwelle	Arbre principal	Albero principal assemble	Eje principal	1
01	8876605	MAINSHAFT	Hauptwelle	Arbre principal	Arbero principal	Eje principal	1
02	X8872236	NEEDLE ROLLER BRG	Nadelrollenlager	Roulement a aiguilles	Cuscinetto a rullin	Cojinette de ridillos en aguja	1
03	8876396	3RD GEAR	Zahnrad 3. Gang	Pigon de 3eme	Ingranaggio albero principale	Engranaje 3a	1
04	8877313	SYNCHRO RING	Synchronring	Anneau de synchro	Andello sincronizzatore	Anillo sincro.	1
04a	8877316	SYNCHRO FLANGE	SynchronFlansch	Bride de Synchro	Flangia sincronizzatore	Brida de sincronizacion	1
05	X8870356	ROLLER	Verriegelungsrolle	Rouleau	Rulli	Rodillo	3
06	8870352	PLUNGER	Bolzen	Plongeur	Nottlino	Vastago	3
07	8870444	SPRING	Feder	Ressort	Molla	Ballesta	3
08	8875128	FIXED HUB	Naba, feststehend	Moyeu fixe	Mozzo fisso	Cubo o campana fija	1
09	8875374	SLIDING SLEEVE	Schiebemuffe	Anneau baladeur	Manicotto scorrevole	Casquillo deslizante	1
10	8877313	SYNCHRO RING	Synchronring	Anneau de synchro	Andello sincronizzatore	Anillo sincro.	1
10a	8877316	SYNCHRO FLANGE	SynchronFlansch	Bride de Synchro	Flangia sincronizzatore	Brida de sincronizacion	1
11	8873636	4TH GEAR	Zahnrad 4.Gang	Pigon de 4eme	Ingranaggio albero principale	Engranaje 4a	1
12	X8872233	NEEDLE ROLLER BRG	Nadelrollenlager	Roulement a aiguilles	Cuscinetto a rullin	Cojinette de ridillos en aguja	1
13	8875196	BEARING SLEEVE,	Lagermuffe	Manchon de roulement	Manica cuscinetto	Casquillo cojinetes	1
14	X8870536	CIRCLIP	Seegerring	Circlip	Anello elastico	Anillo elastico	1

Y04133


Mainshaft



Part No:	English:	Deutsch:	Français:	Italiano:	Espanol:	Notes	QTY:	
15	X8870180	NEEDLE ROLLER BRG	Nadelorollenlager	Roulement a aiguilles	Cuscinetto a rullin	Cojinette de ridillos en aguja	1	
16	8873631	5TH GEAR	Zahnrad 5.Gang	Pigon de 5eme	Ingranaggio albero principale	Engranaje 5a	1	
17	8877314	SYNCHRO RING	Synchronring	Anneau de synchro	Andello sincronizzatore	Anillo sincro.	1	
17a	8877317	SYNCHRO FLANGE	SynchronFlansch	Bride de Synchro	Flangia sincronizzatore	Brida de sincronizacion	1	
18	X8870356	ROLLER	Verriegelungsrolle	Rouleau	Rulli	Rodillo	3	
19	8870352	PLUNGER	Bolzen	Plongeur	Nottlino	Vastago	3	
20	8870444	SPRING	Feder	Ressort	Molla	Ballesta	3	
21	8875127	FIXED HUB	Naba, feststehend	Moyeu fixe	Mozzo fisso	Cudo o campana fija	1	
22	8875375	SLIDING SLEEVE	Schiebemuffe	Anneau baladeur	Manicotto scorrevole	Casquillo deslizante	1	
23	8877314	SYNCHRO RING	Synchronring	Anneau de synchro	Andello sincronizzatore	Anillo sincro.	1	
24	X8870370	CIRCLIP	Seegerring	Circlip	Anello elastico	Anillo elastico	40 DIA X 2.12MM	1
24	U8877531	CIRCLIP Kit	Sicherungsringe	Kit circlips	Corredo anelli elastici	Juego de circlips		1
24	X8870371	CIRCLIP	Seegerring	Circlip	Anello elastico	Anillo elastico	40 DIA X 2.07MM	1
24	X8870372	CIRCLIP	Seegerring	Circlip	Anello elastico	Anillo elastico	40 DIA X 2.MM	1
25	X8870305	NEEDLE ROLLER BRG	Nadelorollenlager	Roulement a aiguilles	Cuscinetto a rullin	Cojinette de ridillos en aguja	1	
26	X8872236	NEEDLE ROLLER BRG	Nadelorollenlager	Roulement a aiguilles	Cuscinetto a rullin	Cojinette de ridillos en aguja	1	

Y04133


Mainshaft



Part No:	English:	Deutsch:	Français:	Italiano:	Espanol:	Notes	QTY:	
27	8872217	2ND GEAR	Zahnrad 2. Gang	Pigon de 2eme	Ingranaggio albero principale	Engranaje 2a	1	
28	8877315	SYNCHRO FLANGE	SynchronFlansch	Bride de Synchro	Flangia sincronizzatore	Brida de sincronizacion	1	
29	8877440	SYNCHRO RING	Synchronring	Anneau de synchro	Andello sincronizzatore	Anillo sincro.	1	
30	8870444	SPRING	Feder	Ressort	Molla	Ballesta	3	
31	8870352	PLUNGER	Bolzen	Plongeur	Nottlino	Vastago	3	
32	X8870356	ROLLER	Verriegelungsrolle	Rouleau	Rulli	Rodillo	3	
33	8875129	FIXED HUB	Naba, feststehend	Moyeu fixe	Mozzo fisso	Cubo o campana fija	1	
34	8875373	SLIDING SLEEVE	Schiebemuffe	Anneau baladeur	Manicotto scorrevole	Casquillo deslizante	1	
35	8877440	SYNCHRO RING	Synchronring	Anneau de synchro	Andello sincronizzatore	Anillo sincro.	1	
36	8877315	SYNCHRO FLANGE	SynchronFlansch	Bride de Synchro	Flangia sincronizzatore	Brida de sincronizacion	1	
38	X8876597	CIRCLIP	Seegerring	Circlip	Anello elastico	Anillo elastico	65 X 4.15	1
38	X8876598	CIRCLIP	Seegerring	Circlip	Anello elastico	Anillo elastico	65 X 4.10	1
38	X8876599	CIRCLIP	Seegerring	Circlip	Anello elastico	Anillo elastico	65 X 4.05	1
38	X8876600	CIRCLIP	Seegerring	Circlip	Anello elastico	Anillo elastico	65 X 4.00	1
38	X8876601	CIRCLIP	Seegerring	Circlip	Anello elastico	Anillo elastico	65 X 3.95	1
38	U8876620	CIRCLIP Kit	Sicherungsringe	Kit circlips	Corredo anelli elastici	Juego de circlips	1	

Y04133


Mainshaft



Part No:	English:	Deutsch:	Français:	Italiano:	Espanol:	Notes	QTY:
39	8876603	1ST GEAR	Zahnrad 1. Gang	Pigon de 1eme	Ingranaggio albero principale	Engranaje 1a	1
40	X8870177	NEEDLE ROLLER BRG	Nadelrollenlager	Roulement a aiguilles	Cuscinetto a rullin	Cojinete de ridoillos en aguja	1
41	8876602	FIXED HUB	Naba, feststehend	Moyeu fixe	Mozzo fisso	Cubo o campana fija	1
42	X8870379	CIRCLIP	Seegerring	Circlip	Anello elastico	Anillo elastico	60 DIA X 2.05MM
42	X8870378	CIRCLIP	Seegerring	Circlip	Anello elastico	Anillo elastico	60 DIA X 2.10MM
42	X8870380	CIRCLIP	Seegerring	Circlip	Anello elastico	Anillo elastico	60 DIA X 2.00MM
42	U8882193	CIRCLIP Kit	Sicherungsringe	Kit circlips	Corredo anelli elastici	Juego de circlips	1
43	X8870178	NEEDLE ROLLER BRG	Nadelrollenlager	Roulement a aiguilles	Cuscinetto a rullin	Cojinete de ridoillos en aguja	1
44	8872013	REVERSE GEAR	Zahnrad Rückwärtsgang	Pignon m.arrière	Ingranaggio RM	Engranaje de ma	1
45	X8877197	BEARING	Nadelrollenlager	Roulement	Cuscinetto a rullin	Cojinete	1
46	8875385	TACHOGRAPH ROTOR	Tachorotor	Tachyrotor	Tachiroto	Velocidad rotor	1
47	D8870572	GRIT SHIELD	Schutzing	Cache-poussiere	Schermo antipolvere	Proteccion suciedad	1
48	8877859	COUPLING FLANGE	Anschlußflansch	Bride de raccordement	Flangia di accoppiamento	Brida de acoplamiento	1
49	X8870564	NUT	Mutter	Ecrou	Dado	Tuerca	1

Y04133


Countershaft



Part No:	English:	Deutsch:	Français:	Italiano:	Espanol:	Notes	QTY:
01	U8880062	LAYSHAFT ASSY	Vorgelegewelle	Arbre de renvoi	Contralbero	Eje secundario	1
02	X8875587	BEARING ASSY	Lagerbausatz	Roulement a aiguilles	Corredo cuscinetti	Conj. Cojinete	1
03	8872210	DISTANCE PIECE	Abstandsstück	Entretoise	Distanziale	Separador	1
04	X8875587	BEARING ASSY	Lagerbausatz	Roulement a aiguilles	Corredo cuscinetti	Conj. Cojinete	1
05	X8871538	CIRCLIP	Seegerring	Circlip	Anello elastico	Anillo elastico	40 DI X 1.87MM
05	X8871537	CIRCLIP	Seegerring	Circlip	Anello elastico	Anillo elastico	40 DI X 1.92MM
05	X8870372	CIRCLIP	Seegerring	Circlip	Anello elastico	Anillo elastico	40 DI X 2.02MM
05	X8870371	CIRCLIP	Seegerring	Circlip	Anello elastico	Anillo elastico	40 DI X 2.07MM
05	X8870370	CIRCLIP	Seegerring	Circlip	Anello elastico	Anillo elastico	40 DI X 2.12MM
05	X8871536	CIRCLIP	Seegerring	Circlip	Anello elastico	Anillo elastico	40 DI X 1.97MM
05	X8871540	CIRCLIP	Seegerring	Circlip	Anello elastico	Anillo elastico	40 DI X 1.77MM
05	X8871539	CIRCLIP	Seegerring	Circlip	Anello elastico	Anillo elastico	40 DI X 1.82MM
05	U8877534	CIRCLIP Kit	Sicherungsringe	Kit circlips	Corredo anelli elastici	Juego de circlips	1
06	U8877535	SHIM KIT	Ausgl.schei.kit	Kit cale	Distanziale	Kit de relleno	1
07	8875879	SPACER	Distanzstück	Entretoise	Distanziale	Separador	2MM

Y04133

Reverse Idler




6 SR-07

Part No:	English:	Deutsch:	Français:	Italiano:	Espanol:	Notes	QTY:
01 8880069	REVERSE IDLER SHAFT	Rückwärts Welle	Axe de pignon de renvoi de ma	Albero, Ingranaggio rinvio RM	Eje intermedio de MA		1
02 8872173	REVERSE IDLER GEAR	Rückwärtsgang-Umkehrad	Pignon de Renvoi de Marche A	Complessivo Ingranaggio Rin	Engranaje Inversor MA		1
03 8870343	THRUST WASHER	Druckscheibe	Rondella de pousse	Rondella di sprinta	Arandela de empuje		2
04 X8872478	NEEDLE ROLLER BRG	Nadelorollenlager	Roulement a aiguilles	Cuscinetto a rullin	Cojinete de rodillos en aguja		2
05 8872479	SPACER	Distanzstück	Entretoise	Distanziale	Separador	4MM	1

Y04133

Selector Assy




6 SR-08

Part No:	English:	Deutsch:	Français:	Italiano:	Espanol:	Notes	QTY:
00	U8875904	SELECTOR ASSY	Wählhebel	Sélecteur assemblé	selettore completo	Conjunto selector	1
01	8874835	SELECTOR SHAFT	Schaltchiene	Axe du sélecteur	Chiavetta selettore	Llave selectore	1
02	8876394	SELECTOR KEY	Schalklinke	Reglette de selection	Chiavetta selettore	Llava selectora	1
03	8876395	INTERLOCK KEY	Verriegelungsklinke	Reglette de verrouillage	Chiavetta bloccaggio	Llave interenclavamiento	1
04	8875503	SHIFT FORK	Gangschaltgabel	Fourchette commande de vit.	Forca	Horquilla	1
05	8880805	SHIFT FORK	Gangschaltgabel	Fourchette commande de vit.	Forca	Horquilla	1
06	8875501	SHIFT FORK	Gangschaltgabel	Fourchette commande de vit.	Forca	Horquilla	1
07	8873691	LOCATION SCREW SEL. B	Schraube	Vis	Vite	Tornillo	M10 X 23 HEX HD
08	8874754	SELECTOR BLOCK	Schaltblock	Bloc de sélecteur	Blocco selezione	Bloque selector	1
09	X8870277	DOWEL	Dübel, stift	Goujon	Spina	Cabilla	DIA 10.0 X 34.6
10	8875500	SHIFT FORK	Gangschaltgabel	Fourchette commande de vit.	Forca	Horquilla	1

Y04133


LRC



Part No:	English:	Deutsch:	Français:	Italiano:	Espanol:	Notes	QTY:	
00	U8875935	LRC ASSY	Fernschaltung	Commane à Distance	Complessivo Comando a Dist	Conjunto Control Remoto	LH VERTICAL	1
01	8874744	HOUSING	Gehäuse	Corps	Scatola	Envuelta		1
03	8874797	SHIFT ROD	Schaltung	Levier rapport	Tirante regola	Varilla regulad.		1
04	DX8871502	PLUG	Stopfen	Bouchon	Tappo	Tapón	M16 X 1.5	1
05	X8880470	WASHER	Scheibe	Rondelle	Rondella	Arrandela	M16 DOWTY SEAL	1
06	X8880846	ELBOW	Knie	Coude	Addatore	Cojinete	1/8 NPTF X 1/4"	1
09	8877658	LEVER	Hebel	Levier	Leva	Palanca		1
10	X8871378	DOWEL	Dübel, stift	Goujon	Spina	Cabilla		1
11	DX11245	WASHER	Scheibe	Rondelle	Rondella	Arrandela	M10 X 2MM	7
12	DMX-3-1001	SPRING WASHER	Federscheibe	Rondelle grower	Rondella di sicurezza	Arandela elásti	M10 X2.2MM	4
13	DMX-8-1005	SCREW	Schraube	Vis	Vite	Tornillo	M10 X 55	4
14	DMX-8-1007	BOLT	Schraubbolzen	Boulon	Vite	Perno	M10 X 50 FLG HD	1
15	8876052	LEVER	Hebel	Levier	Leva	Palanca		1
17	MX-9-1005	NUT	Mutter	Ecrou	Dado	Tuerca	M10	1
18	X8875259	BOOT ACCORDION	Faltenbalg	Manchon protectour	Manicotto de gomma	Manillar de caucho		1
19	X8881481	OIL SEAL 25.35.7	Öldichtung	Joint d'étanchéité d'huile	Tenuta	Retén de aceite		1
20	X8871377	BUSH	Buchse	Bague	Boccola	Casquillo		1

Y04133

LRC




6 SR-09

Part No:	English:	Deutsch:	Français:	Italiano:	Espanol:	Notes	QTY:
21	DX8871486	PLUG	Stopfen	Bouchon	Tappo	Tapón	1
22	8875415	PLUNGER	Bolzen	Plongeur	Nottlino	Vastago	1
23	8870587	SPRING	Feder	Ressort	Molla	Ballesta	1
24	8870590	GASKET	Dichtung	Joint	Guarnizione	Junta	1
25	D8870259	COVER-DETENT	Deckel	Couvercle de verrouillage	Coperchio fermo	Tapa reten	1
26	DMX-3-0801	SPRING WASHER	Federscheibe	Rondelle grower	Rondella di sicurezza	Arandela elásti	M8
27	DMX-8-0801	SCREW	Schraube	Vis	Vite	Tornillo	M8 X 14 HEX HD
29	X8874450	CIRCLIP	Seegerring	Circlip	Anello elastico	Anillo elastico	1
30	8876566	SPRING RETAINER	Federfuhring	Retenue de Ressort	Retenzione di molla	Retencion con resorte	1
31	8873736	SPRING	Feder	Ressort	Molla	Ballesta	1
33	8876566	SPRING RETAINER BOOS	Federfuhring	Retenue de Ressort	Retenzione di molla	Retencion con resorte	1
34	X8874450	CIRCLIP	Seegerring	Circlip	Anello elastico	Anillo elastico	1
35	DMX-3-0801	SPRING WASHER	Federscheibe	Rondelle grower	Rondella di sicurezza	Arandela elásti	M8
36	DMX-8-0803	SCREW	Schraube	Vis	Vite	Tornillo	M8 X 2.5 HEX HD
37	8876041	END COVER	Enddeckel	Couvercle d'extrémité	coperchio finale	Tapa final	1
38	8873734	END COVER GASKET	Dichtung	Joint	Guarnizione	Junta	1

Y04133

Speedo Housing Assy



Part No:	English:	Deutsch:	Français:	Italiano:	Espanol:	Notes	QTY:
00	U8874938	SPEEDO HOUSING ASSY	Tachometergehäuse	Boitier de Tachymetre	Scatola Indicatore Velocita	Envuelta del Velocimetro	1
01	8877755	SPEEDO HOUSING	Tachometergehäuse	Boitier de tachymetre	Scatola indicatore velocita	Envuelta del velocimetro	1
03	X8874937	PLUG	Stopfen	Bouchon	Tappo	Tapón	1
06	DMX-8-1003	SCREW	Schraube	Vis	Vite	Tornillo	M10 X 35 HEX HD 2
07	X13711	OIL SEAL	Öldichtung	Joint d'étanchéité d'huile	Tenuta	Retén de aceite	1
08	DMX-8-1007	BOLT	Schraubbolzen	Boulon	Vite	Perno	M10 X 50 FLG HD 1
14	DMX-8-1020	SCREW	Schraube	Vis	Vite	Tornillo	M10 x 35 1