

Eaton® Power Xpert™ 9395 UPS Spare Parts Kits

9395 480V 275 kVA ISBM Spare Parts Kits

Table 1. 9395 480V 275 kVA ISBM Spare Parts Kit Numbers

Kit Part Number	Kit Description
106711251	"A" Spares 9395 480V 275 kVA ISBM
106711252	"B" Spares 9395 480V 275 kVA ISBM
106711253	"C" Spares 9395 480V 275 kVA ISBM
106711254	"D" Spares 9395 480V 275 kVA ISBM

Table 2. 9395 480V 275 kVA ISBM Spare Parts Kits Contents

Part Number	Component Description	Quantity per Spare Parts Kit			
		A	B	C	D
3989190	SILICONE THERMAL COMPOUND 57GR	1	1		
101073828	9395 STATIC SWITCH BOARD	1	1		
103003706	DISPLAY ASM INDIGO	1			
152602110	HARNESS, PMIP32 ID	1			
120105088-001	CAP, AL ELECT, 64000UF, 63V	1			
P-128000012-025	FUSE 3A 600V 13/32" TIME-DELAY	3	3	3	3
128307027-001	FUSE, SEMICOND, 700A 700V	3	3	3	3
129101001-006	PAD THERMAL, 4.88 X 2.36	3	3		
143327009-001	SCR, 425A 1600V DUAL MODU	3	3		
151101079-001	FAN, 120 MM X 38 MM, 180 CFM	1	1		
180190078-087	BOLT HEX HEAD M10 X 25	9	9		
180500036-080	WASHER FLAT M8 HD	9	9		
180500037-080	WASHER LK M8 CONICAL SPRNG	9	9		
744-00455	MINI CSB COATING ASSY 9395/ETN S.P.P.	1	1	1	
744-B0223	ISBM PS ASSY TRIDENT 9395/ETN S.P.P.	2	1		
744-B1029	NTER 266R1 COATING ASSY 9395P/ETN S.P.P.	1			
744-B1031	MAUI IOF ASSY 9395P/ETN S.P.P.	1			
744-B1055	HRS COATED CNTL BRD ASSY 9395/ETN S.P.P.	1	1	1	



9395 480V 550 kVA ISBM Spare Parts Kits

Table 3. 9395 480V 550 kVA ISBM Spare Parts Kits

Kit Part Number	Kit Description
106711259	"A" Spares 9395 480V 550 kVA ISBM
106711260	"B" Spares 9395 480V 550 kVA ISBM
106711261	"C" Spares 9395 480V 550 kVA ISBM
106711262	"D" Spares 9395 480V 550 kVA ISBM

Table 4. 9395 480V 550 kVA ISBM Spare Parts Kits Contents

Part Number	Component Description	Quantity per Spare Parts Kit			
		A	B	C	D
1026790	THYRI MOD 500A 1600V	6	6		
1026820	FUSE 1400A 660V UR SQB M12	3	3	3	3
3989190	SILICONE THERMAL COMPOUND 57GR	1	1		
101073828	9395 STATIC SWITCH BOARD	1	1		
103003706	DISPLAY ASM INDIGO	1			
152602110	HARNESS, PMIP32 ID	1			
120105088-001	CAP, AL ELECT, 64000UF, 63V	1			
128304038-048	FUSE MIDGET 600VAC 3 A		3		
P-128000012-025	FUSE 3A 600V 13/32" TIME-DELAY	3	3	3	3
129101001-006	PAD THERMAL, 4.88 X 2.36	6	6		
151101091-001	FAN, 172X150X51 MM, 415 CFM	2	2		
744-00455	MINI CSB COATING ASSY 9395/ETN S.P.P.	1	1	1	
744-B0223	ISBM PS ASSY TRIDENT 9395/ETN S.P.P.	2	1		
744-B1029	NTER 266R1 COATING ASSY 9395P/ETN S.P.P.	1			
744-B1031	MAUI IOF ASSY 9395P/ETN S.P.P.	1			
744-B1055	HRS COATED CNTL BRD ASSY 9395/ETN S.P.P.	1	1	1	

9395 400/480V 825 kVA MSS ISBM Spare Parts Kits

Table 5. 9395 400/480V 825 kVA MSS ISBM Spares Kits

Kit Part Number	Component Description
106711271	"A" Spares 9395 400/480 825 kVA MSS ISBM
106711275	"B" Spares 9395 400/480 825 kVA MSS ISBM
106711279	"C" Spares 9395 400/480 825 kVA MSS ISBM
106711283	"D" Spares 9395 400/480 825 kVA MSS ISBM

Table 6. 9395 400/480V 825 kVA MSS ISBM Spare Parts Kits Contents

Part Number	Component Description	Quantity per Spare Parts Kit			
		A	B	C	D
1026790	THYRI MOD 500A 1600V	3			
1027174	PCBAS 9395 RFI BOARD	2	2		
101073828	9395 STATIC SWITCH BOARD	1	1		
103003706	DISPLAY ASM INDIGO	1	1		
149308206	XFORMER, CONTROL, 1KVA	1			
149502133	CURRENT TRANSFORMER 2000:1	3			
120105088-001	CAP, AL ELECT, 64000UF, 63V	2			
P-128000012-025	FUSE 3A 600V 13/32" TIME-DELAY	4	6	6	6
P-128000012-030	FUSE 5A 600V 13/32" TIME-DELAY	2			
128307029-002	FUSE, 2000 A, 690 V, HIGH SPEED, SQUARE BODY	6	6	6	6
140905045-002	RELAY, 10 A, 48 VDC COIL, DPDT	2			
744-00455	MINI CSB COATING ASSY 9395/ETN S.P.P.	1	1	1	
744-B0223	ISBM PS ASSY TRIDENT 9395/ETN S.P.P.	2	2	1	
744-B1029	NTER 266R1 COATING ASSY 9395P/ETN S.P.P.	1	1		
744-B1031	MAUI IOF ASSY 9395P/ETN S.P.P.	1	1		
744-B1055	HRS COATED CNTL BRD ASSY 9395/ETN S.P.P.	1	1	1	1

9395 400/480V 825 kVA ISBM CSS Spare Parts Kits

Table 7. 9395 400/480V 825 kVA ISBM CSS Spares Kits

Kit Part Number	Component Description
106711273	"A" Spares 9395 400/480 825 kVA ISBM CSS
106711277	"B" Spares 9395 400/480 825 kVA ISBM CSS
106711281	"C" Spares 9395 400/480 825 kVA ISBM CSS
106711285	"D" Spares 9395 400/480 825 kVA ISBM CSS

Table 8. 9395 400/480V 825 kVA ISBM CSS Spare Parts Kits Contents

Part Number	Component Description	Quantity per Spare Parts Kit			
		A	B	C	D
1027174	PCBAS 9395 RFI BOARD	2			
3989190	SILICONE THERMAL COMPOUND 57GR	1	1	1	1
103003706	DISPLAY ASM INDIGO	1	1	1	
103007339	ASSY, DC CAPS 825/1100 CSS	1			
103007416	SUBAS 3P825 STATIC SWITCH 400V (RPO VERSION)	1			
103007417	SUBASSY, FAN PAN, 9395 825 CSS	1			
129400075	PAD, THERMAL INTERFACE	18	18	18	10
101073903-002	9395 1100 CSS STSW BOARD	1	1	1	
P-128000012-025	FUSE 3A 600V 13/32" TIME-DELAY	12	12	6	6
128307029-002	FUSE, 2000 A, 690 V, HIGH SPEED, SQUARE BODY	12	12	6	6
151101091-001	FAN, 172X150X51 MM, 415 CFM		4	2	1
174650589-001	BAG, POLYETHYLENE, DRAWSTRING,	2	2		
180500034-625	M6 X 25 SCKT HD CAP SCR	24	24	24	16
744-00455	MINI CSB COATING ASSY 9395/ETN S.P.P.	1	1	1	1
744-B0223	ISBM PS ASSY TRIDENT 9395/ETN S.P.P.	2	2	1	1
744-B1029	NTER 266R1 COATING ASSY 9395P/ETN S.P.P.	1	1		
744-B1032	MAUI PS TIE ASSY 9395P/ETN S.P.P.	1	1		
744-B1055	HRS COATED CNTL BRD ASSY 9395/ETN S.P.P.	1	1	1	1
P-143000024	Thyristor, SEMIKRON SKET 801 819A 1800V	6	6	6	4

9395 480V 1100 kVA CSS ISBM Spare Parts Kits

Table 9. 9395 480V 1100 kVA CSS ISBM Spares Kits

Kit Part Number	Component Description
106711310	"A" Spares 9395 480 825 kVA ISBM CSS
106711312	"B" Spares 9395 480 825 kVA ISBM CSS
106711314	"C" Spares 9395 480 825 kVA ISBM CSS
106711316	"D" Spares 9395 480 825 kVA ISBM CSS

Table 10. 9395 480V 1100 kVA CSS ISBM Spare Parts Kits Contents

Part Number	Component Description	Quantity per Spare Parts Kit			
		A	B	C	D
1027174	PCBAS 9395 RFI BOARD	2	1		
103003706	DISPLAY ASM INDIGO	1	1	1	1
103007183	ASSY, ST SW 2000A	3	3	2	1
103007184	ASSY, ISBM CSS FAN	1			
149502133	CURRENT TRANSFORMER 2000:1	6			
152601536	PLUG, RJ45 TERMINATOR	2	2	2	
120105088-001	CAP, AL ELECT, 64000UF, 63V	2	6		
120110008-001	CAP, ALUM ELECT, 5800 UF, 300V	2	6		
P-128000012-025	FUSE 3A 600V 13/32" TIME-DELAY	6	5	6	6
128307029-003	FUSE, 3000 A, 690 V, HIGH SPEED, SQUARE BODY	6	1	6	6
151101091-001	FAN, 172X150X51 MM, 415 CFM		3	4	3
744-00455	MINI CSB COATING ASSY 9395/ETN S.P.P.	1	1	1	1
744-B0223	ISBM PS ASSY TRIDENT 9395/ETN S.P.P.	4	1	2	1
744-B1029	NTER 266R1 COATING ASSY 9395P/ETN S.P.P.	1	1	1	1
744-B1032	MAUI PS TIE ASSY 9395P/ETN S.P.P.	1		1	1
744-B1055	HRS COATED CNTL BRD ASSY 9395/ETN S.P.P.	2		1	1

9395 400/480V 1100 kVA MSS ISBM Spare Parts Kits

Table 11. 9395 400/480V 1100 kVA MSS ISBM Spare Parts Kits

Kit Part Number	Component Description
106711302	"A" Spares 9395 400/480V 1100 kVA MSS ISBM
106711304	"B" Spares 9395 400/480V 1100 kVA MSS ISBM
106711306	"C" Spares 9395 400/480V 1100 kVA MSS ISBM
106711308	"D" Spares 9395 400/480V 1100 kVA MSS ISBM

Table 12. 9395 400/480V 1100 kVA MSS ISBM Spare Parts Kits Contents

Part Number	Component Description	Quantity per Spare Parts Kit			
		A	B	C	D
1027174	PCBAS 9395 RFI BOARD	2	2		
103003706	DISPLAY ASM INDIGO	1	1		
149308206	XFORMER, CONTROL, 1KVA	1			
149502133	CURRENT TRANSFORMER 2000:1	3			
101073903-002	9395 1100 CSS STSW BOARD	1	1		
120105088-001	CAP, AL ELECT, 64000UF, 63V	2			
P-128000012-022	FUSE 2.25A 600V 13/32" TIME-DELAY	3	3	3	3
P-128000012-025	FUSE 3A 600V 13/32" TIME-DELAY	4	6	6	6
P-128000012-030	FUSE 5A 600V 13/32" TIME-DELAY	2			
128307029-003	FUSE, 3000 A, 690 V, HIGH SPEED, SQUARE BODY	6	6	6	6
140905045-002	RELAY, 10 A, 48 VDC COIL, DPDT	2			
180500034-625	M6 X 25 SCKT HD CAP SCR	8			
744-00455	MINI CSB COATING ASSY 9395/ETN S.P.P.	1	1	1	
744-B0223	ISBM PS ASSY TRIDENT 9395/ETN S.P.P.	2	2	2	
744-B1029	NTER 266R1 COATING ASSY 9395P/ETN S.P.P.	1	1		
744-B1031	MAUI IOF ASSY 9395P/ETN S.P.P.	1	1		
744-B1055	HRS COATED CNTL BRD ASSY 9395/ETN S.P.P.	1	1	1	1
P-143000024	Thyristor, SEMIKRON SKET 801 819A 1800V	2			

9395 400V/480V UPM Spare Part Kits

Table 13. 9395 400/480V UPM Spare Parts Kits

Kit Part Number	Component Description
106711267	"A" 9395 400/480V UPM Spare Parts Kit
106711268	"B" 9395 400/480V UPM Spare Parts Kit
106711269	"C" 9395 400/480V UPM Spare Parts Kit
106711270	"D" 9395 400/480V UPM Spare Parts Kit

Table 14. 9395 400/480V UPM Spare Parts Kits Contents

Part Number	Component Description	Quantity per Spare Parts Kit			
		A	B	C	D
1028001	PCBAS 3P275 BATT FILTER BOARD	1			
1028005	RESIS 2R2 150W 10%	1			
127250448	INSULATOR, MODULE FRONT	2	2		
127250449	INSULATOR, MODULE SIDE	4	4		
101073735-001	PCBAS, Leg Mod, Pent w/100A	4	4		
101073831-001	PCBAS, Power Supply, 850W	2	2	2	
120105088-001	CAP, AL ELECT, 6400UF, 63V	1			
120311025-002	CAPACITOR, METALLIZED POLYPROPYLENE, 370 VAC	18			
120314020-002	CAPACITOR, 45UF, 600V, D-STUD	7			
P-128000012-025	FUSE 3A 600V 13/32" TIME-DELAY	5	5	5	3
128307025-004	FUSE 450A 700VAC M8 45MM SQ	8	8	8	8
128307027-001	FUSE, SEMICOND, 700A 700V	2	2	2	2
151101091-001	FAN, 172X150X51 MM, 415 CFM	8	8	8	4
180190118-015	BOLT HEX FL LK M4 X 12	1			
744-B1055	HRS COATED CNTL BRD ASSY 9395/ETN S.P.P.	1	1	1	
744-B1056	HRS COATED UPM NTER ASSY 9395/ETN S.P.P.	1	1	1	

Table 15. 9395 400/480V UPM (SEMIKRON) Spare Parts Kits P-106000084

Part Number	Component Description	Qty
1027173	SUBAS 3P275 POWER MOD SEMIKRON	4
1028001	PCBAS 3P275 BATT FILTER BOARD	1
1028005	RESIS 2R2 150W 10%	1
127250448	INSULATOR, MODULE FRONT	2
127250449	INSULATOR, MODULE SIDE	4

Table 15. 9395 400/480V UPM (SEMIKRON) Spare Parts Kits P-106000084 (Continued)

Part Number	Component Description	Qty
101073831-001	PCBAS, Power Supply, 850W	2
120105088-001	CAP, AL ELECT, 6400UF, 63V	1
120311025-002	CAPACITOR, METALLIZED POLYPROPYLENE, 370 VAC	18
120314020-002	CAPACITOR, 45UF, 600V, D-STUD	7
P-128000012-025	FUSE 3A 600V 13/32" TIME-DELAY	5
128307025-004	FUSE 450A 700VAC M8 45MM SQ	8
128307027-001	FUSE, SEMICOND, 700A 700V	2
151101091-001	FAN, 172X150X51 MM, 415 CFM	8
180190118-015	BOLT HEX FL LK M4 X 12	1
744-B1055	HRS COATED CNTL BRD ASSY 9395/ETN S.P.P.	1
744-B1056	HRS COATED UPM NTER ASSY 9395/ETN S.P.P.	1



P-164000890 01