

# Eaton® Power Xpert™ 9395P UPS Spare Parts Kits

## 9395P 380–480V 300 kW ISBM Spare Parts Kits

**Table 1. 9395P 380–480V 300 kW ISBM Spare Parts Kits**

Kit Part Number	Component Description
P-106000156	"A" 380–480V 300 kW ISBM Spare Parts Kit
P-106000157	"B" 380–480V 300 kW ISBM Spare Parts Kit
P-106000158	"C" 380–480V 300 kW ISBM Spare Parts Kit

**Table 2. 9395P 380–480V 300 kW ISBM Spare Parts Kits Contents**

Part Number	Component Description	Quantity per Spare Parts Kit		
		A	B	C
128307027-001	FUSE, SEMICOND, 700A 700V	12	1	6
129101001-006	PAD THERMAL, 4.88 X 2.36	6	6	
143327009-001	SCR, 425A 1600V DUAL MODU	6	6	
151101079-001	FAN, 120 MM X 38 MM, 180 CFM	4	4	2
744-00455	MINI CSB COATING ASSY 9395/ETN S.P.P.	1	1	1
744-00458	MAUI 480V CSB COAT ASSY 13X2/ETN S.P.P.	1		
744-B0223	ISBM PS ASSY TRIDENT 9395/ETN S.P.P.	1	1	1
744-B0225	ISBM STS ASSY TRIDENT 9395/ETN S.P.P.	1	1	1
744-B1029	NTER 266R1 COATING ASSY 9395P/ETN S.P.P.		1	1
744-B1055	HRS COATED CNTL BRD ASSY 9395/ETN S.P.P.	1	1	1
P-116000048	HMI DISPLAY, 10", BEIJER	1		
P-128000012-025	FUSE 3A 600V 13/32" TIME-DELAY	12	12	6
PSG60F24RM	PSG POWER SUPPLY THREE PHASE 60W 400-500VAC INPUT, 24VDC/2.5A OUTPUT	1		



## 9395P 575/600V 300 and 600 kW ISBM Spare Parts Kits

**Table 3. 9395P 575/600V 300 and 600 kW ISBM Spare Parts Kits**

Kit Part Number	Component Description
P-103003233	"A" 575/600V 300 and 600 kW ISBM Spare Parts Kit
P-103003234	"B" 575/600V 300 and 600 kW ISBM Spare Parts Kit
P-103003235	"C" 575/600V 300 and 600 kW ISBM Spare Parts Kit

**Table 4. 9395P 575/600V 300 and 600 kW ISBM Spare Parts Kits Contents**

Part Number	Component Description	Quantity per Spare Parts Kit		
		A	B	C
149502122	CURRENT TRANSFORMER 1000:1	6		
152601536	PLUG, RJ45 TERMINATOR	1	1	1
120105088-001	CAP, AL ELECT, 64000UF, 63V	2		
129101001-006	PAD THERMAL, 4.88 X 2.36	3	3	3
151101091-001	FAN, 172X150X51 MM, 415 CFM	2	2	2
730-80452	STS600 ASSY 9395P/ETN	1	1	1
730-80454	EMI600 ASSY 9395P/ETN	1	1	
730-80455	EMISURG600 ASSY 9395P/ETN	1	1	
744-00455	MINI CSB COATING ASSY 9395/ETN S.P.P.	1	1	1
744-00458	MAUI 480V CSB COAT ASSY 13X2/ETN S.P.P.	1		
744-B0223	ISBM PS ASSY TRIDENT 9395/ETN S.P.P.		3	
744-B1029	NTER 266R1 COATING ASSY 9395P/ETN S.P.P.		1	1
744-B1055	HRS COATED CNTL BRD ASSY 9395/ETN S.P.P.	1	1	1
744-F0338	MAUI IOF 600V ASSY 9395P/ETN S.P.P.			1
P-116000048	HMI DISPLAY, 10", BEIJER	1		
P-128000012-025	FUSE 3A 600V 13/32" TIME-DELAY	6	6	6
P-128000034	Fuse, 1000A Square Body	3	3	3
P-143000027	Thyristor, 2200V 430A	3	3	3

## 9395P 380–480V 600 kW ISBM Spare Parts Kits

**Table 5. 9395P 380–480V 600 kW ISBM Spare Parts Kits**

Kit Part Number	Component Description
P-106000159	"A" 380–480V 600 kW ISBM Spare Parts Kit
P-106000160	"B" 380–480V 600 kW ISBM Spare Parts Kit
P-106000161	"C" 380–480V 600 kW ISBM Spare Parts Kit

**Table 6. 9395P 380–480V 600 kW ISBM Spare Parts Kits Contents**

Part Number	Component Description	Quantity per Spare Parts Kit		
		A	B	C
1026790	THYRI MOD 570A 1600V DUAL	6	6	6
1026820	FUSE 1400A 660V UR SQB M12		6	6
1027174	PCBAS 9395 RFI BOARD	2	1	
149502122	CURRENT TRANSFORMER 1000:1	6		
152601536	PLUG, RJ45 TERMINATOR	1	1	1
120105088-001	CAP, AL ELECT, 64000UF, 63V	2		
129101001-006	PAD THERMAL, 4.88 X 2.36	6	6	6
151101091-001	FAN, 172X150X51 MM, 415 CFM		5	4
744-00455	MINI CSB COATING ASSY 9395/ETN S.P.P.	1	1	1
744-00458	MAUI 480V CSB COAT ASSY 13X2/ETN S.P.P.	1		
744-B0223	ISBM PS ASSY TRIDENT 9395/ETN S.P.P.		3	2
744-B1029	NTER 266R1 COATING ASSY 9395P/ETN S.P.P.		1	1
744-B1055	HRS COATED CNTL BRD ASSY 9395/ETN S.P.P.	1	1	1
744-F0338	MAUI IOF 600V ASSY 9395P/ETN S.P.P.			1
P-116000048	HMI DISPLAY, 10", BEIJER	1		
P-128000012-025	FUSE 3A 600V 13/32" TIME-DELAY	6	6	6
PSG60F24RM	PSG POWER SUPPLY THREE PHASE 60W 400-500VAC INPUT, 24VDC/2.5A OUTPUT	1		

## 9395P 480/600V 900 kW ISBM Spare Parts Kits

**Table 7. 9395P 480/600V 900 kW ISBM Spare Parts Kits**

Kit Part Number	Component Description
P-106000094	"A" 480/600V 900 kW ISBM Spare Parts Kit
P-106000095	"B" 480/600V 900 kW ISBM Spare Parts Kit
P-106000096	"C" 480/600V 900 kW ISBM Spare Parts Kit

**Table 8. 9395P 480/600V 900 kW ISBM Spare Parts Kits Contents**

Part Number	Component Description	Quantity per Spare Parts Kit		
		A	B	C
129400075	PAD, THERMAL INTERFACE	6	6	
128307029-002	FUSE, 2000 A, 690 V, HIGH SPEED, SQUARE BODY	12	1	
151101091-001	FAN, 172X150X51 MM, 415 CFM	4	4	2
180500034-625	M6 X 25 SCKT HD CAP SCR	24	24	
744-00455	MINI CSB COATING ASSY 9395/ETN S.P.P.	1	1	1
744-00458	MAUI 480V CSB COAT ASSY 13X2/ETN S.P.P.	1		
744-B0223	ISBM PS ASSY TRIDENT 9395/ETN S.P.P.	3	1	1
744-B0229	OVER 825 STS ASSY 9395TRIDENT/ETN S.P.P.	1	1	1
744-B1029	NTER 266R1 COATING ASSY 9395P/ETN S.P.P.	1	1	1
744-B1032	MAUI PS TIE ASSY 9395P/ETN S.P.P.	1	1	
744-B1055	HRS COATED CNTL BRD ASSY 9395/ETN S.P.P.	1	1	1
P-116000048	HMI DISPLAY, 10", BEIJER	1		
P-128000012-025	FUSE 3A 600V 13/32" TIME-DELAY	12	12	6
P-143000024	Thyristor, SEMIKRON SKET 801 819A 1800V	6	6	
PSG60F24RM	PSG POWER SUPPLY THREE PHASE 60W 400-500VAC INPUT, 24VDC/2.5A OUTPUT	1		

## 9395P 480/600V 1200 kW ISBM Spare Parts Kits

**Table 9. 9395P 480/600V 1200 kW ISBM Spare Parts Kits**

Kit Part Number	Component Description
P-106000097	"A" 480/600V 1200 kW ISBM Spare Parts Kit
P-106000098	"B" 480/600V 1200 kW ISBM Spare Parts Kit
P-106000099	"C" 480/600V 1200 kW ISBM Spare Parts Kit

**Table 10. 9395P 480/600V 1200 kW ISBM Spare Parts Kits Contents**

Part Number	Component Description	Quantity per Spare Parts Kit		
		A	B	C
1027174	PCBAS 9395 RFI BOARD	2		
103007183	ASSY, ST SW 2000A	3	3	3
103007184	ASSY, ISBM CSS FAN	1		
149502133	CURRENT TRANSFORMER 2000:1	6		
152601536	PLUG, RJ45 TERMINATOR	2	2	2
120105088-001	CAP, AL ELECT, 64000UF, 63V	2		
120110008-001	CAP, ALUM ELECT, 5800 UF, 300V	2		
128307029-003	FUSE, 3000 A, 690 V, HIGH SPEED, SQUARE BODY	6	6	6
151101091-001	FAN, 172X150X51 MM, 415 CFM		5	4
730-80454	EMI600 ASSY 9395P/ETN		1	
744-00455	MINI CSB COATING ASSY 9395/ETN S.P.P.	1	1	1
744-00458	MAUI 480V CSB COAT ASSY 13X2/ETN S.P.P.	1		
744-B0223	ISBM PS ASSY TRIDENT 9395/ETN S.P.P.	3	3	2
744-B1029	NTER 266R1 COATING ASSY 9395P/ETN S.P.P.	1	1	1
744-B1032	MAUI PS TIE ASSY 9395P/ETN S.P.P.	1	1	1
744-B1055	HRS COATED CNTL BRD ASSY 9395/ETN S.P.P.	2	1	1
P-116000048	HMI DISPLAY, 10", BEIJER	1		
P-128000012-025	FUSE 3A 600V 13/32" TIME-DELAY	6	6	6
PSG60F24RM	PSG POWER SUPPLY THREE PHASE 60W 400-500VAC INPUT, 24VDC/2.5A OUTPUT	1		

## 9395P Universal UPM Spare Parts Kits

**Table 11. 9395P Universal UPM Spare Parts Kits**

Kit Part Number	Component Description
P-106000171	"A" Universal UPM Spare Parts Kit
P-106000172	"B" Universal UPM Spare Parts Kit
P-106000173	"C" Universal UPM Spare Parts Kit

**Table 12. 9395P Universal UPM Spare Parts Kits Contents**

Part Number	Component Description	Quantity per Spare Parts Kit		
		A	B	C
123110015-002	CONTACTOR, 429 A, 1000 VAC, 3 POLE	1		
123110016-002	CONT, 612 A, 1000 VAC, 3 POLE	1		
123112015-001	CONTACTOR, 857 A, 1000 VAC, 3 POLE	1		
128307025-004	FUSE 450A 700VAC M8 45MM SQ		8	8
730-80488	INTERFACE COATING ASSY 9395P/ETN	1	1	1
730-80489	CONTROL COATING ASSY 9395P/ETN	1	1	1
730-80502	LEG MODULE ASSY 9395P/ETN PACK	1	1	
744-A3916	BAT BAL PM BOARD ASSY 9395/ETN TPE S.P.P	1		
744-F0138	SPS CB ASSY 9395(TRI)/ETN S.P.P.	2	1	1
P-103000871	FAN PAN ASSEMBLY	1	1	1
P-103001405	DC CAP PAN ASSEMBLY	1		
P-128000012-025	FUSE 3A 600V 13/32" TIME-DELAY	5	5	5





P-164000892 01