



# Bussmann series Power Module™ Switch replacement parts




### Field replaceable Power Module switch parts

Component	Description	Part no.
1	200 A or less switch	PSXRPLSW
2	Main fuse	LPJ-(amp)SP
3	Latch-draw pull	52-2394*
4	Microswitch	V7-1B17D8-048*
5	Legend plate power ON 22 mm	M22-XST-GB6*
6	Legend plate normal-test 22 mm	M22-XST-ETCH* and M22S-ST-X*
7	Replacement keys	M22-ES-MS1*
8	Handle assembly	53-6488*
9	Red handle knob	53-2601*
10	Yellow "Bussmann" nameplate	30-44348*

\* These cannot be ordered as Bussmann series part numbers. To order a replacement part, contact your local Bussmann series product sales representative or the Customer Satisfaction team, toll-free at 855-287-7626, and they will place your order with the component part supplier.

**See page 2 for more assembly components.**



**Field replaceable Power Module switch parts**

Component	Description	Part no.
11	Pilot light 120 V - Red	M22-L-R-230R*
	Pilot light 120 V - Green	M22-L-R-230G*
	Pilot light 120 V - White	M22-L-R-230W*
12	Two-position key switch	M22S-WS*
13	Contact Block	M22-K10*
14	Terminal block end cover	XBACUT10*
	Terminal block	XBUT4*
15	Ice cube relay - 120 Vac coil	D5RR3A*
	Ice cube relay - 24 Vdc coil	D5PR3T1-A3*
16	D5 relay socket with screw terminals	DSPA2*
17	Transformer primary fuses	FNQ-R-(amp)
18	Transformer supplementary fuse	FNM-(amp)
19	Transformer 208/240/480 V	C0100E5EFB*
	Transformer 600 V	C0100E3CFB*

\* These cannot be ordered as Bussmann series part numbers. To order a replacement part, contact your local Bussmann series product sales representative or the Customer Satisfaction team, toll-free at 855-287-7626, and they will place your order with the component part supplier.

The only controlled copy of this data sheet is the electronic read-only version located on the Eaton network drive. All other copies of this document are by definition uncontrolled. This bulletin is intended to clearly present comprehensive product data and provide technical information that will help the end user with design applications. Eaton reserves the right, without notice, to change design or construction of any products and to discontinue or limit distribution of any products. Eaton also reserves the right to change or update, without notice, any technical information contained in this bulletin. Once a product has been selected, it should be tested by the user in all possible applications.

**Eaton**  
1000 Eaton Boulevard  
Cleveland, OH 44122  
Eaton.com

Bussmann Division  
114 Old State Road  
Ellisville, MO 63021  
United States  
Eaton.com/bussmannseries

© 2018 Eaton  
All Rights Reserved  
Printed in USA  
Publication No. 10669 — BU-MC18063  
August 2018

Eaton, Bussmann and Low-Peak are valuable trademarks of Eaton in the U.S. and other countries. You are not permitted to use the Eaton trademarks without prior written consent of Eaton.

CSA is a registered trademark of the Canadian Standards Group.  
UL is a registered trademark of the Underwriters Laboratories, Inc.

For Eaton's Bussmann series product information, call 1-855-287-7626 or visit: [Eaton.com/bussmannseries](http://Eaton.com/bussmannseries)

Follow us on social media to get the latest product and support information.

