



LOFTREX™ M filter cartridges

Eaton's LOFTREX M filter cartridges are suitable for a wide range of process applications including RO prefiltration, machine coolants, chemicals, acids, bases, amine filtration, developers, and many more.

LOFTREX M filter cartridges are made of high purity polypropylene fibers. The product includes an integral polypropylene support core.

Features and benefits

- Made of high purity polypropylene fibers (melt blown)
- No binders or adhesives
- Excellent chemical compatibility
- Available in a variety of end cap/adaptor configurations to fit all industry-standard housings
- Individually sealed in plastic foil
- High dirt-holding capacity
- FDA listed (U.S. CFR, Title 21) materials of construction for food and beverage contact

Design

Filter material
Polypropylene (melt blown)

Inner core
Polypropylene

End caps
Polypropylene

O-rings
Silicone (standard),
Buna-N,
EPDM,
FPM,
FEP encapsulated

Retention ratings
1, 3, 5, 10, 20, 50 and 150 µm
@ 95% efficiency

Technical data

Nominal lengths
10", 20", 29.25", 30", 39", 40"
(254, 508, 743, 762, 991, 1.016 mm)

Outside diameter
2.5" (64 mm)

Inside diameter
1.1" (27 mm)

Max. operating temperature
176 °F (80 °C)

Max. differential pressure
58 psid @ 77 °F (4.0 bar @ 25 °C)

Recommended differential change-out pressure for disposal
35 psid (2.4 bar)




Powering Business Worldwide

LOFTREX M filter cartridges


Flow rate*

(68°F/20 °C per 10" filter cartridge for water)



* For liquids other than water, multiply pressure drop by fluid viscosity in centipoise.

Ordering code



North America
44 Apple Street
Tinton Falls, NJ 07724
Toll Free: 800 656-3344
(North America only)
Tel: +1 732 212-4700

China
No. 3, Lane 280,
Linhong Road
Changning District, 200335
Shanghai, P.R. China
Tel: +86 21 5200-0099

Europe/Africa/Middle East
Auf der Heide 2
53947 Nettersheim, Germany
Tel: +49 2486 809-0

Singapore
100G Pasir Panjang Road #07-08
Singapore 118523
Tel: +65 6825-1668

Friedensstraße 41
68804 Altlußheim, Germany
Tel: +49 6205 2094-0
An den Nahewiesen 24
55450 Langenlonsheim, Germany
Tel: +49 6704 204-0

Brazil
Rua Clark, 2061 - Macuco
13279-400 - Valinhos, Brazil
Tel: +55 11 3616-8400

For more information, please
email us at filtration@eaton.com
or visit www.eaton.com/filtration

US
EF-LX-M
02-2018

© 2018 Eaton. All rights reserved. All trademarks and registered trademarks are the property of their respective owners. All information and recommendations appearing in this brochure concerning the use of products described herein are based on tests believed to be reliable. However, it is the user's responsibility to determine the suitability for his own use of such products. Since the actual use by others is beyond our control, no guarantee, expressed or implied, is made by Eaton as to the effects of such use or the results to be obtained. Eaton assumes no liability arising out of the use by others of such products. Nor is the information herein to be construed as absolutely complete, since additional information may be necessary or desirable when particular or exceptional conditions or circumstances exist or because of applicable laws or government regulations.