

# Bag Nomenclature Chart

All the information necessary to understand an Eaton filter bag description is listed below. The filter description listed, is a PO-10-P04S-H-20, a polypropylene, 10 micron, plain no cover, 4"x15" filter bag with a carbon steel ring, a twill handle packed 20 to a box.

Type of Material	
<b>LOF-CLEAR® - ACCUGAF® - PROGAF®</b>	
Multi-layer meltblown polypropylene media	
<b>HAYFLOW® &amp; DURAGAF®</b>	
<b>PEXLF</b>	Extended life polyester, no scrim, glazed
<b>PEXL</b>	Extended life polyester, no scrim, glazed
<b>POXLF</b>	Extended life polypropylene, no scrim, g
<b>POXL</b>	Extended life polypropylene, no scrim, g
UNIRING® - Fully Welded	
<b>PEU</b>	Polyester needled felt. Singed.
<b>POU</b>	Polypropylene needled felt. Singed.
SENTINEL® - Fully Welded	
<b>PE</b>	Polyester needled felt. Singed.
<b>PEF</b>	Polyester FDA compliant felt.
<b>PO</b>	Polypropylene needled felt. Singed.
<b>POF</b>	Polypropylene FDA compliant felt.
SNAP RING® & BANDSEAL™	
<b>PE</b>	Polyester needled felt. Singed.
<b>PO</b>	Polypropylene needled felt. Singed.
<b>N</b>	Nylon needled felt. PE scrim
<b>HT</b>	Nomex needled felt with scrim
<b>PT</b>	Teflon® needled felt. PE scrim
<b>NMO</b>	Nylon monofilament mesh
<b>PEMO</b>	Polyester monofilament mesh
<b>PMO</b>	Polypropylene monofilament mesh
<b>PTMO</b>	Teflon® monofilament mesh
<b>PEMU</b>	Polyester multifilament mesh

Micron Rating
1
5
10
25
50
75
100
200

Cover Type	
PEMU 150	<b>A</b>
Extruded Mesh Cover & PO Spun Bond (4	<b>E</b>
NIMO 80	<b>N</b>
Plain (No Cover)	<b>P</b>
PE Spun Bonded Cover (AGF Only)	<b>R</b>
Modified/Special	<b>M</b>

Size	
Short 7" Bag 7 x 16"	<b>1</b>
Long 7" Bag 7 x 32"	<b>2</b>
Long Modified	<b>02M</b>
Short 4" Bag 4 x 8"	<b>3</b>
Long 4" Bag 4 x 14"	<b>4</b>
Special	<b>99</b>

Ring Type	
SNAP RINGS	
<b>A</b>	Stainless steel snap ring
<b>B</b>	Nylon snap ring
<b>O</b>	Polypropylene snap ring
<b>S</b>	Carbon steel snap ring, Zinc Plated
UNIRING® Rings	
<b>UE</b>	Polypropylene UNIRING®
<b>UK</b>	Kopel UNIRING®
SENTINEL Rings	
<b>E</b>	Polypropylene SENTINEL® Ring
<b>H</b>	Polyester SENTINEL® ring
<b>Z</b>	Santoprene SENTINEL® ring
Tie-on Bag (No Ring)	
<b>R</b>	Tie-on Bag (no ring)
Other Ring Types	
<b>M</b>	Modified / Special

Options	
<b>C</b>	Reverse collar
<b>E</b>	Twill tape reinforced side and thread other than standard
<b>F</b>	Thread other than standard
<b>H</b>	1 Handle in Twill tape
<b>K</b>	Round flat bottom (bucket shape)
<b>L</b>	Standard bag with increased length
<b>M</b>	Special
<b>N</b>	Mesh bag without a felt collar
<b>P</b>	Packaging without plastic liner
<b>Q</b>	Other than standard label
<b>T</b>	Mesh bag with twill tape collar
<b>U</b>	Turned inside out
<b>W</b>	Welded side and bottom only
<b>WW</b>	Fully welded
<b>Y</b>	Side welded/sewn bottom & ring

Bags per Box
4 to 100

