

REVISIONS

REV	DESCRIPTION	BY	ECO	DATE
A	FOR RELEASE	NISHANT SAWARKAR	0219116	8/14/2022
B	UPDATED TITLE BLOCK AND BORDER	NISHANT SAWARKAR	0226081	9/19/2022

NO. OF STATIONS	DIM 'A'	
	2	40" [1016]
	3	40" [1016]
	4	52" [1321]
	5	64" [1626]
	6	76" [1930]
	7	88" [2235]
	8	100" [2540]
	9	112" [2845]
	10	124" [3150]
	11	136" [3454]
	12	148" [3759]
	13	160" [4064]
	14	172" [4369]



FRAME	MAT'L	DIM 'N'	DIM 'P'
	CST	5-1/4"	6"
	CHNL	[133]	[152]
	304SS TUBE	4-3/4"	1-1/2"
		[121]	[38]

NORDEL (EPT)	VITON (VIT)
1000 PSI [69 BAR] 300°F [149°C]	1000 PSI [69 BAR] 350°F [176°C]

HEADER	FULL AUTO												SEMI AUTO				
	CS PNL			SS PNL			SMALL PNL			LARGE PNL							
	DIA	DIM 'J'	DIM 'K'	DIM 'L'	DIM 'M'	DIM 'K'	DIM 'L'	DIM 'M'	DIM 'K'	DIM 'L'	DIM 'M'	DIM 'K'	DIM 'L'	DIM 'M'			
3" [76]	13" [330]	10" [259]	26-13/16" [681]	14-7/16" [367]	12-1/8" [308]	26-5/16" [668]	8-15/16" [227]	8" [203]	19" [483]	4-3/4" [121]	-NA-	-NA-	-NA-				
4" [102]	13-1/2" [343]	10-1/2" [262]	27-5/16" [694]	13-15/16" [354]	12-1/4" [311]	26-13/16" [681]	8-7/16" [214]	8" [203]	19-1/2" [495]	4-1/4" [108]	-NA-	-NA-	-NA-				
6" [152]	14-9/16" [370]	10-1/2" [267]	28-3/8" [721]	12-7/8" [327]	15-1/2" [393]	27-7/8" [708]	7-3/8" [187]	8" [203]	20-9/16" [522]	3-3/16" [81]	-NA-	-NA-	-NA-				
8" [203]	15-9/16" [395]	10-1/2" [272]	29-3/8" [746]	11-7/8" [302]	15-1/2" [398]	28-7/8" [733]	6-3/8" [162]	8" [203]	21-9/16" [548]	2-3/16" [56]	11" [279]	25-1/4" [641]	4-5/16" [110]				
10" [254]	16-5/8" [422]	11" [278]	30-7/16" [773]	10-13/16" [275]	16" [404]	29-15/16" [760]	5-5/16" [135]	-NA	-NA-	-NA-	11" [279]	26-5/16" [668]	3-1/4" [83]				

NOTES:

- EXCEPTION : DIM 'K' OF SMALL SEMI AUTO PANEL FOR 2 STATION ASSEMBLY IS 10 INCH.
- ALL DIMENSIONS ARE IN INCHES [MM].

DRAWN BY NISHANT S		 EATON FILTRATION, LLC DESIGN CENTER			
SCALE AS DRAWN					
RESTRICTION RESTRICTED		TITLE AFC-2200 INTERNAL BACKWASH FILTER INLINE DIMENSION TABLE (HIGH PRESSURE)			
SHEET 1 OF 1					
PROJECTION THIRD ANGLE		DATE 08/14/2022	SIZE A	DWG FILENAME AFC-2200-IB-DT002	REV B
<small>EATON CORPORATION - CONFIDENTIAL AND PROPRIETARY NOTICE TO PERSONS RECEIVING THIS DRAWING AND/OR TECHNICAL INFORMATION                  THIS DOCUMENT, INCLUDING THE DRAWING AND INFORMATION CONTAINED THEREON IS CONFIDENTIAL AND IS THE EXCLUSIVE PROPERTY OF EATON AT ANY TIME. BY TAKING THE                  POSSESSION OF THIS DOCUMENT THE RECIPIENT ACKNOWLEDGES AND AGREES THAT THIS DOCUMENT CANNOT BE USED IN ANY MANNER ADVERSE TO THE INTEREST OF EATON AND                  THAT NO PORTION OF THIS DRAWING MAY BE COPIED OR OTHERWISE REPRODUCED WITHOUT THE PRIOR WRITTEN CONSENT OF EATON, IN THE CASE OF CONFLICTING CONTRACTUAL                  PROVISIONS, THIS NOTICE SHALL GOVERN THE STATUS OF THIS DOCUMENT.                  2022 EATON CORPORATION - ALL RIGHTS RESERVED.</small>					