





**EU1E-SWD-..., EU2E-SWD-...  
EU1S-SWD-..., EU2A-SWD-...**

➔  **MN120006...  
MN05006002Z...  
IL04716001Z...**  
[www.eaton.eu/documentation](http://www.eaton.eu/documentation)  
[www.eaton.com/smartywiredt](http://www.eaton.com/smartywiredt)


- |               |                |                 |                   |                 |               |
|---------------|----------------|-----------------|-------------------|-----------------|---------------|
| (en) Mounting | (it) Montaggio | (da) Montering  | (fi) Asennus      | (lv) Montāža    | (sk) Montáž   |
| (de) Montage  | (zh) 安装        | (el) Τοποθέτηση | (cs) Montáž       | (lt) Montavimas | (bg) Монтаж   |
| (fr) Montage  | (ru) Монтаж    | (pl) Montagem   | (et) Paigaldamine | (pl) Montaż     | (ro) Montarea |
| (es) Montaje  | (nl) Montering | (sv) Montering  | (hu) Felszerelés  | (sl) Montaža    | (hr) Montaža  |




**EU...**






**EU...E...  
EU1S...  
EU2A...**



- |                    |                    |                    |                    |                 |                 |
|--------------------|--------------------|--------------------|--------------------|-----------------|-----------------|
| (en) Connections   | (it) Collegamenti  | (da) Tilslutninger | (fi) Liitännät     | (lv) Pieslēgumi | (sk) Prívody    |
| (de) Anschlüsse    | (zh) 接头            | (el) Συνδέσεις     | (cs) Přívody       | (lt) Jungtys    | (bg) Свързване  |
| (fr) Raccordements | (ru) Присоединения | (pl) Conexões      | (et) Ühendused     | (pl) Przyłącza  | (ro) Conexiuni  |
| (es) Conexiones    | (nl) Aansluitingen | (sv) Anslutningar  | (hu) Csatlakozások | (sl) Priključki | (hr) Priključci |





	X1				
	1	2	3	4	5
EU1E-SWD-1DX	24 V		0 V	IO	
EU1E-SWD-2DX	24 V	I1	0 V	IO	
EU1E-SWD-1XD	24 V		0 V	Q0	
EU1E-SWD-2DD	24 V	I1/Q1	0 V	IQ/Q0	
EU1E-SWD-1AX-1	24 V	0 V	0 V	IA0	
EU1E-SWD-1AX-2	24 V	0 V	0 V	IA0	
EU1E-SWD-1XA-1	24 V	0 V	0 V	QA0	
EU1E-SWD-1XA-2	24 V	0 V	0 V	QA0	
EU1E-SWD-1CX	24 V	B	0 V	A	Ref
	24 V	Direction	0 V	Count	Ref



	X1				
	1	2	3	4	5
EU2E-SWD-2DX	24 V		0 V	I0	
EU2E-SWD-4DX	24 V	I1	0 V	I0	
EU2E-SWD-2XD	24 V		0 V	Q0	
EU2E-SWD-2DD	24 V		0 V	I0/Q0	
EU2E-SWD-4DD	24 V	I1/Q1	0 V	I0/Q0	
EU2E-SWD-2PT	ACD	a0	0 V	A0	B0

	X2				
	1	2	3	4	5
EU2E-SWD-2DX	24 V		0 V	I1	
EU2E-SWD-4DX	24 V	I3	0 V	I2	
EU2E-SWD-2XD	24 V		0 V	Q1	
EU2E-SWD-2DD	24 V		0 V	I1/Q1	
EU2E-SWD-4DD	24 V	I3/Q3	0 V	I2/Q2	
EU2E-SWD-2PT	ACD	a1	0 V	A1	B1

### EU1S-SWD-PF1-2



1	24 V
3	0 V

### EU2A-SWD-PBWN

