

BR and CH plug-on neutral (PON) features and benefits

QUICK

EASY

CLEAN

Shared features across the BR and CH PON offerings:

Q Plug-on neutral:

- E** • Eliminates the pigtail connection providing time and labour savings
- C** • Provides a professional installation

E Optimized Knockouts:

- Optimized knockout locations for additional access
- Easier to remove

Q Inboard Neutral:

- E** • Increases gutter space to allow for professional installation of conductors

Q Drywall offset: (on both sides of the can):

- E** • Self-leveling tabs allow for quick drywall offset

C White box trim and barriers:

- Providing a more professional look and feel
- Smooth case edges

E 2/0 Lug:

- Easily removable and can be installed in any location on the neutral bar

Q Bonding screw:

- E** • Bonding screw replaces Z-strap to provide a quick and easy means of bonding the neutral and ground

Common drive types:

- Q** • Minimizes number of tools required for installation as the neutral bar and breaker screws will share a common drive type




Image above represents the BR PON offering

Features specific to BR PON offering:

Q BR short-body PON breakers:

- E** • Short-body configuration maximizes gutter space providing ease of installation of the conductors
- C** • Reduced clutter of pigtails provides a clean gutter space
- Quick and clean installation, along with a consistent form and fit

Q Extra ground positions:

- E** • Provided in panels with more than 20 circuits allows quicker and easier wiring

Q Backed out neutral and ground screws:

- Allows for quick connection of neutral and ground conductors

10 year warranty on BR loadcentres and circuit breakers

Features specific to CH PON offering:

C One piece silver flashed copper bus:

- Provides superior conductivity, corrosion resistance, and durability

C Unique sandalwood finish:

- Esthetically appealing, scratch-resistant powder coating

E Full length neutral bars

- Offers additional terminations to land the neutral and ground conductors

E CHF AFCI/GFCI/Thermal magnetic breakers:

- Mechanical flag for trip indication (on thermal mag, AFCI & GFCI)
- All CH breakers provide a 2 position handle with simple 1 step reset

Limited lifetime warranty on all CH loadcentres and circuit breakers (including electronic breakers)

Cover features:

E Improved twist-outs:

- Easier to remove twistouts

C Embossed circuit numbers:

- Durable circuit numbering with added marking for twin breakers

E Keyhole hanging feature:

- Ease of cover installation

C Rigid cover spine:

- Provides strength when twistouts are removed



Powering Business Worldwide

Eaton
1000 Eaton Boulevard
Cleveland, OH 44122
United States
Eaton.com

Eaton
Canadian Operations
5050 Mainway
Burlington, ON L7L 5Z1
EatonCanada.ca

© 2018 Eaton
All Rights Reserved
Printed in Canada
Publication No. PA003018EN
June 2018