

Pro

ProXchange

862/1869/1871/mw



FEATURES

- Cast marine brass or copper free aluminum construction available.
- Neoprene gasket resists petroleum and provides a watertight seal.
- Silicone lubricant provided for cover screws and flange.
- Round or Square box types in surface or flush mounting.
- Double pole rotary switch rated at 20 amps.

APPLICATIONS

- Marine and watertight requirements

APPROVALS

- Conforms to IP66
- ABS

TECHNICAL SPECIFICATIONS

BOX/COVER/KNOB

Cast marine brass or copper free aluminum.

HARDWARE

Stainless steel.

GASKET

One piece neoprene.

ENTRIES

Standard undrilled. Up to 3/4" NPT through feed. 862 up to 3/4" NPT four way. See ENTRY OPTIONS for selections.

VOLTAGE AND CURRENT

20 Amp 120/240v AC

1 HP at 120v AC or 2 HP at 240v AC

MOUNTING

862/1869/1871

Surface, via two 1/4" mounting bolts (not included).

862F

Flush, via two 1/4" mounting bolts (not included).

ORDERING REFERENCES

PART NUMBER	DESCRIPTION	WEIGHT LBS
862B	BRASS, Surface Mount Round Box	2.1
862BF	BRASS, Flush Mount Round Box	3.0
1869B	BRASS, Surface Mount Two Gang Box	4.5
1871B	BRASS, Surface Mount Square Box	3.2
862A	ALUMINUM, Surface Mount Round Box	0.9
1871A	ALUMINUM, Surface Mount Square Box	1.2

ENTRY OPTIONS

862 Version

NPT Trade Size	Dead End	Thru Feed	90 Degree	X-Positions
1/2"	E1	C1	L1	X1
3/4"	E2	C2	L2	X2


1869 & 1871 Versions

NPT Trade Size	Dead End	Thru Feed
1/2"	E1	C1
3/4"	E2	C2

SPARE PARTS

Part No.	Description
INX6509B	COVER, Brass, Surface Mount Round Box
INX6510B	COVER, Brass, Surface Mount Square Box
INX6511B	COVER, Brass, Surface Mount Two Gang Box
INX6512B	COVER, Brass, Flush Mount Round Box
INX6509A	COVER, Aluminum, Surface Mount Round Box
INX6510A	COVER, Aluminum, Surface Mount Square Box
INX6001B	BOX, Brass, Surface Mount Round
INX6002B	BOX, Brass, Surface Mount Square
INX6003B	BOX, Brass, Surface Mount Two Gang
INX6004B	BOX, Brass, Flush Mount Round
INX6001A	BOX, Aluminum, Surface Mount Round
INX6002A	BOX, Aluminum, Surface Mount Square
INX8002B	KNOB AND SHAFT ASSEMBLY, Brass
INX8002A	KNOB AND SHAFT ASSEMBLY, Aluminum
INX3192	SWITCH
GKT3001	GASKET, Surface Mount Round Box
GKT4000	GASKET, Surface/Flush Mount Square Box
GKT5001	GASKET, Surface Mount Two Gang Box
GKT2007	GASKET, Flush Mount Round Box

DIMENSIONS



Dimensions in inches