

Pow-R-Xpress

Horizontal main sub-feed breaker kits

Horizontal breaker kits are assembled with terminals and load bus connectors. Easily mounted for either top or bottom entry. Offering is available for 100–225 A for single-phase and three-phase applications.

Circuit breaker	NAED/UIC#	Description	Product code
BKD2F100H1	786689585402	PRX MCB kit PDD22F 100 A, 240 V, 35 k, horizontal single-phase	PSOK0
BKD2F125H1	786689585419	PRX MCB kit PDD22F 125 A, 240 V, 35 k, horizontal single-phase	PSOK0
BKD2F150H1	786689585426	PRX MCB kit PDD22F 150 A, 240 V, 35 k, horizontal single-phase	PSOK0
BKD2F175H1	786689585433	PRX MCB kit PDD22F 175 A, 240 V, 35 k, horizontal single-phase	PSOK0
BKD2F200H1	786689585440	PRX MCB kit PDD22F 200 A, 240 V, 35 k, horizontal single-phase	PSOK0
BKD2F225H1	786689585457	PRX MCB kit PDD22F 225 A, 240 V, 35 k, horizontal single-phase	PSOK0
BKD2G100H1	786689585464	PRX MCB kit PDD22G 100 A, 240 V, 65 k, horizontal single-phase	PSOK0
BKD2G125H1	786689585471	PRX MCB kit PDD22G 125 A, 240 V, 65 k, horizontal single-phase	PSOK0
BKD2G150H1	786689585488	PRX MCB kit PDD22G 150 A, 240 V, 65 k, horizontal single-phase	PSOK0
BKD2G175H1	786689585495	PRX MCB kit PDD22G 175 A, 240 V, 65 k, horizontal single-phase	PSOK0
BKD2G200H1	786689585501	PRX MCB kit PDD22G 200 A, 240 V, 65 k, horizontal single-phase	PSOK0
BKD2G225H1	786689585518	PRX MCB kit PDD22G 225 A, 240 V, 65 k, horizontal single-phase	PSOK0
BKD2F100H	786689395032	PRX MCB kit PDD23F 100 A, 240 V, 35 kAIC, horizontal	PSOK0
BKD2F125H	786689395049	PRX MCB kit PDD23F 125 A, 240 V, 35 kAIC, horizontal	PSOK0
BKD2F150H	786689395056	PRX MCB kit PDD23F 150 A, 240 V, 35 kAIC, horizontal	PSOK0
BKD2F175H	786689395063	PRX MCB kit PDD23F 175 A, 240 V, 35 kAIC, horizontal	PSOK0
BKD2F200H	786689395070	PRX MCB kit PDD23F 200 A, 240 V, 35 kAIC, horizontal	PSOK0
BKD2F225H	786689395087	PRX MCB kit PDD23F 225 A, 240 V, 35 kAIC, horizontal	PSOK0
BKD2G100H	786689395094	PRX MCB kit PDD23G 100 A, 240 V, 65 kAIC, horizontal	PSOK0
BKD2G125H	786689395100	PRX MCB kit PDD23G 125 A, 240 V, 65 kAIC, horizontal	PSOK0
BKD2G150H	786689395117	PRX MCB kit PDD23G 150 A, 240 V, 65 kAIC, horizontal	PSOK0
BKD2G175H	786689395124	PRX MCB kit PDD23G 175 A, 240 V, 65 kAIC, horizontal	PSOK0
BKD2G200H	786689395131	PRX MCB kit PDD23G 200 A, 240 V, 65 kAIC, horizontal	PSOK0
BKD2G225H	786689395148	PRX MCB kit PDD23G 225 A, 240 V, 65 kAIC, horizontal	PSOK0
BKG2G100H	786689395155	PRX MCB kit PDG23G 100 A, 480 V, 35 kAIC, horizontal	PSOK0
BKG2G110H	786689395162	PRX MCB kit PDG23G 110 A, 480 V, 35 kAIC, horizontal	PSOK0
BKG2G125H	786689395179	PRX MCB kit PDG23G 125 A, 480 V, 35 kAIC, horizontal	PSOK0
BKG2G150H	786689395186	PRX MCB kit PDG23G 150 A, 480 V, 35 kAIC, horizontal	PSOK0
BKG2G175H	786689395193	PRX MCB kit PDG23G 175 A, 480 V, 35 kAIC, horizontal	PSOK0
BKG2G200H	786689395209	PRX MCB kit PDG23G 200 A, 480 V, 35 kAIC, horizontal	PSOK0
BKG2G225H	786689395216	PRX MCB kit PDG23G 225 A, 480 V, 35 kAIC, horizontal	PSOK0
BKG2M100H	786689395223	PRX MCB kit PDG23M 100 A, 480 V, 65 kAIC, horizontal	PSOK0
BKG2M110H	786689395230	PRX MCB kit PDG23M 110 A, 480 V, 65 kAIC, horizontal	PSOK0
BKG2M125H	786689395247	PRX MCB kit PDG23M 125 A, 480 V, 65 kAIC, horizontal	PSOK0
BKG2M150H	786689395254	PRX MCB kit PDG23M 150 A, 480 V, 65 kAIC, horizontal	PSOK0
BKG2M175H	786689395261	PRX MCB kit PDG23M 175 A, 480 V, 65 kAIC, horizontal	PSOK0
BKG2M200H	786689395278	PRX MCB kit PDG23M 200 A, 480 V, 65 kAIC, horizontal	PSOK0
BKG2M225H	786689395285	PRX MCB kit PDG23M 225 A, 480 V, 65 kAIC, horizontal	PSOK0
SFBCVR225AHORZ	786689587215	225 A horizontal SFB breaker cover for 400 A panelboard	P11U0
SFBCVR225BHORZ	786689587222	225 A horizontal SFB breaker cover for 600 A panelboard	P11U0

Eaton
1000 Eaton Boulevard
Cleveland, OH 44122
United States
Eaton.com

© 2021 Eaton
All Rights Reserved
Printed in USA
Publication No. MZ014031EN / Z25198
June 2021

For more information, contact your local Eaton sales representative. Learn more about the Pow-R-Xpress program at Eaton.com/PRX.