

# Single meter socket assemblies

## 125, 200 & 320 Amp continuous, CT meter socket

### No bypass



No Bypass  
1005 CD

No Bypass  
1007 CD



No Bypass  
2004 CD

No Bypass  
EN20L4

UPC Number	Catalog Number	Amp Rating	Jaws	Service Type	Meter Mounting	Model Families	Connections	
							Line	Load
78205139475	1004 CD	125	4	1Ø 3W	Ring Type	011	#14 - 2/0	#14 - 2/0
78205108120	1005 CD	125	5	1Ø 3W	Ring Type	011	#14 - 2/0	#14 - 2/0
78205139485	1007 CD	100	7	3Ø 4W	Ring Type	927	#14 - 1/0	#14 - 1/0
78205139545	2004 CD	200	4	1Ø 3W	Ring Type	204	#6 - 250MCM	#6 - 250MCM
78205139565	2007 CD	200	7	3Ø 4W	Ring Type	207	#6 - 250MCM	#6 - 250MCM
11653718	EN12L4	125	4	1Ø 3W	Ringless	EN12	#6 - 350MCM	#6 - 350MCM
11652526	EN20L4	200	4	1Ø 3W	Ringless	EN20	#6 - 350MCM	#6 - 350MCM

### Lever bypass



Lever Bypass  
EC12L4

Lever Bypass  
EL20L4



Lever Bypass  
EC32T4

Lever Bypass  
EL32T7

UPC Number	Catalog Number	Amp Rating	Jaws	Service Type	Meter Mounting	Connections	
						Line	Load
11653326	EC12L4	125	4	1Ø 3W	Ringless	#14 - 2/0	#14 - 2/0
11653328	EC12L7	125	7	3Ø 4W	Ringless	#14 - 2/0	#14 - 2/0
11653340	EL20L4	200	4	1Ø 3W	Ringless	#6 - 350MCM	#6 - 350MCM
11653342	EL20L7	200	7	3Ø 4W	Ringless	#6 - 350MCM	#6 - 350MCM
11653346	EL32T4	320	4	1Ø 3W	Ringless	3/8"-16 Studs	3/8"-16 Studs
11653348	EL32T7	320	7	3Ø 4W	Ringless	3/8"-16 Studs	3/8"-16 Studs

### Current transformer rated



Current  
Transformer  
1004 CT-B

Current  
Transformer  
1006 CT



Current  
Transformer  
10013 CT


Current  
Transformer  
10015 CT-B

UPC Number	Catalog Number	Amp Rating	Jaws	Service Type	Meter Mounting	Connections	
						Line	Load
78205117722	1004 CT	20	4	1Ø 3W	Ring Type*	#14 - #10	Front
78205102422	1004 CT-B	20	4	1Ø 3W	Ring Type*	#14 - #10	Back
78205108121	1005 CT	20	5	1Ø 3W	Ring Type*	#14 - #10	Front
78205131000	1005 CT-B	20	5	1Ø 3W	Ring Type*	#14 - #10	Back
78205131005	1006 CT	20	6	1Ø 3W	Ring Type*	#14 - #10	Front
78205131010	1006 CT-B	20	6	1Ø 3W	Ring Type*	#14 - #10	Back
78205139490	1008 CT	20	8	3Ø 4W	Ring Type*	#14 - #10	Front
78205139515	1008 CT-B	20	8	3Ø 4W	Ring Type*	#14 - #10	Back
78205139520	10013 CT	20	13	3Ø 4W	Ring Type*	#14 - #10	Front
78205139535	10013 CT-B	20	13	3Ø 4W	Ring Type*	#14 - #10	Back
78205139540	10015 CT	20	15	3Ø 4W	Ring Type*	#14 - #10	Front
78205139542	10015 CT-B	20	15	3Ø 4W	Ring Type*	#14 - #10	Back


\* Can be used with Ringless style mounting however surge bracket is not included

# Socket Assemblies

## With backplate



With Backplate  
1004 CD KIT



With Backplate  
2007 CD KIT



With Backplate  
20315 L



With Backplate  
20327 L

UPC Number	Catalog Number	Amp Rating	Jaws	Service Type	Bypass	Meter Mounting	Connections	
							Line	Load
78205108118	1004 CD KIT	125	4	1Ø 3W	--	Ring Type	#14 - 2/0	#14 - 2/0
78205108122	1007 CD KIT	100	7	3Ø 4W	--	Ring Type	#14 - 1/0	#14 - 1/0
78205108461	2004 CD KIT	200	4	1Ø 3W		Ring Type	#6 - 250MCM	#6 - 250MCM
78205108463	2007 CD KIT	200	7	3Ø 4W	--	Ring Type	#6 - 250MCM	#6 - 250MCM
78205120314	20314 L	100	4	1Ø 3W	Test Block	Ring Type	#14 - 1/0	#14 - 1/0
78205120300	20315 L	100	5	3Ø 3W	Test Block	Ring Type	#14 - 1/0	#14 - 1/0
78205120305	20317 L	100	7	3Ø 4W	Test Block	Ring Type	#14 - 1/0	#14 - 1/0
78205120308	20324 L	200	4	1Ø 3W	Test Block	Ring Type	#6 - 250MCM	#6 - 250MCM
78205120310	20325 L	200	5	3Ø 3W	Test Block	Ring Type	#6 - 250MCM	#6 - 250MCM
78205120312	20327 L	200	7	3Ø 4W	Test Block	Ring Type	#6 - 250MCM	#6 - 250MCM

## Mounting accessories



Mounting  
Accessories  
25114



Mounting  
Accessories  
25114 A


UPC Number	Catalog Number	Description
78205125114	25114	Cast Aluminum Mounting Ring
78205125145	25114 A	Cross Bar Adapter*

\* Required to mate 25114 mounting ring to 4, 5, and 6 jaw sockets

## Covers & sealing rings



Steel Cover  
30420



Clear Lexan Cover  
25162



Aluminum Snap  
Type Sealing Ring  
25016 A



Stainless Steel  
Snap Type Sealing  
Ring 25016 B



Aluminum Screw  
Type Sealing Ring  
25016 D

UPC Number	Catalog Number	Description
78205101148	30420	Steel Cover for Socket Opening
78205139430	25162	Clear Lexan Cover for Socket Opening
78205139405	25016 A	Aluminum Snap Type Sealing Ring
78205139415	25016 B	Stainless Steel Snap Type Sealing Ring
78205139420	25016 D	Aluminum Screw Type Sealing Ring

**Eaton**  
1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
Eaton.com

© 2015 Eaton  
All Rights Reserved  
Printed in USA  
Publication No. CA307004EN  
November 2015 MOEM

B-Line Division  
509 West Monroe Street  
Highland, IL 62249  
United States  
Phone: 800-851-7415

[www.cooperline.com/contactus](http://www.cooperline.com/contactus)

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

