



323410RTCT1FAL (closed)



323410RTCT1FAL (open)

Application

- Designed to house current transformers (CT)
- Used as wiring boxes, junction and pull boxes
- Protects against falling rain, sleet, and external ice formation
- Surface mount

Construction

- NEMA Type 3R
- Mounting provisions installed
- Screw cover with padlock provisions for sealing cover to cabinet
- Universal mounting plate on adjustable channels for easier CT installation



Standards

- UL 414 Listed

Finish

- Aluminum - unpainted
- Steel - ANSI 61 gray powder coated

Part/UPC Number	Catalog Number	Cover	Overall Dimensions			Material	Utility †
			Height	Width	Depth		
79903857528	323410 RTCT1F	Lift Off	34"	32"	10"	Galvaneal Steel	FP&L
78205155913	323410 RTCT1FAL	Lift Off	34"	32"	10"	Aluminum	FP&L
79903857529	323412 RTCT1F	Lift Off	34"	32"	12"	Galvaneal Steel	FP&L, DUKE
78205155914	323412 RTCT1FAL	Lift Off	34"	32"	12"	Aluminum	FP&L, DUKE
79903857530	304614.5 RTCT1F	Lift Off	46"	30"	14 1/2"	Galvaneal Steel	FP&L, DUKE
78205155915	304614.5 RTCT1FAL	Lift Off	46"	30"	14 1/2"	Aluminum	FP&L, DUKE

† Utilities shown are brand names of their respective owners.

CT Utility Enclosures

NEMA Type 3R



24269DDHRTCT1FAL (closed)



24269DDHRTCT1FAL (open)

Application

- Designed to house current transformers (CT)
- Used as wiring boxes, junction and pull boxes
- Protects against falling rain, sleet, and external ice formation
- Surface mount

Construction

- NEMA Type 3R
- Mounting provisions installed
- Doors have a quick-release padlock hasp with installed door stop mechanism
- Side louvers include filters and baffle plates

Finish

- Aluminum - unpainted
- Steel - ANSI 61 gray powder coated

Part/UPC Number	Catalog Number	Cover	Overall Dimensions			Ground Lug	Material
			Height	Width	Depth		
79903857531	24269 DDHRTCT1F *	Double, Hinged	27"	24"	9"	(2) #14 - 2/0	Galvaneal Steel
78205155981	24269 DDHRTCT1FAL *	Double, Hinged	27"	24"	9"	(2) #14 - 2/0	Aluminum
79903857532	363612 DDHRTCT1F *	Double, Hinged	37"	36"	12"	(2) #14 - 2/0	Galvaneal Steel
78205155982	363612 DDHRTCT1FAL *	Double, Hinged	37"	36"	12"	(2) #14 - 2/0	Aluminum

* Not UL Listed

† Utilities shown are brand names of their respective owners.

Data subject to change without notice. Consult local utility for area acceptance. All dimensions are in inches.