



No.	CP0603 Rev. 01
E-Ref:	None
Supersedes:	05/06
File Ref:	Cat. Sec. 240
Date:	10/1/2007

	Voltage Rating (kV)	Current Rating (A)	CPS EMF Part Number (240-92)	Elastimold MCLF Part Number	G&W EPOX Part Number	CPS Epoxy Enc Fuse Part Number (240-86)
<b>5kV Class</b>	5.5	10	55F010EMF0202			
	5.5	15	55F015EMF0202			
	5.5	20	55F020EMF0202			
	5.5	25	55F025EMF0202			
	5.5	30	55F030EMF0202			
	5.5	40	55F040EMF0202			
	5.5	50	55F050EMF0202			
	5.5	65	55F065EMF0202			
	5.5	80	55F080EMF0202	M05CLF080		
	5.5	100	55F100EMF0202	M05CLF100		
	5.5	125	55F125EMF0202	M05CLF125		
	5.5	150	55F150EMF0202	M05CLF150		
	5.5	180		M05CLF180		
	5.5	200	55F200EMF0202			
	<b>15kV Class</b>	8.3	3			
8.3		6			FSE2PA83F006	83F006-EX2
8.3		8			FSE2PA83F008	83F008-EX2
8.3		10	83F010EMF0202	M15CLF010	FSE2PA83F010	83F010-EX2
8.3		12			FSE2PA83F012	83F012-EX2
8.3		15	83F015EMF0202			
8.3		18			FSE2PA83F018	83F018-EX2
8.3		20	83F020EMF0202	M15CLF020	FSE2PA83F020	83F020-EX2
8.3		25	83F025EMF0202		FSE2PA83F025	83F025-EX2
8.3		30	83F030EMF0202	M15CLF030	FSE2PA83F030	83F030-EX2
8.3		40	83F040EMF0202	M15CLF040	FSE2PA83F040	83F040-EX2
8.3		50	83F050EMF0202	M15CLF050	FSE2PB83F050	83F050-EX2
8.3		65	83F065EMF0202	M15CLF065	FSE2PB83F065	83F065-EX2
8.3		80	83F080EMF0202	M15CLF080	FSE2PB83F080	83F080-EX2
8.3		100	83F100EMF0202	M15CLF100	FSE2PB83F100	83F100-EX2
8.3		115		M15CLF115		
8.3		125	83F125EMF0202		FSE2PB83F125	83F125-EX2
8.3		140			FSE2PB83F140	83F140-EX2
8.3	150	83F150EMF0202				
8.3	185					
8.3	200	83F200EMF0202				

	<b>Voltage Rating (kV)</b>	<b>Current Rating (A)</b>	<b>CPS EMF Part Number (240-92)</b>	<b>Elastimold MCLF Part Number</b>	<b>G&amp;W EPOX Part Number</b>	<b>CPS Epoxy Enc Fuse Part Number (240-86)</b>
	15.5	3				155F003-EX2
	15.5	6				155F006-EX2
	15.5	8	155F008EMF0202			155F008-EX2
	15.5	10	155F010EMF0202	M25CLF010	FSE2PA15F010	155F010-EX2
	15.5	12			FSE2PA15F012	155F012-EX2
	15.5	15	155F015EMF0202			
	15.5	18			FSE2PA15F018	155F018-EX2
	15.5	20	155F020EMF0202	M25CLF020	FSE2PA15F020	155F020-EX2
<b>25kV Class</b>	15.5	25	155F025EMF0202		FSE2PA15F025	155F025-EX2
	15.5	30	155F030EMF0202	M25CLF030	FSE2PA15F030	155F030-EX2
	15.5	40	155F040EMF0202	M25CLF040	FSE2PA15F040	155F040-EX2
	15.5	50	155F050EMF0202	M25CLF050	FSE2PB15F050	155F050-EX2
	15.5	60			FSE2PB15F060	
	15.5	65	155F065EMF0202	M25CLF065	FSE2PB15F065	155F065-EX2
	15.5	80	155F080EMF0202	M25CLF080	FSE2PB15F080	155F080-EX2
	15.5	100	155F100EMF0202	M25CLF100	FSE2PB15F100	155F100-EX2
	15.5	125	155F125EMF0202		FSE2PB15F125	155F125-EX2
	15.5	140				
	17.2	3				
	17.2	6				
	17.2	8	172F008EMF0202			
	17.2	10	172F010EMF0202	M25CLF010		
	17.2	12				
	17.2	15	172F015EMF0202			
	17.2	18				
	17.2	20	172F020EMF0202	M25CLF020		
<b>25kV Class</b>	17.2	25	172F025EMF0202			
	17.2	30	172F030EMF0202	M25CLF030		
	17.2	40	172F040EMF0202	M25CLF040		
	17.2	50	172F050EMF0202	M25CLF050		
	17.2	65	172F065EMF0202			
	17.2	80	172F080EMF0202			
	17.2	100	172F100EMF0202			
	23	8	currently n/a			
	23	10	currently n/a	M35CLF010		
	23	15	currently n/a			
	23	20	currently n/a	M35CLF020		
<b>35kV Class</b>	23	25	currently n/a			
	23	30	currently n/a	M35CLF030		
	23	40	currently n/a	M35CLF040		
	23	50	currently n/a	M35CLF050		
	23	65	currently n/a			
	23	80	currently n/a			