





CABLE CHANNEL 0" & 6" RADIUS HORIZONTAL CROSS CONNECTOR



0" RADIUS
ATTACHMENT
(6" WIDTH SHOWN)



6" RADIUS
ATTACHMENT
(6" WIDTH SHOWN)



OPTIONAL PIVOT
CONNECTOR ATTACHMENT
(6" WIDTH SHOWN)

- HORIZONTAL CROSS CONNECTOR IS DESIGNED TO ATTACH CABLE CHANNEL IN EITHER A 0" OR 6" RADIUS CONFIGURATION.
- ATTACHMENT HARDWARE IS INCLUDED.
- MATERIAL

ALUMINUM: 5052 - H32, .125 THICK
STEEL: ASTM A570 GR. 33, 14 GA.

- FINISH
- PART NUMBERS FOR OPTIONAL PIVOT CONNECTORS:

3" WIDTH - *CC-03-PC
4" WIDTH - *CC-04-PC
6" WIDTH - *CC-06-PC

* = A -ALUMINUM
G - HOT DIP GALVANIZED STEEL
SS4 - 304 STAINLESS STEEL
SS6 - 316 STAINLESS STEEL

PART NUMBER	CABLE CHANNEL WIDTH	LENGTH	DEPTH
*CC-03-HXC060	3.00	18.00	18.00
*CC-04-HXC060	4.00	19.00	19.00
*CC-06-HXC060	6.00	21.00	21.00

* = A -ALUMINUM
G - HOT DIP GALVANIZED STEEL
SS4 - 304 STAINLESS STEEL
SS6 - 316 STAINLESS STEEL



EATON, B-LINE DIVISION
509 WEST MONROE STREET
HIGHLAND, ILLINOIS 62249-0326
PHONE (618) 654-2184
FAX (618) 654-5499

TITLE:
CABLE CHANNEL 0" & 6" RADIUS
HORIZONTAL CROSS CONNECTOR

EQUIPMENT FURNISHED HAS BEEN FABRICATED
IN ACCORDANCE WITH THIS DRAWING.

THIS DRAWING AND/OR THE TECHNICAL INFORMATION CONTAINED HEREON IS THE PROPERTY OF EATON CORPORATION ("EATON"), AND IS ISSUED IN CONFIDENCE FOR EATON ENGINEERING PURPOSES ONLY AND MAY NOT BE REPRODUCED OR USED FOR ANY PURPOSE WHATSOEVER WITHOUT THE EXPRESS WRITTEN PERMISSION OF EATON TO THE USER. THIS DRAWING AND/OR TECHNICAL INFORMATION IS THE PROPERTY OF EATON AND IS LOANED FOR MUTUAL ASSISTANCE, TO BE RETURNED WHEN ITS INTENDED PURPOSE HAS BEEN SERVED.

PRODUCT DWG. NO'S:

7825

SHEET OF
DRAWN BY: TJC

DRAWING NO.
S00007825

DATE: 7/23/96