



Stainless steel FLEXTRAY™ wire basket

In harsh environments, support your cables with stainless steel FLEXTRAY wire baskets instead of conduit. FLEXTRAY is adaptable to conditions on the job site and installs quickly.

Features & benefits:

- Tray offered in two finishes:
 - Stainless Steel Type 304 for most applications
 - Stainless Steel Type 316 for highly corrosive applications
- Broad range of support options
- Field-adaptable tray for easy to cut and bend on the job site for routing around obstructions
- Easy cable dropout from end or side




Powering Business Worldwide



FLEXTRAY wire basket




Splicing Hardware



Support Washer



Tab-Loc Splice



Splice Plate



U Bracket



L Bracket



Shelf Bracket



FLIP CLIP™ Connector

The list below contains some of our most popular stainless items.

FLEXTRAY™ WIRE BASKET

(Depth x Width x Length) add 304LSS for Type 304 Stainless Steel or SS for 316 Stainless Steel

Catalog #	D x W x L	Catalog #	D x W x L	Catalog #	D x W x L
FT2X2X10__	2" x 2" x 118.312"	FT4X4X10__	4" x 4" x 118.312"	FT6X8X10__	6" x 8" x 118.312"
FT2X4X10__	2" x 4" x 118.312"	FT4X6X10__	4" x 6" x 118.312"	FT6X12X10__	6" x 12" x 118.312"
FT2X6X10__	2" x 6" x 118.312"	FT4X8X10__	4" x 8" x 118.312"	FT6X16X10__	6" x 16" x 118.312"
FT2X8X10__	2" x 8" x 118.312"	FT4X12X10__	4" x 12" x 118.312"	FT6X18X10__	6" x 18" x 118.312"
FT2X12X10__	2" x 12" x 118.312"	FT4X16X10__	4" x 16" x 118.312"	FT6X20X10__	6" x 20" x 118.312"
FT2X16X10__	2" x 16" x 118.312"	FT4X18X10__	4" x 18" x 118.312"	FT6X24X10__	6" x 24" x 118.312"
FT2X18X10__	2" x 18" x 118.312"	FT4X20X10__	4" x 20" x 118.312"		
FT2X20X10__	2" x 20" x 118.312"	FT4X24X10__	4" x 24" x 118.312"		
FT2X24X10__	2" x 24" x 118.312"	FT4X30X10__	4" x 30" x 118.312"		
FT2X30X10__	2" x 30" x 118.312"				
FT2X32X10__	2" x 32" x 118.312"				

WALL SUPPORTS

Catalog #	Description	Catalog #	Description
FTB2UBSS6	U Bracket for 2 x 2 Flextray	FTB06CSS6	Shelf Bracket for 6" wide Flextray
4 L BRKTSS	'L' Bracket for 4" wide Flextray	FTB08CSS6	Shelf Bracket for 8" wide Flextray
8 L BRKTSS	'L' Bracket for 8" wide Flextray	FTB12CSS6	Shelf Bracket for 12" wide Flextray
12 L BRKTSS	'L' Bracket for 12" wide Flextray	FTB16CSS6	Shelf Bracket for 16" wide Flextray
16 L BRKTSS	'L' Bracket for 16" wide Flextray	FTB18CSS6	Shelf Bracket for 18" wide Flextray
20 L BRKTSS	'L' Bracket for 20" wide Flextray	FTB20CSS6	Shelf Bracket for 20" wide Flextray
24 L BRKTSS	'L' Bracket for 24" wide Flextray	FTB24CSS6	Shelf Bracket for 24" wide Flextray

CEILING SUPPORTS

Catalog #	Description	Catalog #	Description
WB46HSS6	Flip Clip	WB5506SS6	Trapeze Kit for 6" wide Flextray
WB5518CHSS6	Heavy Duty Center Hanger	WB5508SS6	Trapeze Kit for 8" wide Flextray
		WB5512SS6	Trapeze Kit for 12" wide Flextray
		WB5518SS6	Trapeze Kit for 18" wide Flextray
		WB5524SS6	Trapeze Kit for 24" wide Flextray

SPLICING

Catalog #	Description	Catalog #	Description
FTHDWE1/4SS	¼" Bolt & Nut	FTS3SPSS6	3" Splice Plate
TOP WASHERSS	Top Washer	FTSTLCS6	Tab-Loc Splice
BTM WASHERSS	Bottom Washer	SPLICE BARSS	Splice Bar

ACCESSORIES

Description	Description
Covers	Inserts
Wall Termination Kit	Dividers
Blind Ends	Wall Mount Kit

Refer to B-Line series product catalogs for additional information.

For more information, visit www.cooperbline.com/flextray

Eaton
1000 Eaton Boulevard
Cleveland, OH 44122
United States
Eaton.com

© 2016 Eaton
All Rights Reserved
Printed in USA
Publication No. SA302013EN
January 2016 CBFSS

B-Line Division
509 West Monroe Street
Highland, IL 62249
United States
Phone: 800-851-7415

www.eaton.com/b-lineseries

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

