

Aspire product line

Smart dimmers with preset

Rating		Description	Color suffix	Catalog no.
W	V/AC			
300	120	Smart dimmer, dimmable LED/CFL, single-pole & multi-location	AW, DS, SG, WS	□ 9540-N
600	120	Smart dimmer, INC/HAL/ELV & MLV		
600	120	Smart dimmer, INC/HAL/MLV single-pole	AW, DS, SG, WS	□ 9534
1000	120	Smart dimmer, INC/HAL/MLV, single-pole	AW, DS, SG, WS	□ 9536
1000	120	Smart dimmer, ELV, single-pole	AW, DS, SG, WS	□ 9537
—	—	Smart accessory dimmer, multi-location	AW, DS, SG, WS	□ 9542

cULus Listed to UL1472, file no. E47967; NOM certified

Slide dimmers

Rating		Description	Neutral	Color suffix	Catalog no.
W	V/AC				
600	120	INC/HAL/MLV dimmer, single-pole/3-way with preset	No	AW, DS, SG, WS	□ 9530
600	120	ELV dimmer, single-pole/3-way with preset	No	AW, DS, SG, WS	□ 9531
1000	120	INC/HAL/MLV dimmer, single-pole/3-way with preset	No	AW, DS, SG, WS	□ 9532
1000	120	ELV dimmer, single-pole/3-way with preset	No	AW, DS, SG, WS	□ 9533
1000	120	FLR dimmer, single-pole/3-way w/preset, Mark 10®, AmbiStar® & Tu-Wire® compatible	Yes	AW, DS, SG, WS	□ 9568
1000	277	FLR dimmer, single-pole/3-way w/preset, Mark 10® compatible	Yes	AW, DS, SG, WS	□ 95687
300	120	LED/CFL, single-pole/3-way		AW, DS, SG, WS	□ 9540-N
600	120	INC/HAL			

cULus Listed to UL1472, file no. E47967; NOM certified

Fan speed controls

Rating		Description	Color suffix	Catalog no.
A	V/AC			
1.5	120	Quiet 3-speed fan control, single-pole /3-way, side wire	AW, DS, SG, WS	□ 9544
5	120	Fully variable fan speed control, single-pole/3-way, side wire	AW, DS, SG, WS	□ 9543

cULus Listed to UL1917, file no. E202842; NOM certified

Timers

Rating		Description	Color suffix	Catalog no.
A	V/AC			
15	120	5-button minute timer with OFF button, single-pole	AW, DS, SG, WS, C1, C2, C3	□ 9590
15	120	5-button hour timer with OFF button, single-pole	AW, DS, SG, WS, C1, C2, C3	□ 9591

cULus Listed to UL60730-1A & 60730-2-7, file no. E325082; certified to CSA E60730-1:02 & E60730-2-9:01; NOM certified

Switches

Rating		Description	Color suffix	Catalog no.
A	V/AC			
15	120/277	Single-pole, side wire & push wire	AW, DS, SG, WS	□ 9501
15	120/277	3-way, side wire & push wire	AW, DS, SG, WS	□ 9503
15	120/277	4-way, back wire & push wire	AW, DS, SG, WS	□ 9504 *
20	120/277	Single-pole, side wire & push wire	AW, DS, SG, WS	□ 9515
20	120/277	3-way, side wire & push wire	AW, DS, SG, WS	□ 9516

cULus Listed to UL20, file no. E18704; * UL verified to Federal Spec. WC-896E; NOM certified

Visit our website:
www.Cooperwiringdevices.com

Eaton's
 Aspire design system

The perfect
 upgrade that
 sells itself



Electrical Sector
 203 Cooper Circle
 Peachtree City, GA 30269
 United States
 Eaton.com
 Arrowhart.com

Electrical Sector
 Canada Operations
 5925 McLaughlin Road
 Mississauga, Ontario, L5R 1B8
 Canada
 EatonCanada.ca
 Cooperwiringdevices.com

Electrical Sector
 Mexico Operations
 Carr. Tlalnepantla -
 Cuautitlán Km 178 s/n
 Col. Villa Jardín esq.
 Cerrada 8 de Mayo
 Cuautitlán, México CP 54800
 México
 Eaton.mx
 Cooperwiringdevices.com

Eaton

1000 Eaton Boulevard
 Cleveland, OH 44122
 United States
 Eaton.com

© 2015 Eaton
 All Rights Reserved
 Printed in USA
 Publication No. BR610007EN
 August 2015

Eaton is a registered trademark.

All other trademarks are property
 of their respective owners.

EATON
 Powering Business Worldwide

EATON
 Powering Business Worldwide

Elegance beyond expectation

What is Aspire?

Aspire is Eaton's Wiring Devices' award-winning series of products that add a touch of elegance to the most sophisticated interior design. The clean, modern appearance of the Aspire product line represents the most innovative approach to designer wiring devices and makes a statement as an integral element of decor.

Aspire products



Dimmers

Turn lights ON and OFF and adjust the light intensity to create the right mood for any occasion using any load.



Switches

With performance-improving technical features, like backwire clamps on the terminal screws, you have a switch that not only looks great, but is easy to install and delivers high performance.



Timers

Easily programmable to alternate time intervals to suit your needs. Available in both hours and minutes versions. LED indication of time interval selected and countdown.



Receptacles/GFCIs

Installer-friendly features not only save labor, but ensure neat, firm connections and the most important feature of all — years of dependable, reliable service.



Screwless wallplates

Designed to coordinate with Aspire designer color series, wallplates appear to float freely on the surface of the wall, framing every device beautifully.

Designer series color options:

AW	AW	DS	DS	SG	SG	WS	WS
----	----	----	----	----	----	----	----

Alpine White

Desert Sand

Silver Granite

White Satin

Note: See catalog for color availability for specific products

Sophistication in every room

Aspire's unique and sophisticated appearance becomes a key element of interior design while providing precise, adjustable lighting control to create a sense of ambiance and reduce energy costs.

The Aspire design system features a full line of wiring devices to meet every application in every area of the home - kitchens, bathrooms, living rooms, dining rooms, home offices, media rooms, spas and pools.



Dimmers



Switches



Receptacle

Features & benefits

- Wide array of devices to cover every application for a complete, finished look throughout an entire home
- Smooth, quiet actuation with proven design features and functionality, combined with quality construction, provides years of dependable service
- Affordable luxury upgrade
- All products designed for ease of installation
- 4 coordinating color and texture combinations designed for today's homes
- Available in three distinctive, two-tone color combinations: White Satin, Desert Sand and Silver Granite, plus single-tone Alpine White

Details that define décor

All rooms begin the same way: walls, doors and windows. The details that you choose to add – fine moldings, furnishings and fixtures that define a room – transform it into a unique and distinctive expression of your personal sense of taste and style.

Now the Aspire design system enables homeowners to add a finishing touch of elegance to the most visible controls in any room – the light switches, dimmers and receptacles.



Setting the Mood

Aspire features an award-winning, stylish design and smooth, precise lighting control to set the right mood for any occasion.



Energy Savings

Aspire features microprocessor-controlled and mechanical dimmers, as well as matching timers that provide significant energy savings in addition to ambiance and light control.

Devices that compliment
your furnishings in every
room of your home.