

Eaton's Wiring Devices  
Universal Slide Dimmer

# Universal Slide Dimmer



Eaton's **Universal Slide Dimmers** are designed to match the ever-advancing technology of LED lights. In addition, these dimmers reduce energy consumption without compromising aesthetics, features or performance. Ideal for residential and light commercial applications.

**EATON**

*Powering Business Worldwide*

Eaton's **universal slide dimmer** is ergonomically designed and provides flicker-free dimming for seamless ambiance.



**Highly versatile**

Compatible with dimmable LED, dimmable CFL, INC, HAL, dimmable FLR, ELV and MLV light sources.

**Adjustable low-end trim**

Set the minimum light level for each switch using a simple control.

**Flicker-free dimming**

Microprocessor-based design enhances performance and delivers seamless dimming.

**Easy installation**

No neutral wire required. Back wire clamps speed installation.

**Universal slide dimmer**

**Product description**

Single Pole & 3-Way  
 300W Dimmable LED, Dimmable Compact Fluorescent (CFL)  
 600W Incandescent (INC)/Halogen (HAL), Dimmable Fluorescent (FLR),  
 Magnetic Low-Voltage (MLV), Electronic Low-Voltage (ELV)



**Updated technology**

**Design features**

- Preset feature allows user to return to previous light level when turning lights ON
- Device can be wired into either 3-way location (load side or line side)
- Neutral is not required for installation of device
- Adjustable low-level trim setting for optimal lamp compatibility
- Radio frequency interference filtering is standard on all models
- Electrostatic discharge protection
- Precise color matching
- Compatible with any decorator wallplate or screwless decorator wallplate
- Compatible with most common dimmable lighting loads (forward phase-cut)
- Soft gradual ON feature
- Title 20/24 compliant

**Universal Slide Dimmer**



Catalog No.	Description	Compatible Universal Types	Rating		Color Suffix
			Watt	V/AC	
□ SUL06P-__	Universal slide dimmer, single pole/3-way preset, back and side wire	Dimmable LED/CFL	300	120	B, BK, GY, LA, V, W
		Dimmable FLR, INC, HAL, MLV, ELV	600	120	B, BK, GY, LA, V, W

Compliances, specifications and availability are subject to change without notice.

**Color Ordering Information**

For ordering devices, include Cat. No. followed by the color code: B (Brown), BK (Black), GY (Gray), LA (Light Almond), V (Ivory), W (White)



Electrical Sector  
 203 Cooper Circle  
 Peachtree City, GA 30269  
 United States  
 Eaton.com  
 Eaton.com/wiringdevices

Electrical Sector  
 Canada Operations  
 5925 McLaughlin Road  
 Mississauga, Ontario, L5R 1B8  
 Canada  
 EatonCanada.ca  
 Eaton.com/wiringdevices

Electrical Sector  
 Mexico Operations  
 Carr. Tlalnepantla -  
 Cuautiltlan Km 17.8 s/n  
 Col. Villa Jardin esq.  
 Cerrada 8 de Mayo  
 Cuautiltlan, Mexico CP 54800  
 México  
 Eaton.mx  
 Eaton.com/wiringdevices



**Eaton**  
 1000 Eaton Boulevard  
 Cleveland, OH 44122  
 United States  
 Eaton.com

© 2019 Eaton  
 All Rights Reserved  
 Printed in USA  
 Publication No. SA610045EN  
 August 2019

Eaton is a registered trademark.  
 All other trademarks are property of their respective owners.