

Our universe is always expanding

Eaton's Universal Dimmers...

Dimming done right.

Eaton's **Universal Dimmers** are designed to match the ever-advancing technology of LED lights. In addition, these dimmers reduce energy consumption without compromising aesthetics, features or performance. Ideal for residential and light commercial applications.

EATON

Powering Business Worldwide

Eaton's universal dimmers are ergonomically designed and provide flicker-free dimming for seamless ambiance.

Highly versatile

Compatible with dimmable LED/CFL, INC, HAL, dimmable FLR, ELV and MLV light sources.

Adjustable low-end trim

Set the minimum light level for each switch using a simple control.

Flicker-free dimming

Microprocessor-based design enhances performance and delivers seamless dimming.

Easy installation

No neutral wire required. Back wire clamps speed installation.

Universal dimmers



Product description

Single Pole & 3-Way
300W Dimmable LED/CFL
600W Dimmable FLR, INC,
HAL, MLV, ELV

Design features

- Preset feature allows user to return to previous light level when turning lights ON
- Integrated full-slide control for easy, precise operation
- Device can be wired into either 3-way location (load side or line side)
- Neutral is not required for installation of device
- Adjustable low-level trim setting for optimal lamp compatibility
- Compatible with most common dimmable lighting loads (Forward phase-cut)*
- Soft gradual ON feature
- Faceplate is removable to allow for color changes (DUL06P & TUL06P)
- Color change kits are available with packout of 3 different colors for increased flexibility and convenience (DUL06P & TUL06P ONLY)
- Compatible with any decorator wallplate or screwless decorator wallplate (DUL06P & SUL06P ONLY)
- Compatible with any traditional toggle wallplate or screwless toggle wallplate (TUL06P ONLY)
- California Title 20/24 compliant

*Quick compatibility guide (www.eaton.com/led-dimming)

Universal Decorator Dimmer

Catalog No.	Description	Compatible Lamp Types	Rating		
			Watt	V/AC	Color Suffix
<input type="checkbox"/> DUL06P-__	Universal decorator dimmer, single pole/3-way preset, back and side wire	Dimmable LED/CFL INC, HAL, FLR, MLV, ELV	300	120	C2, C6, C7
<input type="checkbox"/> DCK1-__	Color change faceplate for DUL06P	—	—	—	B, BK, GY, LA, V, W

Universal Slide Dimmer

Catalog No.	Description	Compatible Lamp Types	Rating		
			Watt	V/AC	Color Suffix
<input type="checkbox"/> SUL06P-__	Universal slide dimmer, single pole/3-way preset, back and side wire	Dimmable LED/CFL INC, HAL, FLR, MLV, ELV	300	120	B, BK, GY, LA, V, W
<input type="checkbox"/> DCK1-__	Color change faceplate for DUL06P	—	—	—	B, BK, GY, LA, V, W


Universal Toggle Dimmer

Catalog No.	Description	Compatible Lamp Types	Rating		
			Watt	V/AC	Color Suffix
<input type="checkbox"/> TUL06P-__	Universal toggle dimmer single pole/3-way preset, back and side wire	Dimmable LED/CFL INC, HAL, FLR, MLV, ELV	300	120	C2, C7
<input type="checkbox"/> TCK3-__	Color change faceplate for TUL06P	—	—	—	B, BK, GY, LA, V, W

Compliances, specifications and availability are subject to change without notice.

Color ordering information

For ordering devices, include Catalog no. followed by the Color suffix: B (Brown), BK (Black), GY (Gray), LA (Light Almond), V (Ivory), W (White), RB (Oil Rubbed Bronze), SG (Silver Granite), C2 (Color Change Kit: LA, W, V), C6 (Color Change Kit: W, RB, SG), C7 (Color Change Kit: BK, B, GY)



C2 Color Change Kit
LA (Light Almond), W (White), V (Ivory)

C6 Color Change Kit
W (White), RB (Oil Rubbed Bronze), SG (Silver Granite)

C7 Color Change Kit
BK (Black), B (Brown), GY (Gray)

Electrical Sector
203 Cooper Circle
Peachtree City, GA 30269
United States
Eaton.com
Eaton.com/wiringdevices

Electrical Sector
Canada Operations
5925 McLaughlin Road
Mississauga, Ontario, L5R 1B8
Canada
EatonCanada.ca
Eaton.com/wiringdevices

Electrical Sector
Mexico Operations
Carr. Tlalnepantla -
Cuautitlán Km 17.8 s/n
Col. Villa Jardín esq.
Cerrada 8 de Mayo
Cuautitlán, Mexico CP 54800
México
Eaton.mx
Eaton.com/wiringdevices



Eaton
1000 Eaton Boulevard
Cleveland, OH 44122
United States
Eaton.com

© 2020 Eaton
All Rights Reserved
Printed in USA
Publication No. SA610048EN
March 2020

Eaton is a registered trademark.
All other trademarks are property of their respective owners.